

SIEMENS

OPC Interface Specifications V7

Fire WAN

Document No. A6V12061179_en_a_70
Edition 2023-09-29

ID	Object Model	Description		
Fire WAN-0010	FireWAN Enclosure	Rack for WAN modules.		
		States		Commands on OPC Item Mode
		OPC Item PresentValue	OPC Item Mode	Result State
		0-Quiet	1-Normal	Normal
		3-Fault	1-Normal	Fault
		267-Non Default Mode	12-Disabled	Disabled

ID	Object Model	Description
Fire WAN-0020	FireWAN HUB-4 Module	Module for FSI Panels connection.
States		
OPC Item PresentValue	OPC Item Mode	Result State
0-Quiet	1-Normal	Normal
3-Fault	1-Normal	Fault
267-Non Default Mode	12-Disabled	Disabled

Commands on OPC Item Mode	
\	\

ID	Object Model	Description
Fire WAN-0030	FireWAN HUB-4 Port	Modem or RS485 interfaces for FSI panel connection.
States		
OPC Item PresentValue	OPC Item Mode	Result State
0-Quiet	1-Normal	Normal
3-Fault	1-Normal	Fault
267-Non Default Mode	12-Disabled	Disabled

Commands on OPC Item Mode	
\	\

ID	Object Model	Description
Fire WAN-0040	FireWAN NIC-C Module	Module for Management Station connection.
States		
OPC Item PresentValue	OPC Item Mode	Result State
0-Quiet	1-Normal	Normal
3-Fault	1-Normal	Fault
267-Non Default Mode	12-Disabled	Disabled

Commands on OPC Item Mode	
\	\

ID	Object Model	Description		
Fire WAN-0050	FireWAN PSC-12 Module	Enclosure Power Supply.		
States			Commands on OPC Item Mode	
OPC Item PresentValue	OPC Item Mode	Result State	\	\
0-Quiet	1-Normal	Normal		
3-Fault	1-Normal	Fault		
267-Non Default Mode	1-Normal	Security		
267-Non Default Mode	12-Disabled	Disabled		

ID	Object Model	Description
Fire WAN-0060	FireWAN PSC-12 Relay	Enclosure Power Supply Relay for generic purposes.
States		
OPC Item PresentValue	OPC Item Mode	Result State
0-Quiet	1-Normal	Normal
3-Fault	1-Normal	Fault
267-Non Default Mode	12-Disabled	Disabled

Commands on OPC Item Mode	
\	\

ID	Object Model	Description
Fire WAN-0070	FireWAN PSX-12 Module	Enclosure Supplemental Power Supply.
States		
OPC Item PresentValue	OPC Item Mode	Result State
0-Quiet	1-Normal	Normal
3-Fault	1-Normal	Fault
267-Non Default Mode	1-Normal	Security
267-Non Default Mode	12-Disabled	Disabled

Commands on OPC Item Mode	
\	\

Siemens Industry Inc.
Building Technologies Division
1000 Deerfield Pkwy
Buffalo Grove IL 60089
Tel. +1 847-215-1000

© Siemens Industry Inc. 2012 - 2023
Technical specifications and availability subject to change without notice.