

Emerson Part Number	Siemens Part Number	Bray Part Number	Material Description
BV2W02FD6LNRXXX	A7F30003213	NYL2-C020/92-063-P	BFV 2W 2" 175PSI DA NC 60PSI POS
BV2W02FD6LNXXX	A7F30003207	NYL2-C020/92-063	BFV 2W 2" 175PSI DA 60PSI
BV2W02FD6LNYXXX	A7F30003209	NYL2-C020/92-063-SC	BFV 2W 2" 175PSI DA 60PSI 120V
BV2W02FD6LNZXXX	A7F30003210	NYL2-C020/92-063-S4C	BFV 2W 2" 175PSI DA 60PSI 24V
BV2W02FE2LNXXHX	A7F30077121	NYL2-C020/70-0061H	BFV 2W 2" 175PSI 120VAC 2 POS HTR
BV2W02FE2LNXXHX	A7F30077319	NYL2-C020/70-0061H	BFV 2W 2" 175PSI 120VAC 2 POS HTR
BV2W02FEMLNXXHX	A7F30077122	NYL2-C020/70-0061SVH	BFV 2W 2" 175PSI NC 120VAC MOD HTR
BV2W02FS6LCQXXX	A7F30004179	NYL2-C020/93-834-P	BFV 2W 2" 175PSI SR NC 60PSI POS
BV2W02FS6LCVXXX	A7F30004175	NYL2-C020/93-834-SC	BFV 2W 2" 175PSI SR NC 60PSI 120V
BV2W02FS6LCWXXX	A7F30004176	NYL2-C020/93-834-S4C	BFV 2W 2" 175PSI SR NC 60PSI 24V
BV2W02FS6LCXXX	A7F30004173	NYL2-C020/93-834	BFV 2W 2" 175PSI SR NC 60PSI
BV2W02FS6LOQXXX	A7F30004347	NYL2-N020/93-834-P	BFV 2W 2" 175PSI SR NO 60PSI POS
BV2W02FS6LOVXXX	A7F30004343	NYL2-N020/93-834-SC	BFV 2W 2" 175PSI SR NO 60PSI 120V
BV2W02FS6LOWXXX	A7F30004344	NYL2-N020/93-834-S4C	BFV 2W 2" 175PSI SR NO 60PSI 24V
BV2W02FS6LOXXX	A7F30004341	NYL2-N020/93-834	BFV 2W 2" 175PSI SR NO 60PSI
BV2W02UG1LCXXX	A7F30005152	NYL2-C020/GCA221.1U	BFV 2W 2" 175PSI SR NC 120VAC 2 POS
BV2W02UG1LOXXX	A7F30005208	NYL2-N020/GCA221.1U	BFV 2W 2" 175PSI SR NO 120VAC 2 POS
BV2W02UG2LCXXX	A7F30005150	NYL2-C020/GCA121.1U	BFV 2W 2" 175PSI SR NC 24VAC 2 POS
BV2W02UG2LOXAXX	A7F30005207	NYL2-N020/GCA126.1U	BFV 2W 2" 175PSI SR NO 24VAC 2 POS SW
BV2W02UG2LOXXX	A7F30005206	NYL2-N020/GCA121.1U	BFV 2W 2" 175PSI SR NO 24VAC 2 POS
BV2W02UG4LCXXX	A7F30005158	NYL2-C020/GCA161.1U	BFV 2W 2" 175PSI SR NC 24VAC 0-10DC
BV2W02UG4LOXXX	A7F30005210	NYL2-N020/GCA161.1U	BFV 2W 2" 175PSI SR NO 24VAC 0-10DC
BV2W02UG5LCXXX	A7F30005160	NYL2-C020/GCA151.1U	BFV 2W 2" 175PSI SR NC 24VAC 4-20mA
BV2W02UG5LOXXX	A7F30005212	NYL2-N020/GCA151.1U	BFV 2W 2" 175PSI SR NO 24VAC 4-20mA
BV2W02UG6LNXXX	A7F30005149	NYL2-C020/GBB131.1U	BFV 2W 2" 175PSI 24VAC TRI
BV2W02UG7LNXXX	A7F30005154	NYL2-C020/GBB161.1U	BFV 2W 2" 175PSI 24VAC 0-10DC
BV2W02UG8LNXXX	A7F30005156	NYL2-C020/GBB151.1U	BFV 2W 2" 175PSI 24VAC 4-20mA
BV2W03FD6LNRXXX	A7F30003229	NYL2-C030/92-083-P	BFV 2W 3" 175PSI DA NC 60PSI POS
BV2W03FD6LNXXX	A7F30003223	NYL2-C030/92-083	BFV 2W 3" 175PSI DA 60PSI
BV2W03FD6LNYXXX	A7F30003225	NYL2-C030/92-083-SC	BFV 2W 3" 175PSI DA 60PSI 120V
BV2W03FD6LNZXXX	A7F30003226	NYL2-C030/92-083-S4C	BFV 2W 3" 175PSI DA 60PSI 24V
BV2W03FE2LNXXHX	A7F30077127	NYL2-C030/70-0061H	BFV 2W 3" 175PSI 120VAC 2 POS HTR
BV2W03FE2LNXXX	A7F30077126	NYL2-C030/70-0061	BFV 2W 3" 175PSI 120VAC 2 POS
BV2W03FEMLNXXHX	A7F30077031	NYL2-C030/70-0061SVH	BFV 2W 3" 175PSI NC 120VAC MOD HTR
BV2W03FS6LCQXXX	A7F30004195	NYL2-C030/93-923-P	BFV 2W 3" 175PSI SR NC 60PSI POS
BV2W03FS6LCVXXX	A7F30004191	NYL2-C030/93-923-SC	BFV 2W 3" 175PSI SR NC 60PSI 120V
BV2W03FS6LCWXXX	A7F30004192	NYL2-C030/93-923-S4C	BFV 2W 3" 175PSI SR NC 60PSI 24V
BV2W03FS6LCXXX	A7F30004189	NYL2-C030/93-923	BFV 2W 3" 175PSI SR NC 60PSI
BV2W03FS6LOQXXX	A7F30004363	NYL2-N030/93-923-P	BFV 2W 3" 175PSI SR NO 60PSI POS
BV2W03FS6LOVXXX	A7F30004359	NYL2-N030/93-923-SC	BFV 2W 3" 175PSI SR NO 60PSI 120V
BV2W03FS6LOWXXX	A7F30004360	NYL2-N030/93-923-S4C	BFV 2W 3" 175PSI SR NO 60PSI 24V
BV2W03FS6LOXXX	A7F30004357	NYL2-N030/93-923	BFV 2W 3" 175PSI SR NO 60PSI
BV2W03UG1LCXXX	A7F30005178	NYL2-C030/GCA221.1U-D	BFV 2W 3" 175PSI SR NC 120VAC 2 POS
BV2W03UG1LOXAXX	A7F30005225	NYL2-N030/GCA226.1U-D	BFV 2W 3" 175PSI SR NO 120VAC 2 POS SW
BV2W03UG1LOXXX	A7F30005224	NYL2-N030/GCA221.1U-D	BFV 2W 3" 175PSI SR NO 120VAC 2 POS
BV2W03UG2LCXAXX	A7F30005179	NYL2-C030/GCA226.1U-D	BFV 2W 3" 175PSI SR NC 120VAC 2 POS SW
BV2W03UG2LCXXX	A7F30005176	NYL2-C030/GCA121.1U-D	BFV 2W 3" 175PSI SR NC 24VAC 2 POS
BV2W03UG2LOXXX	A7F30005222	NYL2-N030/GCA121.1U-D	BFV 2W 3" 175PSI SR NO 24VAC 2 POS
BV2W03UG4LCXXX	A7F30005182	NYL2-C030/GCA161.1U-D	BFV 2W 3" 175PSI SR NC 24VAC 0-10DC

BV2W03UG4LOXAXX	A7F30005227	NYL2-N030/GCA166.1U-D	BFV 2W 3" 175PSI SR NO 24VAC 0-10DC SW
BV2W03UG4LOXXXX	A7F30005226	NYL2-N030/GCA161.1U-D	BFV 2W 3" 175PSI SR NO 24VAC 0-10DC
BV2W03UG5LCXXXX	A7F30005184	NYL2-C030/GCA151.1U-D	BFV 2W 3" 175PSI SR NC 24VAC 4-20mA
BV2W03UG5LOXXXX	A7F30005228	NYL2-N030/GCA151.1U-D	BFV 2W 3" 175PSI SR NO 24VAC 4-20mA
BV2W03UG6LNXPXX	A7F30005181	NYL2-C030/GIB166.1U	BFV 2W 3" 175PSI 24VAC 0-10DC SW
BV2W03UG6LNXXXX	A7F30005175	NYL2-C030/GIB131.1U	BFV 2W 3" 175PSI 24VAC TRI
BV2W03UG7LNXXXX	A7F30005180	NYL2-C030/GIB161.1U	BFV 2W 3" 175PSI 24VAC 0-10DC
BV2W04FD6LNRXXX	A7F30003245	NYL2-C040/92-083-P	BFV 2W 4" 175PSI DA NC 60PSI POS
BV2W04FD6LNXXXX	A7F30003239	NYL2-C040/92-083	BFV 2W 4" 175PSI DA 60PSI
BV2W04FD6LNYXXX	A7F30003241	NYL2-C040/92-083-SC	BFV 2W 4" 175PSI DA 60PSI 120V
BV2W04FD6LNZXXX	A7F30003242	NYL2-C040/92-083-S4C	BFV 2W 4" 175PSI DA 60PSI 24V
BV2W04FE2LNXXHX	A7F30077132	NYL2-C040/70-0061H	BFV 2W 4" 175PSI 120VAC 2 POS HTR
BV2W04FE2LNXXXX	A7F30077131	NYL2-C040/70-0061	BFV 2W 4" 175PSI 120VAC 2 POS
BV2W04FEMLNXXHX	A7F30077030	NYL2-C040/70-0061SVH	BFV 2W 4" 175PSI NC 120VAC MOD HTR
BV2W04FS6LCQXXX	A7F30004211	NYL2-C040/93-1183-P	BFV 2W 4" 175PSI SR NC 60PSI POS
BV2W04FS6LCVXXX	A7F30004207	NYL2-C040/93-1183-SC	BFV 2W 4" 175PSI SR NC 60PSI 120V
BV2W04FS6LCWXXX	A7F30004208	NYL2-C040/93-1183-S4C	BFV 2W 4" 175PSI SR NC 60PSI 24V
BV2W04FS6LCXXXX	A7F30004205	NYL2-C040/93-1183	BFV 2W 4" 175PSI SR NC 60PSI
BV2W04FS6LOQXXX	A7F30004379	NYL2-N040/93-1183-P	BFV 2W 4" 175PSI SR NO 60PSI POS
BV2W04FS6LOVXXX	A7F30004375	NYL2-N040/93-1183-SC	BFV 2W 4" 175PSI SR NO 60PSI 120V
BV2W04FS6LOWXXX	A7F30004376	NYL2-N040/93-1183-S4C	BFV 2W 4" 175PSI SR NO 60PSI 24V
BV2W04FS6LOXXXX	A7F30004373	NYL2-N040/93-1183	BFV 2W 4" 175PSI SR NO 60PSI
BV2W04UD6LNRXXX	A7F30003237	NYL2-C041/92-083-P	BFV 2W 4" 50PSI DA NC 60PSI POS
BV2W04UD6LNXXXX	A7F30003231	NYL2-C041/92-083	BFV 2W 4" 50PSI DA 60PSI
BV2W04UD6LNYXXX	A7F30003233	NYL2-C041/92-083-SC	BFV 2W 4" 50PSI DA 60PSI 120V
BV2W04UD6LNZXXX	A7F30003234	NYL2-C041/92-083-S4C	BFV 2W 4" 50PSI DA 60PSI 24V
BV2W04UE2LNXXHX	A7F30077129	NYL2-C041/70-0061H	BFV 2W 4" 50PSI 120VAC 2 POS HTR
BV2W04UE2LNXXXX	A7F30077128	NYL2-C041/70-0061	BFV 2W 4" 50PSI 120VAC 2 POS
BV2W04UEMLNXXHX	A7F30077130	NYL2-C041/70-0061SVH	BFV 2W 4" 50PSI NC 120VAC MOD HTR
BV2W04UG1LCXXXX	A7F30005189	NYL2-C041/GCA221.1U-D	BFV 2W 4" 50PSI SR NC 120VAC 2 POS
BV2W04UG1LOXXXX	A7F30005232	NYL2-N041/GCA221.1U-D	BFV 2W 4" 50PSI SR NO 120VAC 2 POS
BV2W04UG2LCXAXX	A7F30005188	NYL2-C041/GCA126.1U-D	BFV 2W 4" 50PSI SR NC 24VAC 2 POS SW
BV2W04UG2LCXXXX	A7F30005187	NYL2-C041/GCA121.1U-D	BFV 2W 4" 50PSI SR NC 24VAC 2 POS
BV2W04UG2LOXAXX	A7F30005231	NYL2-N041/GCA126.1U-D	BFV 2W 4" 50PSI SR NO 24VAC 2 POS SW
BV2W04UG2LOXXXX	A7F30005230	NYL2-N041/GCA121.1U-D	BFV 2W 4" 50PSI SR NO 24VAC 2 POS
BV2W04UG4LCXXXX	A7F30005193	NYL2-C041/GCA161.1U-D	BFV 2W 4" 50PSI SR NC 24VAC 0-10DC
BV2W04UG4LOXXXX	A7F30005234	NYL2-N041/GCA161.1U-D	BFV 2W 4" 50PSI SR NO 24VAC 0-10DC
BV2W04UG5LCXXXX	A7F30005195	NYL2-C041/GCA151.1U-D	BFV 2W 4" 50PSI SR NC 24VAC 4-20mA
BV2W04UG5LOXXXX	A7F30005236	NYL2-N041/GCA151.1U-D	BFV 2W 4" 50PSI SR NO 24VAC 4-20mA
BV2W04UG6LNXXXX	A7F30005186	NYL2-C041/GIB131.1U	BFV 2W 4" 50PSI 24VAC TRI
BV2W04UG7LNXXXX	A7F30005191	NYL2-C041/GIB161.1U	BFV 2W 4" 50PSI 24VAC 0-10DC
BV2W04US6LCQXXX	A7F30004203	NYL2-C041/93-834-P	BFV 2W 4" 50PSI SR NC 60PSI POS
BV2W04US6LCVXXX	A7F30004199	NYL2-C041/93-834-SC	BFV 2W 4" 50PSI SR NC 60PSI 120V
BV2W04US6LCWXXX	A7F30004200	NYL2-C041/93-834-S4C	BFV 2W 4" 50PSI SR NC 60PSI 24V
BV2W04US6LCXXXX	A7F30004197	NYL2-C041/93-834	BFV 2W 4" 50PSI SR NC 60PSI
BV2W04US6LOQXXX	A7F30004371	NYL2-N041/93-834-P	BFV 2W 4" 50PSI SR NO 60PSI POS
BV2W04US6LOVXXX	A7F30004367	NYL2-N041/93-834-SC	BFV 2W 4" 50PSI SR NO 60PSI 120V
BV2W04US6LOWXXX	A7F30004368	NYL2-N041/93-834-S4C	BFV 2W 4" 50PSI SR NO 60PSI 24V
BV2W04US6LOXXXX	A7F30004365	NYL2-N041/93-834	BFV 2W 4" 50PSI SR NO 60PSI
BV2W05FD6LNRXXX	A7F30003261	NYL2-C050/92-092-P	BFV 2W 5" 175PSI DA NC 60PSI POS
BV2W05FD6LNXXXX	A7F30003255	NYL2-C050/92-092	BFV 2W 5" 175PSI DA 60PSI
BV2W05FD6LNYXXX	A7F30003257	NYL2-C050/92-092-SC	BFV 2W 5" 175PSI DA 60PSI 120V

Unrestricted

BV2W05FD6LNZXXX	A7F30003258	NYL2-C050/92-092-S4C	BFV 2W 5" 175PSI DA 60PSI 24V
BV2W05FE2LNXXHX	A7F30077137	NYL2-C050/70-0061H	BFV 2W 5" 175PSI 120VAC 2 POS HTR
BV2W05FE2LNXXXX	A7F30077136	NYL2-C050/70-0061	BFV 2W 5" 175PSI 120VAC 2 POS
BV2W05FEMLNXXHX	A7F30077138	NYL2-C050/70-0061SVH	BFV 2W 5" 175PSI NC 120VAC MOD HTR
BV2W05FS6LCQXXX	A7F30004227	NYL2-C050/93-1184-P	BFV 2W 5" 175PSI SR NC 60PSI POS
BV2W05FS6LCVXXX	A7F30004223	NYL2-C050/93-1184-SC	BFV 2W 5" 175PSI SR NC 60PSI 120V
BV2W05FS6LCWXXX	A7F30004224	NYL2-C050/93-1184-S4C	BFV 2W 5" 175PSI SR NC 60PSI 24V
BV2W05FS6LCXXXX	A7F30004221	NYL2-C050/93-1184	BFV 2W 5" 175PSI SR NC 60PSI
BV2W05FS6LOQXXX	A7F30004395	NYL2-N050/93-1184-P	BFV 2W 5" 175PSI SR NO 60PSI POS
BV2W05FS6LOVXXX	A7F30004391	NYL2-N050/93-1184-SC	BFV 2W 5" 175PSI SR NO 60PSI 120V
BV2W05FS6LOWXXX	A7F30004392	NYL2-N050/93-1184-S4C	BFV 2W 5" 175PSI SR NO 60PSI 24V
BV2W05FS6LOXXXX	A7F30004389	NYL2-N050/93-1184	BFV 2W 5" 175PSI SR NO 60PSI
BV2W05UD6LNRXXX	A7F30003253	NYL2-C051/92-083-P	BFV 2W 5" 50PSI DA NC 60PSI POS
BV2W05UD6LNXXXX	A7F30003247	NYL2-C051/92-083	BFV 2W 5" 50PSI DA 60PSI
BV2W05UD6LNYXXX	A7F30003249	NYL2-C051/92-083-SC	BFV 2W 5" 50PSI DA 60PSI 120V
BV2W05UD6LNZXXX	A7F30003250	NYL2-C051/92-083-S4C	BFV 2W 5" 50PSI DA 60PSI 24V
BV2W05UE2LNXXHX	A7F30077134	NYL2-C051/70-0061H	BFV 2W 5" 50PSI 120VAC 2 POS HTR
BV2W05UE2LNXXXX	A7F30077133	NYL2-C051/70-0061	BFV 2W 5" 50PSI 120VAC 2 POS
BV2W05UEMLNXXHX	A7F30077135	NYL2-C051/70-0061SVH	BFV 2W 5" 50PSI NC 120VAC MOD HTR
BV2W05UG6LNXXXX	A7F30005200	NYL2-C051/GIB131.1U-D	BFV 2W 5" 50PSI 24VAC TRI
BV2W05UG7LNAXX	A7F30005202	NYL2-C051/GIB166.1U-D	BFV 2W 5" 50PSI 24VAC 0-10DC SW
BV2W05UG7LNXXXX	A7F30005201	NYL2-C051/GIB161.1U-D	BFV 2W 5" 50PSI 24VAC 0-10DC
BV2W05US6LCQXXX	A7F30004219	NYL2-C051/93-1183-P	BFV 2W 5" 50PSI SR NC 60PSI POS
BV2W05US6LCVXXX	A7F30004215	NYL2-C051/93-1183-SC	BFV 2W 5" 50PSI SR NC 60PSI 120V
BV2W05US6LCWXXX	A7F30004216	NYL2-C051/93-1183-S4C	BFV 2W 5" 50PSI SR NC 60PSI 24V
BV2W05US6LCXXXX	A7F30004213	NYL2-C051/93-1183	BFV 2W 5" 50PSI SR NC 60PSI
BV2W05US6LOQXXX	A7F30004387	NYL2-N051/93-1183-P	BFV 2W 5" 50PSI SR NO 60PSI POS
BV2W05US6LOVXXX	A7F30004383	NYL2-N051/93-1183-SC	BFV 2W 5" 50PSI SR NO 60PSI 120V
BV2W05US6LOWXXX	A7F30004384	NYL2-N051/93-1183-S4C	BFV 2W 5" 50PSI SR NO 60PSI 24V
BV2W05US6LOXXXX	A7F30004381	NYL2-N051/93-1183	BFV 2W 5" 50PSI SR NO 60PSI
BV2W06FD6LNRXXX	A7F30003277	NYL2-C060/92-119-P	BFV 2W 6" 175PSI DA NC 60PSI POS
BV2W06FD6LNXXXX	A7F30003271	NYL2-C060/92-119	BFV 2W 6" 175PSI DA 60PSI
BV2W06FD6LNYXXX	A7F30003276	NYL2-C060/92-119-SC	BFV 2W 6" 175PSI DA 60PSI 24V SW
BV2W06FD6LNZXXX	A7F30003273	NYL2-C060/92-119-S4C	BFV 2W 6" 175PSI DA 60PSI 120V
BV2W06FE2LNXXHX	A7F30077143	NYL2-C060/70-0061H	BFV 2W 6" 175PSI 120VAC 2 POS HTR
BV2W06FE2LNXXXX	A7F30077142	NYL2-C060/70-0061	BFV 2W 6" 175PSI 120VAC 2 POS
BV2W06FEMLNXXHX	A7F30077144	NYL2-C060/70-0061SVH	BFV 2W 6" 175PSI NC 120VAC MOD HTR
BV2W06FS6LCQXXX	A7F30004243	NYL2-C060/93-1284-P	BFV 2W 6" 175PSI SR NC 60PSI POS
BV2W06FS6LCVXXX	A7F30004242	NYL2-C060/93-1284-SC	BFV 2W 6" 175PSI SR NC 60PSI 24V SW
BV2W06FS6LCWXXX	A7F30004239	NYL2-C060/93-1284-S4C	BFV 2W 6" 175PSI SR NC 60PSI 120V
BV2W06FS6LCXXXX	A7F30004237	NYL2-C060/93-1284	BFV 2W 6" 175PSI SR NC 60PSI
BV2W06FS6LOQXXX	A7F30004411	NYL2-N060/93-1274-P	BFV 2W 6" 175PSI SR NO 60PSI POS
BV2W06FS6LOVXXX	A7F30004407	NYL2-N060/93-1274-SC	BFV 2W 6" 175PSI SR NO 60PSI 120V
BV2W06FS6LOWXXX	A7F30004408	NYL2-N060/93-1274-S4C	BFV 2W 6" 175PSI SR NO 60PSI 24V
BV2W06UD6LNRXXX	A7F30003269	NYL2-C061/92-083-P	BFV 2W 6" 50PSI DA NC 60PSI POS
BV2W06UD6LNXXXX	A7F30003263	NYL2-C061/92-083	BFV 2W 6" 50PSI DA 60PSI
BV2W06UD6LNYXXX	A7F30003265	NYL2-C061/92-083-SC	BFV 2W 6" 50PSI DA 60PSI 120V
BV2W06UD6LNZXXX	A7F30003266	NYL2-C061/92-083-S4C	BFV 2W 6" 50PSI DA 60PSI 24V
BV2W06UE2LNXXHX	A7F30077140	NYL2-C061/70-0061H	BFV 2W 6" 50PSI 120VAC 2 POS HTR
BV2W06UE2LNXXXX	A7F30077139	NYL2-C061/70-0061	BFV 2W 6" 50PSI 120VAC 2 POS
BV2W06UEMLNXXHX	A7F30077141	NYL2-C061/70-0061SVH	BFV 2W 6" 50PSI NC 120VAC MOD HTR
BV2W06UG6LNXXXX	A7F30005203	NYL2-C061/GIB131.1U-D	BFV 2W 6" 50PSI 24VAC TRI

Unrestricted

BV2W06UG7LNXXXX	A7F30005205	NYL2-C061/GIB166.1U-D	BFV 2W 6" 50PSI 24VAC 0-10DC SW
BV2W06UG7LNXXXX	A7F30005204	NYL2-C061/GIB161.1U-D	BFV 2W 6" 50PSI 24VAC 0-10DC
BV2W06US6LCQXXX	A7F30004235	NYL2-C061/93-1183-P	BFV 2W 6" 50PSI SR NC 60PSI POS
BV2W06US6LCVXXX	A7F30004231	NYL2-C061/93-1183-SC	BFV 2W 6" 50PSI SR NC 60PSI 120V
BV2W06US6LCWXXX	A7F30004232	NYL2-C061/93-1183-S4C	BFV 2W 6" 50PSI SR NC 60PSI 24V
BV2W06US6LCXXXX	A7F30004229	NYL2-C061/93-1183	BFV 2W 6" 50PSI SR NC 60PSI
BV2W06US6LOQXXX	A7F30004403	NYL2-N061/93-1183-P	BFV 2W 6" 50PSI SR NO 60PSI POS
BV2W06US6LOVXXX	A7F30004399	NYL2-N061/93-1183-SC	BFV 2W 6" 50PSI SR NO 60PSI 120V
BV2W06US6LOWXXX	A7F30004400	NYL2-N061/93-1183-S4C	BFV 2W 6" 50PSI SR NO 60PSI 24V
BV2W06US6LOXXXX	A7F30004397	NYL2-N061/93-1183	BFV 2W 6" 50PSI SR NO 60PSI
BV2W08FD6LNRXXX	A7F30003293	NYL2-C080/92-127-P	BFV 2W 8" 175PSI DA NC 60PSI POS
BV2W08FD6LNXXXX	A7F30003287	NYL2-C080/92-127	BFV 2W 8" 175PSI DA 60PSI
BV2W08FD6LNYXXX	A7F30003289	NYL2-C080/92-127-S	BFV 2W 8" 175PSI DA 60PSI 120V
BV2W08FD6LNZXXX	A7F30003290	NYL2-C080/92-127-S4C	BFV 2W 8" 175PSI DA 60PSI 24V
BV2W08FE2LNXXHX	A7F30001796	NYL2-C080/70-0201H	BFV 2W 8" 175PSI 120VAC 2 POS HTR
BV2W08FE2LNXXXX	A7F30001795	NYL2-C080/70-0201	BFV 2W 8" 175PSI 120VAC 2 POS
BV2W08FEMLNXXHX	A7F30001797	NYL2-C080/70-0201SVH	BFV 2W 8" 175PSI NC 120VAC MOD HTR
BV2W08FS6LCQXXX	A7F30004259	NYL2-C080/93-1604-P	BFV 2W 8" 175PSI SR NC 60PSI POS
BV2W08FS6LCVXXX	A7F30004255	NYL2-C080/93-1604-SC	BFV 2W 8" 175PSI SR NC 60PSI 120V
BV2W08FS6LCWXXX	A7F30004256	NYL2-C080/93-1604-S4C	BFV 2W 8" 175PSI SR NC 60PSI 24V
BV2W08FS6LCXXXX	A7F30004253	NYL2-C080/93-1604	BFV 2W 8" 175PSI SR NC 60PSI
BV2W08FS6LOQXXX	A7F30004427	NYL2-N080/93-1603-P	BFV 2W 8" 175PSI SR NO 60PSI POS
BV2W08FS6LOVXXX	A7F30004423	NYL2-N080/93-1603-SC	BFV 2W 8" 175PSI SR NO 60PSI 120V
BV2W08FS6LOWXXX	A7F30004424	NYL2-N080/93-1603-S4C	BFV 2W 8" 175PSI SR NO 60PSI 24V
BV2W08UD6LNRXXX	A7F30003285	NYL2-C081/92-118-P	BFV 2W 8" 50PSI DA NC 60PSI POS
BV2W08UD6LNXXXX	A7F30003279	NYL2-C081/92-118	BFV 2W 8" 50PSI DA 60PSI
BV2W08UD6LNYXXX	A7F30003281	NYL2-C081/92-118-S	BFV 2W 8" 50PSI DA 60PSI 120V
BV2W08UD6LNZXXX	A7F30003282	NYL2-C081/92-118-S4C	BFV 2W 8" 50PSI DA 60PSI 24V
BV2W08UE2LNXXHX	A7F30001778	NYL2-C081/70-0121H	BFV 2W 8" 50PSI 120VAC 2 POS HTR
BV2W08UE2LNXXXX	A7F30001777	NYL2-C081/70-0121	BFV 2W 8" 50PSI 120VAC 2 POS
BV2W08UEMLNXXHX	A7F30001779	NYL2-C081/70-0121SVH	BFV 2W 8" 50PSI NC 120VAC MOD HTR
BV2W08US6LCQXXX	A7F30004251	NYL2-C081/93-1274-P	BFV 2W 8" 50PSI SR NC 60PSI POS
BV2W08US6LCVXXX	A7F30004247	NYL2-C081/93-1274-S	BFV 2W 8" 50PSI SR NC 60PSI 120V
BV2W08US6LCWXXX	A7F30004248	NYL2-C081/93-1274-S4C	BFV 2W 8" 50PSI SR NC 60PSI 24V
BV2W08US6LCXXXX	A7F30004245	NYL2-C081/93-1274	BFV 2W 8" 50PSI SR NC 60PSI
BV2W08US6LOQXXX	A7F30004419	NYL2-N081/93-1274-P	BFV 2W 8" 50PSI SR NO 60PSI POS
BV2W08US6LOVXXX	A7F30004415	NYL2-N081/93-1274-SC	BFV 2W 8" 50PSI SR NO 60PSI 120V
BV2W08US6LOWXXX	A7F30004416	NYL2-N081/93-1274-S4C	BFV 2W 8" 50PSI SR NO 60PSI 24V
BV2W08US6LOXXXX	A7F30004413	NYL2-N081/93-1274	BFV 2W 8" 50PSI SR NO 60PSI
BV2W10FD6LNRXXX	A7F30003309	NYL2-C100/92-160-P	BFV 2W 10" 175PSI DA NC 60PSI POS
BV2W10FD6LNXXXX	A7F30003303	NYL2-C100/92-160	BFV 2W 10" 175PSI DA 60PSI
BV2W10FD6LNYXXX	A7F30003307	NYL2-C100/92-160-SC-SW	BFV 2W 10" 175PSI DA 60PSI 120V SW
BV2W10FD6LNYXXX	A7F30003305	NYL2-C100/92-160-SC	BFV 2W 10" 175PSI DA 60PSI 120V
BV2W10FD6LNZXXX	A7F30003306	NYL2-C100/92-160-S4C	BFV 2W 10" 175PSI DA 60PSI 24V
BV2W10FE2LNXXHX	A7F30001828	NYL2-C100/70-0301H	BFV 2W 10" 175PSI 120VAC 2 POS HTR
BV2W10FE2LNXXXX	A7F30001827	NYL2-C100/70-0301	BFV 2W 10" 175PSI 120VAC 2 POS
BV2W10FEMLNXXHX	A7F30001829	NYL2-C100/70-0301SVH	BFV 2W 10" 175PSI NC 120VAC MOD HTR
BV2W10FS6LCQXXX	A7F30004275	NYL2-C100/93-2103-P	BFV 2W 10" 175PSI SR NC 60PSI POS
BV2W10FS6LCVXXX	A7F30004271	NYL2-C100/93-2103-SC	BFV 2W 10" 175PSI SR NC 60PSI 120V
BV2W10FS6LCWXXX	A7F30004272	NYL2-C100/93-2103-S4C	BFV 2W 10" 175PSI SR NC 60PSI 24V
BV2W10FS6LCXXXX	A7F30004269	NYL2-C100/93-2103	BFV 2W 10" 175PSI SR NC 60PSI
BV2W10FS6LOQXXX	A7F30004443	NYL2-N100/93-2103-P	BFV 2W 10" 175PSI SR NO 60PSI POS

Unrestricted

BV2W10FS6LOVXXX	A7F30004439	NYL2-N100/93-2103-SC	BFV 2W 10" 175PSI SR NO 60PSI 120V
BV2W10FS6LOWXXX	A7F30004441	NYL2-N100/93-2103-SC-SW	BFV 2W 10" 175PSI SR NO 60PSI 120V SW
BV2W10FS6LOWXXX	A7F30004440	NYL2-N100/93-2103-S4C	BFV 2W 10" 175PSI SR NO 60PSI 24V
BV2W10FS6LOXXX	A7F30004437	NYL2-N100/93-2103	BFV 2W 10" 175PSI SR NO 60PSI
BV2W10UD6LNRXXX	A7F30003301	NYL2-C101/92-118-P	BFV 2W 10" 50PSI DA NC 60PSI POS
BV2W10UD6LNXXX	A7F30003295	NYL2-C101/92-118	BFV 2W 10" 50PSI DA 60PSI
BV2W10UD6LNYXXX	A7F30003299	NYL2-C101/92-118-SC-SW	BFV 2W 10" 50PSI DA 60PSI 120V SW
BV2W10UD6LNYXXX	A7F30003297	NYL2-C101/92-118-S	BFV 2W 10" 50PSI DA 60PSI 120V
BV2W10UD6LNZXXX	A7F30003298	NYL2-C101/92-118-S4C	BFV 2W 10" 50PSI DA 60PSI 24V
BV2W10UE2LNXXHX	A7F30001799	NYL2-C101/70-0201H	BFV 2W 10" 50PSI 120VAC 2 POS HTR
BV2W10UE2LNXXX	A7F30001798	NYL2-C101/70-0201	BFV 2W 10" 50PSI 120VAC 2 POS
BV2W10UEMLNXXHX	A7F30001815	NYL2-C101/70-0201SVH	BFV 2W 10" 50PSI NC 120VAC MOD HTR
BV2W10US6LCQXXX	A7F30004267	NYL2-C101/93-1604-P	BFV 2W 10" 50PSI SR NC 60PSI POS
BV2W10US6LCVXXX	A7F30004263	NYL2-C101/93-1604-SC	BFV 2W 10" 50PSI SR NC 60PSI 120V
BV2W10US6LCWXXX	A7F30004264	NYL2-C101/93-1604-S4C	BFV 2W 10" 50PSI SR NC 60PSI 24V
BV2W10US6LCXXX	A7F30004261	NYL2-C101/93-1604	BFV 2W 10" 50PSI SR NC 60PSI
BV2W10US6LOQXXX	A7F30004435	NYL2-N101/93-1604-P	BFV 2W 10" 50PSI SR NO 60PSI POS
BV2W10US6LOVXXX	A7F30004431	NYL2-N101/93-1604-SC	BFV 2W 10" 50PSI SR NO 60PSI 120V
BV2W10US6LOWXXX	A7F30004432	NYL2-N101/93-1604-S4C	BFV 2W 10" 50PSI SR NO 60PSI 24V
BV2W10US6LOXXX	A7F30004429	NYL2-N101/93-1604	BFV 2W 10" 50PSI SR NO 60PSI
BV2W12FD6LNRXXX	A7F30003325	NYL2-C120/92-160-P	BFV 2W 12" 175PSI DA NC 60PSI POS
BV2W12FD6LNXXX	A7F30003319	NYL2-C120/92-160	BFV 2W 12" 175PSI DA 60PSI
BV2W12FD6LNYXXX	A7F30003321	NYL2-C120/92-160-SC	BFV 2W 12" 175PSI DA 60PSI 120V
BV2W12FD6LNZXXX	A7F30003322	NYL2-C120/92-160-S4C	BFV 2W 12" 175PSI DA 60PSI 24V
BV2W12FE2LNXXHX	A7F30001858	NYL2-C120/70-0501H	BFV 2W 12" 175PSI 120VAC 2 POS HTR
BV2W12FE2LNXXX	A7F30001857	NYL2-C120/70-0501	BFV 2W 12" 175PSI 120VAC 2 POS
BV2W12FEMLNXXHX	A7F30001859	NYL2-C120/70-0501SVH	BFV 2W 12" 175PSI NC 120VAC MOD HTR
BV2W12FS6LCQXXX	A7F30004291	NYL2-C120/93-2552-P	BFV 2W 12" 175PSI SR NC 60PSI POS
BV2W12FS6LCVXXX	A7F30004287	NYL2-C120/93-2552-SC	BFV 2W 12" 175PSI SR NC 60PSI 120V
BV2W12FS6LCWXXX	A7F30004288	NYL2-C120/93-2552-S4C	BFV 2W 12" 175PSI SR NC 60PSI 24V
BV2W12FS6LCXXX	A7F30004285	NYL2-C120/93-2552	BFV 2W 12" 175PSI SR NC 60PSI
BV2W12FS6LOQXXX	A7F30004459	NYL2-N120/93-2552-P	BFV 2W 12" 175PSI SR NO 60PSI POS
BV2W12FS6LOVXXX	A7F30004455	NYL2-N120/93-2552-SC	BFV 2W 12" 175PSI SR NO 60PSI 120V
BV2W12FS6LOWXXX	A7F30004456	NYL2-N120/93-2552-S4C	BFV 2W 12" 175PSI SR NO 60PSI 24V
BV2W12FS6LOXXX	A7F30004453	NYL2-N120/93-2552	BFV 2W 12" 175PSI SR NO 60PSI
BV2W12UD6LNRXXX	A7F30003317	NYL2-C121/92-127-P	BFV 2W 12" 50PSI DA NC 60PSI POS
BV2W12UD6LNXXX	A7F30003311	NYL2-C121/92-127	BFV 2W 12" 50PSI DA 60PSI
BV2W12UD6LNYXXX	A7F30003313	NYL2-C121/92-127-SC	BFV 2W 12" 50PSI DA 60PSI 120V
BV2W12UD6LNZXXX	A7F30003314	NYL2-C121/92-127-S4C	BFV 2W 12" 50PSI DA 60PSI 24V
BV2W12UE2LNXXHX	A7F30001855	NYL2-C121/70-0301H	BFV 2W 12" 50PSI 120VAC 2 POS HTR
BV2W12UE2LNXXX	A7F30001854	NYL2-C121/70-0301	BFV 2W 12" 50PSI 120VAC 2 POS
BV2W12UEMLNXXHX	A7F30001856	NYL2-C121/70-0301SVH	BFV 2W 12" 50PSI NC 120VAC MOD HTR
BV2W12US6LCQXXX	A7F30004283	NYL2-C121/93-1605-P	BFV 2W 12" 50PSI SR NC 60PSI POS
BV2W12US6LCVXXX	A7F30004279	NYL2-C121/93-1605-SC	BFV 2W 12" 50PSI SR NC 60PSI 120V
BV2W12US6LCWXXX	A7F30004280	NYL2-C121/93-1605-S4C	BFV 2W 12" 50PSI SR NC 60PSI 24V
BV2W12US6LCXXX	A7F30004277	NYL2-C121/93-1605	BFV 2W 12" 50PSI SR NC 60PSI
BV2W12US6LOQXXX	A7F30004451	NYL2-N121/93-1605-P	BFV 2W 12" 50PSI SR NO 60PSI POS
BV2W12US6LOVXXX	A7F30004447	NYL2-N121/93-1605-SC	BFV 2W 12" 50PSI SR NO 60PSI 120V
BV2W12US6LOWXXX	A7F30004448	NYL2-N121/93-1605-S4C	BFV 2W 12" 50PSI SR NO 60PSI 24V
BV2W12US6LOXXX	A7F30004445	NYL2-N121/93-1605	BFV 2W 12" 50PSI SR NO 60PSI
BV2W14FD6LNRXXX	A7F30003341	NYL2-C140/92-210-P	BFV 2W 14" 150PSI DA NC 60PSI POS
BV2W14FD6LNXXX	A7F30003335	NYL2-C140/92-210	BFV 2W 14" 150PSI DA 60PSI

Unrestricted

BV2W14FD6LNYXXX	A7F30003337	NYL2-C140/92-210-SC	BFV 2W 14" 150PSI DA 60PSI 120V
BV2W14FD6LNZXXX	A7F30003338	NYL2-C140/92-210-S4C	BFV 2W 14" 150PSI DA 60PSI 24V
BV2W14FE2LNXXHX	A7F30001907	NYL2-C140/70-0651H	BFV 2W 14" 150PSI 120VAC 2 POS HTR
BV2W14FE2LNXXXX	A7F30001906	NYL2-C140/70-0651	BFV 2W 14" 150PSI 120VAC 2 POS
BV2W14FEMLNXXHX	A7F30001908	NYL2-C140/70-0651SVH	BFV 2W 14" 150PSI NC 120VAC MOD HTR
BV2W14FS6LCQXXX	A7F30004307	NYL2-C140/93-2553-P	BFV 2W 14" 150PSI SR NC 60PSI POS
BV2W14FS6LCVXXX	A7F30004303	NYL2-C140/93-2553-SC	BFV 2W 14" 150PSI SR NC 60PSI 120V
BV2W14FS6LCWXXX	A7F30004304	NYL2-C140/93-2553-S4C	BFV 2W 14" 150PSI SR NC 60PSI 24V
BV2W14FS6LCXXXX	A7F30004301	NYL2-C140/93-2553	BFV 2W 14" 150PSI SR NC 60PSI
BV2W14FS6LOQXXX	A7F30004475	NYL2-N140/93-2553-P	BFV 2W 14" 150PSI SR NO 60PSI POS
BV2W14FS6LOVXXX	A7F30004471	NYL2-N140/93-2553-SC	BFV 2W 14" 150PSI SR NO 60PSI 120V
BV2W14FS6LOWXXX	A7F30004472	NYL2-N140/93-2553-S4C	BFV 2W 14" 150PSI SR NO 60PSI 24V
BV2W14FS6LOXXXX	A7F30004469	NYL2-N140/93-2553	BFV 2W 14" 150PSI SR NO 60PSI
BV2W14UD6LNRXXX	A7F30003333	NYL2-C141/92-160-P	BFV 2W 14" 50PSI DA NC 60PSI POS
BV2W14UD6LNXXXX	A7F30003327	NYL2-C141/92-160	BFV 2W 14" 50PSI DA 60PSI
BV2W14UD6LNYXXX	A7F30003329	NYL2-C141/92-160-SC	BFV 2W 14" 50PSI DA 60PSI 120V
BV2W14UD6LNZXXX	A7F30003330	NYL2-C141/92-160-S4C	BFV 2W 14" 50PSI DA 60PSI 24V
BV2W14UE2LNXXHX	A7F30001904	NYL2-C141/70-0501H	BFV 2W 14" 50PSI 120VAC 2 POS HTR
BV2W14UE2LNXXXX	A7F30001883	NYL2-C141/70-0501	BFV 2W 14" 50PSI 120VAC 2 POS
BV2W14UEMLNXXHX	A7F30001905	NYL2-C141/70-0501SVH	BFV 2W 14" 50PSI NC 120VAC MOD HTR
BV2W14US6LCQXXX	A7F30004299	NYL2-C141/93-2104-P	BFV 2W 14" 50PSI SR NC 60PSI POS
BV2W14US6LCVXXX	A7F30004295	NYL2-C141/93-2104-SC	BFV 2W 14" 50PSI SR NC 60PSI 120V
BV2W14US6LCWXXX	A7F30004296	NYL2-C141/93-2104-S4C	BFV 2W 14" 50PSI SR NC 60PSI 24V
BV2W14US6LCXXXX	A7F30004293	NYL2-C141/93-2104	BFV 2W 14" 50PSI SR NC 60PSI
BV2W14US6LOQXXX	A7F30004467	NYL2-N141/93-2104-P	BFV 2W 14" 50PSI SR NO 60PSI POS
BV2W14US6LOVXXX	A7F30004463	NYL2-N141/93-2104-SC	BFV 2W 14" 50PSI SR NO 60PSI 120V
BV2W14US6LOWXXX	A7F30004464	NYL2-N141/93-2104-S4C	BFV 2W 14" 50PSI SR NO 60PSI 24V
BV2W14US6LOXXXX	A7F30004461	NYL2-N141/93-2104	BFV 2W 14" 50PSI SR NO 60PSI
BV2W16FD6LNRXXX	A7F30003357	NYL2-C160/92-210-P	BFV 2W 16" 150PSI DA NC 60PSI POS
BV2W16FD6LNXXXX	A7F30003351	NYL2-C160/92-210	BFV 2W 16" 150PSI DA 60PSI
BV2W16FD6LNYXXX	A7F30003353	NYL2-C160/92-210-SC	BFV 2W 16" 150PSI DA 60PSI 120V
BV2W16FD6LNZXXX	A7F30003354	NYL2-C160/92-210-S4C	BFV 2W 16" 150PSI DA 60PSI 24V
BV2W16FE2LNXXHX	A7F30063460	NYL2-C160/70-1300H	BFV 2W 16" 150PSI 120VAC 2 POS HTR
BV2W16FEMLNXXHX	A7F30073614	NYL2-C160/70-1300SVH	BFV 2W 16" 150PSI NC 120VAC MOD HTR
BV2W16FS6LCQXXX	A7F30004323	NYL2-C160/93-2554-P	BFV 2W 16" 150PSI SR NC 60PSI POS
BV2W16FS6LCVXXX	A7F30004319	NYL2-C160/93-2554-SC	BFV 2W 16" 150PSI SR NC 60PSI 120V
BV2W16FS6LCWXXX	A7F30004320	NYL2-C160/93-2554-S4C	BFV 2W 16" 150PSI SR NC 60PSI 24V
BV2W16FS6LCXXXX	A7F30004317	NYL2-C160/93-2554	BFV 2W 16" 150PSI SR NC 60PSI
BV2W16FS6LOQXXX	A7F30004491	NYL2-N160/93-2554-P	BFV 2W 16" 150PSI SR NO 60PSI POS
BV2W16FS6LOVXXX	A7F30004487	NYL2-N160/93-2554-SC	BFV 2W 16" 150PSI SR NO 60PSI 120V
BV2W16FS6LOWXXX	A7F30004488	NYL2-N160/93-2554-S4C	BFV 2W 16" 150PSI SR NO 60PSI 24V
BV2W16FS6LOXXXX	A7F30004485	NYL2-N160/93-2554	BFV 2W 16" 150PSI SR NO 60PSI
BV2W16UD6LNRXXX	A7F30003349	NYL2-C161/92-160-P	BFV 2W 16" 50PSI DA NC 60PSI POS
BV2W16UD6LNXXXX	A7F30003343	NYL2-C161/92-160	BFV 2W 16" 50PSI DA 60PSI
BV2W16UD6LNYXXX	A7F30003345	NYL2-C161/92-160-SC	BFV 2W 16" 50PSI DA 60PSI 120V
BV2W16UD6LNZXXX	A7F30003346	NYL2-C161/92-160-S4C	BFV 2W 16" 50PSI DA 60PSI 24V
BV2W16UE2LNXXHX	A7F30001916	NYL2-C161/70-0651H	BFV 2W 16" 50PSI 120VAC 2 POS HTR
BV2W16UE2LNXXXX	A7F30001909	NYL2-C161/70-0651	BFV 2W 16" 50PSI 120VAC 2 POS
BV2W16UEMLNXXHX	A7F30001996	NYL2-C161/70-0651SVH	BFV 2W 16" 50PSI NC 120VAC MOD HTR
BV2W16US6LCQXXX	A7F30004315	NYL2-C161/93-2104-P	BFV 2W 16" 50PSI SR NC 60PSI POS
BV2W16US6LCVXXX	A7F30004311	NYL2-C161/93-2104-SC	BFV 2W 16" 50PSI SR NC 60PSI 120V
BV2W16US6LCWXXX	A7F30004312	NYL2-C161/93-2104-S4C	BFV 2W 16" 50PSI SR NC 60PSI 24V

Unrestricted

BV2W16US6LCXXXX	A7F30004309	NYL2-C161/93-2104	BFV 2W 16" 50PSI SR NC 60PSI
BV2W16US6LOQXXX	A7F30004483	NYL2-N161/93-2104-P	BFV 2W 16" 50PSI SR NO 60PSI POS
BV2W16US6LOVXXX	A7F30004479	NYL2-N161/93-2104-SC	BFV 2W 16" 50PSI SR NO 60PSI 120V
BV2W16US6LOWXXX	A7F30004480	NYL2-N161/93-2104-S4C	BFV 2W 16" 50PSI SR NO 60PSI 24V
BV2W16US6LOXXXX	A7F30004477	NYL2-N161/93-2104	BFV 2W 16" 50PSI SR NO 60PSI
BV2W18FEMLNXXHX	A7F30077280	NYL2-C180/70-1300SVH	BFV 2W 18" 150PSI NC 120VAC MOD HTR
BV2W25FD6LNRXXX	A7F30003221	NYL2-C025/92-063-P	BFV 2W 2.5" 175PSI DA NC 60PSI POS
BV2W25FD6LNXXXX	A7F30003215	NYL2-C025/92-063	BFV 2W 2.5" 175PSI DA 60PSI
BV2W25FD6LNYXXX	A7F30003217	NYL2-C025/92-063-SC	BFV 2W 2.5" 175PSI DA 60PSI 120V
BV2W25FD6LNZXXX	A7F30003218	NYL2-C025/92-063-S4C	BFV 2W 2.5" 175PSI DA 60PSI 24V
BV2W25FE2LNXXHX	A7F30077124	NYL2-C025/70-0061H	BFV 2W 2.5" 175PSI 120VAC 2 POS HTR
BV2W25FE2LNXXXX	A7F30077123	NYL2-C025/70-0061	BFV 2W 2.5" 175PSI 120VAC 2 POS
BV2W25FEMLNXXHX	A7F30077125	NYL2-C025/70-0061SVH	BFV 2W 2.5" 175PSI NC 120VAC MOD HTR
BV2W25FS6LCQXXX	A7F30004187	NYL2-C025/93-834-P	BFV 2W 2.5" 175PSI SR NC 60PSI POS
BV2W25FS6LCVXXX	A7F30004183	NYL2-C025/93-834-SC	BFV 2W 2.5" 175PSI SR NC 60PSI 120V
BV2W25FS6LCWXXX	A7F30004184	NYL2-C025/93-834-S4C	BFV 2W 2.5" 175PSI SR NC 60PSI 24V
BV2W25FS6LCXXXX	A7F30004181	NYL2-C025/93-834	BFV 2W 2.5" 175PSI SR NC 60PSI
BV2W25FS6LOQXXX	A7F30004355	NYL2-N025/93-834-P	BFV 2W 2.5" 175PSI SR NO 60PSI POS
BV2W25FS6LOVXXX	A7F30004351	NYL2-N025/93-834-SC	BFV 2W 2.5" 175PSI SR NO 60PSI 120V
BV2W25FS6LOWXXX	A7F30004352	NYL2-N025/93-834-S4C	BFV 2W 2.5" 175PSI SR NO 60PSI 24V
BV2W25FS6LOXXXX	A7F30004349	NYL2-N025/93-834	BFV 2W 2.5" 175PSI SR NO 60PSI
BV2W25UG1LCXXXX	A7F30005165	NYL2-C025/GCA221.1U	BFV 2W 2.5" 175PSI SR NC 120VAC 2 POS
BV2W25UG1LOXXXX	A7F30005216	NYL2-N025/GCA221.1U	BFV 2W 2.5" 175PSI SR NO 120VAC 2 POS
BV2W25UG2LCXAXX	A7F30005164	NYL2-C025/GCA126.1U	BFV 2W 2.5" 175PSI SR NC 24VAC 2 POS SW
BV2W25UG2LCXXXX	A7F30005163	NYL2-C025/GCA121.1U	BFV 2W 2.5" 175PSI SR NC 24VAC 2 POS
BV2W25UG2LOXAXX	A7F30005215	NYL2-N025/GCA126.1U	BFV 2W 2.5" 175PSI SR NO 24VAC 2 POS SW
BV2W25UG2LOXXXX	A7F30005214	NYL2-N025/GCA121.1U	BFV 2W 2.5" 175PSI SR NO 24VAC 2 POS
BV2W25UG4LCXXXX	A7F30005171	NYL2-C025/GCA161.1U	BFV 2W 2.5" 175PSI SR NC 24VAC 0-10DC
BV2W25UG4LOXXXX	A7F30005218	NYL2-N025/GCA161.1U	BFV 2W 2.5" 175PSI SR NO 24VAC 0-10DC
BV2W25UG5LCXXXX	A7F30005173	NYL2-C025/GCA151.1U	BFV 2W 2.5" 175PSI SR NC 24VAC 4-20mA
BV2W25UG5LOXXXX	A7F30005220	NYL2-N025/GCA151.1U	BFV 2W 2.5" 175PSI SR NO 24VAC 4-20mA
BV2W25UG6LNXXXX	A7F30005162	NYL2-C025/GBB131.1U	BFV 2W 2.5" 175PSI 24VAC TRI
BV2W25UG7LNXXXX	A7F30005167	NYL2-C025/GBB161.1U	BFV 2W 2.5" 175PSI 24VAC 0-10DC
BV2W25UG8LNXXXX	A7F30005169	NYL2-C025/GBB151.1U	BFV 2W 2.5" 175PSI 24VAC 4-20mA
BV3W02FD6LARXXX	A7F30003443	NYL3-1020/92-063-P	BFV 3WA 2" 175PSI DA NC 60PSI POS
BV3W02FD6LAXXXX	A7F30003437	NYL3-1020/92-063	BFV 3WA 2" 175PSI DA 60PSI
BV3W02FD6LAYXXX	A7F30003439	NYL3-1020/92-063-SC	BFV 3WA 2" 175PSI DA 60PSI 120V
BV3W02FD6LAZXXX	A7F30003440	NYL3-1020/92-063-S4C	BFV 3WA 2" 175PSI DA 60PSI 24V
BV3W02FD6LBRXXX	A7F30003627	NYL3-8020/92-063-P	BFV 3WB 2" 175PSI DA NC 60PSI POS
BV3W02FD6LBXXXX	A7F30003621	NYL3-8020/92-063	BFV 3WB 2" 175PSI DA 60PSI
BV3W02FD6LBYXXX	A7F30003623	NYL3-8020/92-063-S	BFV 3WB 2" 175PSI DA 60PSI 120V
BV3W02FD6LBZXXX	A7F30003624	NYL3-8020/92-063-S4C	BFV 3WB 2" 175PSI DA 60PSI 24V
BV3W02FD6LCRXXX	A7F30003811	NYL3-2020/92-063-P	BFV 3WC 2" 175PSI DA NC 60PSI POS
BV3W02FD6LCXXXX	A7F30003805	NYL3-2020/92-063	BFV 3WC 2" 175PSI DA 60PSI
BV3W02FD6LCYXXX	A7F30003807	NYL3-2020/92-063-S	BFV 3WC 2" 175PSI DA 60PSI 120V
BV3W02FD6LCZXXX	A7F30003808	NYL3-2020/92-063-S4C	BFV 3WC 2" 175PSI DA 60PSI 24V
BV3W02FD6LDRXXX	A7F30003995	NYL3-7020/92-063-P	BFV 3WD 2" 175PSI DA NC 60PSI POS
BV3W02FD6LDXXXX	A7F30003989	NYL3-7020/92-063	BFV 3WD 2" 175PSI DA 60PSI
BV3W02FD6LDYXXX	A7F30003991	NYL3-7020/92-063-S	BFV 3WD 2" 175PSI DA 60PSI 120V
BV3W02FD6LDZXXX	A7F30003992	NYL3-7020/92-063-S4C	BFV 3WD 2" 175PSI DA 60PSI 24V
BV3W02FE2LAXXHX	A7F30002344	NYL3-1020/70-0061H	BFV 3WA 2" 175PSI 120VAC 2 POS HTR
BV3W02FE2LAXXHX	A7F30077155	NYL3-1020/70-0061H	BFV 3WA 2" 175PSI 120VAC 2 POS HTR

Unrestricted

BV3W02FE2LAXXXX	A7F30002343	NYL3-1020/70-0061	BFV 3WA 2" 175PSI 120VAC 2 POS
BV3W02FE2LAXXXX	A7F30077154	NYL3-1020/70-0061	BFV 3WA 2" 175PSI 120VAC 2 POS
BV3W02FE2LBXXHX	A7F30002642	NYL3-8020/70-0061H	BFV 3WB 2" 175PSI 120VAC 2 POS HTR
BV3W02FE2LBXXHX	A7F30077173	NYL3-8020/70-0061H	BFV 3WB 2" 175PSI 120VAC 2 POS HTR
BV3W02FE2LBXXXX	A7F30002641	NYL3-8020/70-0061	BFV 3WB 2" 175PSI 120VAC 2 POS
BV3W02FE2LBXXXX	A7F30077172	NYL3-8020/70-0061	BFV 3WB 2" 175PSI 120VAC 2 POS
BV3W02FE2LCXXHX	A7F30002886	NYL3-2020/70-0061H	BFV 3WC 2" 175PSI 120VAC 2 POS HTR
BV3W02FE2LCXXHX	A7F30077191	NYL3-2020/70-0061H	BFV 3WC 2" 175PSI 120VAC 2 POS HTR
BV3W02FE2LCXXXX	A7F30002859	NYL3-2020/70-0061	BFV 3WC 2" 175PSI 120VAC 2 POS
BV3W02FE2LCXXXX	A7F30077190	NYL3-2020/70-0061	BFV 3WC 2" 175PSI 120VAC 2 POS
BV3W02FE2LDXXHX	A7F30003139	NYL3-7020/70-0061H	BFV 3WD 2" 175PSI 120VAC 2 POS HTR
BV3W02FE2LDXXHX	A7F30077209	NYL3-7020/70-0061H	BFV 3WD 2" 175PSI 120VAC 2 POS HTR
BV3W02FE2LDXXXX	A7F30003138	NYL3-7020/70-0061	BFV 3WD 2" 175PSI 120VAC 2 POS
BV3W02FE2LDXXXX	A7F30077208	NYL3-7020/70-0061	BFV 3WD 2" 175PSI 120VAC 2 POS
BV3W02FEMLAXXHX	A7F30077210	NYL3-1020/70-0061SVH	BFV 3WA 2" 175PSI 120VAC MOD HTR
BV3W02FEMLBXXHX	A7F30002643	NYL3-8020/70-0061SVH	BFV 3WB 2" 175PSI 120VAC MOD HTR
BV3W02FEMLCXXHX	A7F30077192	NYL3-2020/70-0061SVH	BFV 3WC 2" 175PSI 120VAC MOD HTR
BV3W02FEMLDXXHX	A7F30003140	NYL3-7020/70-0061SVH	BFV 3WD 2" 175PSI 120VAC MOD HTR
BV3W02FEPLAXXHX	A7F30077156	NYL3-1020/70-0061SVH	BFV 3WA 2" 175PSI 120VAC 4-20 MOD HTR
BV3W02FEPLBXXHX	A7F30077174	NYL3-8020/70-0061SVH	BFV 3WB 2" 175PSI 120VAC 4-20 MOD HTR
BV3W02FEPLCXXHX	A7F30002888	NYL3-2020/70-0061SVH	BFV 3WC 2" 175PSI 120VAC 4-20 MOD HTR
BV3W02FEPLDXXHX	A7F30077210	NYL3-7020/70-0061SVH	BFV 3WD 2" 175PSI 120VAC 4-20 MOD HTR
BV3W02FS6LAQXXX	A7F30004515	NYL3-1020/93-833-P	BFV 3WA 2" 175PSI SR NC 60PSI POS
BV3W02FS6LAVXXX	A7F30004511	NYL3-1020/93-833-SC	BFV 3WA 2" 175PSI SR NC 60PSI 120V
BV3W02FS6LAWXXX	A7F30004512	NYL3-1020/93-833-S4C	BFV 3WA 2" 175PSI SR NC 60PSI 24V
BV3W02FS6LAXXXX	A7F30004509	NYL3-1020/93-833	BFV 3WA 2" 175PSI SR NC 60PSI
BV3W02FS6LBQXXX	A7F30004675	NYL3-8020/93-833-P	BFV 3WB 2" 175PSI SR NC 60PSI POS
BV3W02FS6LBVXXX	A7F30004671	NYL3-8020/93-833-S	BFV 3WB 2" 175PSI SR NC 60PSI 120V
BV3W02FS6LBWXXX	A7F30004672	NYL3-8020/93-833-S4C	BFV 3WB 2" 175PSI SR NC 60PSI 24V
BV3W02FS6LBXXXX	A7F30004669	NYL3-8020/93-833	BFV 3WB 2" 175PSI SR NC 60PSI
BV3W02FS6LCQXXX	A7F30004835	NYL3-2020/93-833-P	BFV 3WC 2" 175PSI SR NC 60PSI POS
BV3W02FS6LCVXXX	A7F30004831	NYL3-2020/93-833-S	BFV 3WC 2" 175PSI SR NC 60PSI 120V
BV3W02FS6LCWXXX	A7F30004832	NYL3-2020/93-833-S4C	BFV 3WC 2" 175PSI SR NC 60PSI 24V
BV3W02FS6LCXXXX	A7F30004829	NYL3-2020/93-833	BFV 3WC 2" 175PSI SR NC 60PSI
BV3W02FS6LDQXXX	A7F30004995	NYL3-7020/93-833-P	BFV 3WD 2" 175PSI SR NC 60PSI POS
BV3W02FS6LDVXXX	A7F30004991	NYL3-7020/93-833-S	BFV 3WD 2" 175PSI SR NC 60PSI 120V
BV3W02FS6LDWXXX	A7F30004992	NYL3-7020/93-833-S4C	BFV 3WD 2" 175PSI SR NC 60PSI 24V
BV3W02FS6LDXXXX	A7F30004989	NYL3-7020/93-833	BFV 3WD 2" 175PSI SR NC 60PSI
BV3W02UG2LAXXXX	A7F30005239	NYL3-1020/GCA121.1U	BFV 3WA 2" 175PSI SR 24VAC 2 POS
BV3W02UG2LBXXXX	A7F30005294	NYL3-8020/GCA121.1U	BFV 3WB 2" 175PSI SR 24VAC 2 POS
BV3W02UG2LCXXXX	A7F30005348	NYL3-2020/GBB-131.1U	BFV 3WC 2" 175PSI 24VAC TRI
BV3W02UG2LDXXXX	A7F30005403	NYL3-7020/GBB-131.1U	BFV 3WD 2" 175PSI 24VAC TRI
BV3W02UG4LAXXXX	A7F30005247	NYL3-1020/GCA161.1U	BFV 3WA 2" 175PSI SR 24VAC 0-10DC
BV3W02UG4LBXXXX	A7F30005302	NYL3-8020/GCA161.1U	BFV 3WB 2" 175PSI SR 24VAC 0-10DC
BV3W02UG4LCXXXX	A7F30005357	NYL3-2020/GCA161.1U	BFV 3WC 2" 175PSI SR 24VAC 0-10DC
BV3W02UG4LDXXXX	A7F30005412	NYL3-7020/GCA161.1U	BFV 3WD 2" 175PSI SR 24VAC 0-10DC
BV3W02UG5LAXXXX	A7F30005249	NYL3-1020/GCA151.1U	BFV 3WA 2" 175PSI SR 24VAC 4-20mA
BV3W02UG5LBXXXX	A7F30005304	NYL3-8020/GCA151.1U	BFV 3WB 2" 175PSI SR 24VAC 4-20mA
BV3W02UG5LCXXXX	A7F30005359	NYL3-2020/GCA151.1U	BFV 3WC 2" 175PSI SR 24VAC 4-20mA
BV3W02UG5LDXXXX	A7F30005414	NYL3-7020/GCA151.1U	BFV 3WD 2" 175PSI SR 24VAC 4-20mA
BV3W02UG6LAXXXX	A7F30005238	NYL3-1020/GBB131.1U	BFV 3WA 2" 175PSI 24VAC TRI
BV3W02UG6LBXXXX	A7F30005293	NYL3-8020/GBB131.1U	BFV 3WB 2" 175PSI 24VAC TRI

Unrestricted

BV3W02UG7LAXXXX	A7F30005243	NYL3-1020/GBB161.1U	BFV 3WA 2" 175PSI 24VAC 0-10DC
BV3W02UG7LBXXXX	A7F30005298	NYL3-8020/GBB161.1U	BFV 3WB 2" 175PSI 24VAC 0-10DC
BV3W02UG7LCXXXX	A7F30005353	NYL3-2020/GBB161.1U	BFV 3WC 2" 175PSI 24VAC 0-10DC
BV3W02UG7LDXXXX	A7F30005408	NYL3-7020/GBB161.1U	BFV 3WD 2" 175PSI 24VAC 0-10DC
BV3W02UG8LAXXXX	A7F30005245	NYL3-1020/GBB151.1U	BFV 3WA 2" 175PSI 24VAC 4-20mA
BV3W02UG8LBXXXX	A7F30005300	NYL3-8020/GBB151.1U	BFV 3WB 2" 175PSI 24VAC 4-20mA
BV3W02UG8LCXXXX	A7F30005355	NYL3-2020/GBB-151.1U	BFV 3WC 2" 175PSI 24VAC 4-20mA
BV3W02UG8LDXXXX	A7F30005410	NYL3-7020/GBB-151.1U	BFV 3WD 2" 175PSI 24VAC 4-20mA
BV3W03FD6LARXXX	A7F30003459	NYL3-1030/92-083-P	BFV 3WA 3" 175PSI DA NC 60PSI POS
BV3W03FD6LAXXXX	A7F30003453	NYL3-1030/92-083	BFV 3WA 3" 175PSI DA 60PSI
BV3W03FD6LAYXXX	A7F30003455	NYL3-1030/92-083-SC	BFV 3WA 3" 175PSI DA 60PSI 120V
BV3W03FD6LAZXXX	A7F30003456	NYL3-1030/92-083-S4C	BFV 3WA 3" 175PSI DA 60PSI 24V
BV3W03FD6LBRXXX	A7F30003643	NYL3-8030/92-083-P	BFV 3WB 3" 175PSI DA NC 60PSI POS
BV3W03FD6LBXXXX	A7F30003637	NYL3-8030/92-083	BFV 3WB 3" 175PSI DA 60PSI
BV3W03FD6LBYXXX	A7F30003639	NYL3-8030/92-083-S	BFV 3WB 3" 175PSI DA 60PSI 120V
BV3W03FD6LBZXXX	A7F30003640	NYL3-8030/92-083-S4C	BFV 3WB 3" 175PSI DA 60PSI 24V
BV3W03FD6LCRXXX	A7F30003827	NYL3-2030/92-083-P	BFV 3WC 3" 175PSI DA NC 60PSI POS
BV3W03FD6LCXXXX	A7F30003821	NYL3-2030/92-083	BFV 3WC 3" 175PSI DA 60PSI
BV3W03FD6LCYXXX	A7F30003823	NYL3-2030/92-083-S	BFV 3WC 3" 175PSI DA 60PSI 120V
BV3W03FD6LCZXXX	A7F30003824	NYL3-2030/92-083-S4C	BFV 3WC 3" 175PSI DA 60PSI 24V
BV3W03FD6LDRXXX	A7F30004011	NYL3-7030/92-083-P	BFV 3WD 3" 175PSI DA NC 60PSI POS
BV3W03FD6LDXXXX	A7F30004005	NYL3-7030/92-083	BFV 3WD 3" 175PSI DA 60PSI
BV3W03FD6LDYXXX	A7F30004007	NYL3-7030/92-083-S	BFV 3WD 3" 175PSI DA 60PSI 120V
BV3W03FD6LDZXXX	A7F30004008	NYL3-7030/92-083-S4C	BFV 3WD 3" 175PSI DA 60PSI 24V
BV3W03FE2LAXXHX	A7F30002370	NYL3-1030/70-0061H	BFV 3WA 3" 175PSI 120VAC 2 POS HTR
BV3W03FE2LAXXHX	A7F30077161	NYL3-1030/70-0061H	BFV 3WA 3" 175PSI 120VAC 2 POS HTR
BV3W03FE2LAXXXX	A7F30002349	NYL3-1030/70-0061	BFV 3WA 3" 175PSI 120VAC 2 POS
BV3W03FE2LAXXXX	A7F30077160	NYL3-1030/70-0061	BFV 3WA 3" 175PSI 120VAC 2 POS
BV3W03FE2LBXXHX	A7F30002648	NYL3-8030/70-0061H	BFV 3WB 3" 175PSI 120VAC 2 POS HTR
BV3W03FE2LBXXHX	A7F30077179	NYL3-8030/70-0061H	BFV 3WB 3" 175PSI 120VAC 2 POS HTR
BV3W03FE2LCXXHX	A7F30002898	NYL3-2030/70-0061H	BFV 3WC 3" 175PSI 120VAC 2 POS HTR
BV3W03FE2LCXXHX	A7F30077197	NYL3-2030/70-0061H	BFV 3WC 3" 175PSI 120VAC 2 POS HTR
BV3W03FE2LCXXXX	A7F30002897	NYL3-2030/70-0061	BFV 3WC 3" 175PSI 120VAC 2 POS
BV3W03FE2LCXXXX	A7F30077196	NYL3-2030/70-0061	BFV 3WC 3" 175PSI 120VAC 2 POS
BV3W03FE2LDXXHX	A7F30003145	NYL3-7030/70-0061H	BFV 3WD 3" 175PSI 120VAC 2 POS HTR
BV3W03FE2LDXXHX	A7F30077215	NYL3-7030/70-0061H	BFV 3WD 3" 175PSI 120VAC 2 POS HTR
BV3W03FE2LDXXXX	A7F30003144	NYL3-7030/70-0061	BFV 3WD 3" 175PSI 120VAC 2 POS
BV3W03FE2LDXXXX	A7F30077214	NYL3-7030/70-0061	BFV 3WD 3" 175PSI 120VAC 2 POS
BV3W03FEMLAXXHX	A7F30077216	NYL3-1030/70-0061SVH	BFV 3WA 3" 175PSI 120VAC MOD HTR
BV3W03FEMLBXXHX	A7F30002649	NYL3-8030/70-0061SVH	BFV 3WB 3" 175PSI 120VAC MOD HTR
BV3W03FEMLCXXHX	A7F30077198	NYL3-2030/70-0061SVH	BFV 3WC 3" 175PSI 120VAC MOD HTR
BV3W03FEMLDXXHX	A7F30003146	NYL3-7030/70-0061SVH	BFV 3WD 3" 175PSI 120VAC MOD HTR
BV3W03FEPLAXXHX	A7F30077162	NYL3-1030/70-0061SVH	BFV 3WA 3" 175PSI 120VAC 4-20 MOD HTR
BV3W03FEPLBXXHX	A7F30077180	NYL3-8030/70-0061SVH	BFV 3WB 3" 175PSI 120VAC 4-20 MOD HTR
BV3W03FEPLCXXHX	A7F30002899	NYL3-2030/70-0061SVH	BFV 3WC 3" 175PSI 120VAC 4-20 MOD HTR
BV3W03FEPLDXXHX	A7F30077216	NYL3-7030/70-0061SVH	BFV 3WD 3" 175PSI 120VAC 4-20 MOD HTR
BV3W03FS6LAQXXX	A7F30004531	NYL3-1030/93-1182-P	BFV 3WA 3" 175PSI SR NC 60PSI POS
BV3W03FS6LAVXXX	A7F30004527	NYL3-1030/93-1182-S	BFV 3WA 3" 175PSI SR NC 60PSI 120V
BV3W03FS6LAWXXX	A7F30004528	NYL3-1030/93-1182-S4C	BFV 3WA 3" 175PSI SR NC 60PSI 24V
BV3W03FS6LAXXXX	A7F30004525	NYL3-1030/93-1182	BFV 3WA 3" 175PSI SR NC 60PSI
BV3W03FS6LBQXXX	A7F30004691	NYL3-8030/93-1182-P	BFV 3WB 3" 175PSI SR NC 60PSI POS
BV3W03FS6LBVXXX	A7F30004687	NYL3-8030/93-1182-S	BFV 3WB 3" 175PSI SR NC 60PSI 120V

Unrestricted

BV3W03FS6LBWXXX	A7F30004688	NYL3-8030/93-1182-S4C	BFV 3WB 3" 175PSI SR NC 60PSI 24V
BV3W03FS6LBXXXX	A7F30004685	NYL3-8030/93-1182	BFV 3WB 3" 175PSI SR NC 60PSI
BV3W03FS6LCQXXX	A7F30004851	NYL3-2030/93-1182-P	BFV 3WC 3" 175PSI SR NC 60PSI POS
BV3W03FS6LCVXXX	A7F30004847	NYL3-2030/93-1182-S	BFV 3WC 3" 175PSI SR NC 60PSI 120V
BV3W03FS6LCWXXX	A7F30004848	NYL3-2030/93-1182-S4C	BFV 3WC 3" 175PSI SR NC 60PSI 24V
BV3W03FS6LCXXXX	A7F30004845	NYL3-2030/93-1182	BFV 3WC 3" 175PSI SR NC 60PSI
BV3W03FS6LDQXXX	A7F30005011	NYL3-7030/93-1182-P	BFV 3WD 3" 175PSI SR NC 60PSI POS
BV3W03FS6LDVXXX	A7F30005007	NYL3-7030/93-1182-S	BFV 3WD 3" 175PSI SR NC 60PSI 120V
BV3W03FS6LDWXXX	A7F30005008	NYL3-7030/93-1182-S4C	BFV 3WD 3" 175PSI SR NC 60PSI 24V
BV3W03FS6LDXXXX	A7F30005005	NYL3-7030/93-1182	BFV 3WD 3" 175PSI SR NC 60PSI
BV3W03UG4LAXXXX	A7F30005269	NYL3-1030/GCA161.1U-D	BFV 3WA 3" 175PSI SR 24VAC 0-10DC
BV3W03UG4LBXXXX	A7F30005324	NYL3-8030/GCA161.1U-D	BFV 3WB 3" 175PSI SR 24VAC 0-10DC
BV3W03UG4LCXXXX	A7F30005379	NYL3-2030/GCA161.1U-D	BFV 3WC 3" 175PSI SR 24VAC 0-10DC
BV3W03UG4LDXXXX	A7F30005434	NYL3-7030/GCA161.1U-D	BFV 3WD 3" 175PSI SR 24VAC 0-10DC
BV3W03UG5LAXXXX	A7F30005271	NYL3-1030/GCA151.1U-D	BFV 3WA 3" 175PSI SR 24VAC 4-20mA
BV3W03UG5LBXXXX	A7F30005326	NYL3-8030/GCA151.1U-D	BFV 3WB 3" 175PSI SR 24VAC 4-20mA
BV3W03UG5LCXXXX	A7F30005381	NYL3-2030/GCA151.1U-D	BFV 3WC 3" 175PSI SR 24VAC 4-20mA
BV3W03UG5LDXXXX	A7F30005436	NYL3-7030/GCA151.1U-D	BFV 3WD 3" 175PSI SR 24VAC 4-20mA
BV3W03UG6LAXXXX	A7F30005262	NYL3-1030/GIB131.1U	BFV 3WA 3" 175PSI 24VAC TRI
BV3W03UG6LBXXXX	A7F30005317	NYL3-8030/GIB131.1U	BFV 3WB 3" 175PSI 24VAC TRI
BV3W03UG6LCXXXX	A7F30005372	NYL3-2030/GIB131.1U	BFV 3WC 3" 175PSI 24VAC TRI
BV3W03UG6LDXXXX	A7F30005427	NYL3-7030/GIB131.1U	BFV 3WD 3" 175PSI 24VAC TRI
BV3W03UG7LAXXXX	A7F30005267	NYL3-1030/GIB161.1U	BFV 3WA 3" 175PSI 24VAC 0-10DC
BV3W03UG7LBXXXX	A7F30005322	NYL3-8030/GIB-161.1U	BFV 3WB 3" 175PSI 24VAC 0-10DC
BV3W03UG7LCXXXX	A7F30005377	NYL3-2030/GIB-161.1U	BFV 3WC 3" 175PSI 24VAC 0-10DC
BV3W03UG7LDXXXX	A7F30005432	NYL3-7030/GIB-161.1U	BFV 3WD 3" 175PSI 24VAC 0-10DC
BV3W04FD6LARXXX	A7F30003475	NYL3-1040/92-092-P	BFV 3WA 4" 175PSI DA NC 60PSI POS
BV3W04FD6LAXXXX	A7F30003469	NYL3-1040/92-092	BFV 3WA 4" 175PSI DA 60PSI
BV3W04FD6LAYXXX	A7F30003471	NYL3-1040/92-092-S	BFV 3WA 4" 175PSI DA 60PSI 120V
BV3W04FD6LAZXXX	A7F30003472	NYL3-1040/92-092-S4C	BFV 3WA 4" 175PSI DA 60PSI 24V
BV3W04FD6LBRXXX	A7F30003659	NYL3-8040/92-092-P	BFV 3WB 4" 175PSI DA NC 60PSI POS
BV3W04FD6LBXXXX	A7F30003653	NYL3-8040/92-092	BFV 3WB 4" 175PSI DA 60PSI
BV3W04FD6LBXXXX	A7F30003655	NYL3-8040/92-092-S	BFV 3WB 4" 175PSI DA 60PSI 120V
BV3W04FD6LBZXXX	A7F30003656	NYL3-8040/92-092-S4C	BFV 3WB 4" 175PSI DA 60PSI 24V
BV3W04FD6LCRXXX	A7F30003843	NYL3-2040/92-092-P	BFV 3WC 4" 175PSI DA NC 60PSI POS
BV3W04FD6LCXXXX	A7F30003837	NYL3-2040/92-092	BFV 3WC 4" 175PSI DA 60PSI
BV3W04FD6LCYXXX	A7F30003839	NYL3-2040/92-092-S	BFV 3WC 4" 175PSI DA 60PSI 120V
BV3W04FD6LCZXXX	A7F30003840	NYL3-2040/92-092-S4C	BFV 3WC 4" 175PSI DA 60PSI 24V
BV3W04FD6LDRXXX	A7F30004027	NYL3-7040/92-092-P	BFV 3WD 4" 175PSI DA NC 60PSI POS
BV3W04FD6LDXXXX	A7F30004021	NYL3-7040/92-092	BFV 3WD 4" 175PSI DA 60PSI
BV3W04FD6LDYXXX	A7F30004023	NYL3-7040/92-092-S	BFV 3WD 4" 175PSI DA 60PSI 120V
BV3W04FD6LDZXXX	A7F30004024	NYL3-7040/92-092-S4C	BFV 3WD 4" 175PSI DA 60PSI 24V
BV3W04FE2LAXXHX	A7F30002378	NYL3-1040/70-0061H	BFV 3WA 4" 175PSI 120VAC 2 POS HTR
BV3W04FE2LAXXHX	A7F30077167	NYL3-1040/70-0061H	BFV 3WA 4" 175PSI 120VAC 2 POS HTR
BV3W04FE2LAXXXX	A7F30002377	NYL3-1040/70-0061	BFV 3WA 4" 175PSI 120VAC 2 POS
BV3W04FE2LAXXXX	A7F30077166	NYL3-1040/70-0061	BFV 3WA 4" 175PSI 120VAC 2 POS
BV3W04FE2LBXXHX	A7F30002698	NYL3-8040/70-0061H	BFV 3WB 4" 175PSI 120VAC 2 POS HTR
BV3W04FE2LBXXHX	A7F30077185	NYL3-8040/70-0061H	BFV 3WB 4" 175PSI 120VAC 2 POS HTR
BV3W04FE2LBXXXX	A7F30002697	NYL3-8040/70-0061	BFV 3WB 4" 175PSI 120VAC 2 POS
BV3W04FE2LBXXXX	A7F30077184	NYL3-8040/70-0061	BFV 3WB 4" 175PSI 120VAC 2 POS
BV3W04FE2LCXXHX	A7F30002906	NYL3-2040/70-0061H	BFV 3WC 4" 175PSI 120VAC 2 POS HTR
BV3W04FE2LCXXHX	A7F30077203	NYL3-2040/70-0061H	BFV 3WC 4" 175PSI 120VAC 2 POS HTR

Unrestricted

BV3W04FE2LCXXXX	A7F30002905	NYL3-2040/70-0061	BFV 3WC 4" 175PSI 120VAC 2 POS
BV3W04FE2LCXXXX	A7F30077202	NYL3-2040/70-0061	BFV 3WC 4" 175PSI 120VAC 2 POS
BV3W04FE2LDXXHX	A7F30003151	NYL3-7040/70-0061H	BFV 3WD 4" 175PSI 120VAC 2 POS HTR
BV3W04FE2LDXXHX	A7F30077221	NYL3-7040/70-0061H	BFV 3WD 4" 175PSI 120VAC 2 POS HTR
BV3W04FE2LDXXXX	A7F30003150	NYL3-7040/70-0061	BFV 3WD 4" 175PSI 120VAC 2 POS
BV3W04FE2LDXXXX	A7F30077220	NYL3-7040/70-0061	BFV 3WD 4" 175PSI 120VAC 2 POS
BV3W04FEMLAXXHX	A7F30077168	NYL3-1040/70-0061SVH	BFV 3WA 4" 175PSI 120VAC MOD HTR
BV3W04FEMLBXXHX	A7F30002699	NYL3-8040/70-0061SVH	BFV 3WB 4" 175PSI 120VAC MOD HTR
BV3W04FEMLCXXHX	A7F30077204	NYL3-2040/70-0061SVH	BFV 3WC 4" 175PSI 120VAC MOD HTR
BV3W04FEMLDXXHX	A7F30003152	NYL3-7040/70-0061SVH	BFV 3WD 4" 175PSI 120VAC MOD HTR
BV3W04FEPLAXXHX	A7F30077168	NYL3-1040/70-0061SVH	BFV 3WA 4" 175PSI 120VAC 4-20 MOD HTR
BV3W04FEPLBXXHX	A7F30077186	NYL3-8040/70-0061SVH	BFV 3WB 4" 175PSI 120VAC 4-20 MOD HTR
BV3W04FEPLCXXHX	A7F30077204	NYL3-2040/70-0061SVH	BFV 3WC 4" 175PSI 120VAC 4-20 MOD HTR
BV3W04FEPLDXXHX	A7F30077222	NYL3-7040/70-0061SVH	BFV 3WD 4" 175PSI 120VAC 4-20 MOD HTR
BV3W04FS6LAQXXX	A7F30004547	NYL3-1040/93-1183-P	BFV 3WA 4" 175PSI SR NC 60PSI POS
BV3W04FS6LAVXXX	A7F30004543	NYL3-1040/93-1183-S	BFV 3WA 4" 175PSI SR NC 60PSI 120V
BV3W04FS6LAWXXX	A7F30004544	NYL3-1040/93-1183-S4C	BFV 3WA 4" 175PSI SR NC 60PSI 24V
BV3W04FS6LAXXXX	A7F30004541	NYL3-1040/93-1183	BFV 3WA 4" 175PSI SR NC 60PSI
BV3W04FS6LBQXXX	A7F30004707	NYL3-8040/93-1183-P	BFV 3WB 4" 175PSI SR NC 60PSI POS
BV3W04FS6LBVXXX	A7F30004703	NYL3-8040/93-1183-S	BFV 3WB 4" 175PSI SR NC 60PSI 120V
BV3W04FS6LBWXXX	A7F30004704	NYL3-8040/93-1183-S4C	BFV 3WB 4" 175PSI SR NC 60PSI 24V
BV3W04FS6LBXXXX	A7F30004701	NYL3-8040/93-1183	BFV 3WB 4" 175PSI SR NC 60PSI
BV3W04FS6LCQXXX	A7F30004867	NYL3-2040/93-1183-P	BFV 3WC 4" 175PSI SR NC 60PSI POS
BV3W04FS6LCVXXX	A7F30004863	NYL3-2040/93-1183-S	BFV 3WC 4" 175PSI SR NC 60PSI 120V
BV3W04FS6LCWXXX	A7F30004864	NYL3-2040/93-1183-S4C	BFV 3WC 4" 175PSI SR NC 60PSI 24V
BV3W04FS6LCXXXX	A7F30004861	NYL3-2040/93-1183	BFV 3WC 4" 175PSI SR NC 60PSI
BV3W04FS6LDQXXX	A7F30005027	NYL3-7040/93-1183-P	BFV 3WD 4" 175PSI SR NC 60PSI POS
BV3W04FS6LDVXXX	A7F30005023	NYL3-7040/93-1183-S	BFV 3WD 4" 175PSI SR NC 60PSI 120V
BV3W04FS6LDWXXX	A7F30005024	NYL3-7040/93-1183-S4C	BFV 3WD 4" 175PSI SR NC 60PSI 24V
BV3W04FS6LDXXXX	A7F30005021	NYL3-7040/93-1183	BFV 3WD 4" 175PSI SR NC 60PSI
BV3W04UD6LARXXX	A7F30003467	NYL3-1041/92-083-P	BFV 3WA 4" 50PSI DA NC 60PSI POS
BV3W04UD6LAXXXX	A7F30003461	NYL3-1041/92-083	BFV 3WA 4" 50PSI DA 60PSI
BV3W04UD6LAYXXX	A7F30003463	NYL3-1041/92-083-S	BFV 3WA 4" 50PSI DA 60PSI 120V
BV3W04UD6LAZXXX	A7F30003464	NYL3-1041/92-083-S4C	BFV 3WA 4" 50PSI DA 60PSI 24V
BV3W04UD6LBRXXX	A7F30003651	NYL3-8041/92-083-P	BFV 3WB 4" 50PSI DA NC 60PSI POS
BV3W04UD6LBXXXX	A7F30003645	NYL3-8041/92-083	BFV 3WB 4" 50PSI DA 60PSI
BV3W04UD6LBYXXX	A7F30003647	NYL3-8041/92-083-S	BFV 3WB 4" 50PSI DA 60PSI 120V
BV3W04UD6LBZXXX	A7F30003648	NYL3-8041/92-083-S4C	BFV 3WB 4" 50PSI DA 60PSI 24V
BV3W04UD6LCRXXX	A7F30003835	NYL3-2041/92-083-P	BFV 3WC 4" 50PSI DA NC 60PSI POS
BV3W04UD6LCXXXX	A7F30003829	NYL3-2041/92-083	BFV 3WC 4" 50PSI DA 60PSI
BV3W04UD6LCYXXX	A7F30003831	NYL3-2041/92-083-S	BFV 3WC 4" 50PSI DA 60PSI 120V
BV3W04UD6LCZXXX	A7F30003832	NYL3-2041/92-083-S4C	BFV 3WC 4" 50PSI DA 60PSI 24V
BV3W04UD6LDRXXX	A7F30004019	NYL3-7041/92-083-P	BFV 3WD 4" 50PSI DA NC 60PSI POS
BV3W04UD6LDXXXX	A7F30004013	NYL3-7041/92-083	BFV 3WD 4" 50PSI DA 60PSI
BV3W04UD6LDYXXX	A7F30004015	NYL3-7041/92-083-S	BFV 3WD 4" 50PSI DA 60PSI 120V
BV3W04UD6LDZXXX	A7F30004016	NYL3-7041/92-083-S4C	BFV 3WD 4" 50PSI DA 60PSI 24V
BV3W04UE2LAXXHX	A7F30077164	NYL3-1041/70-0061H	BFV 3WA 4" 50PSI 120VAC 2 POS HTR
BV3W04UE2LAXXXX	A7F30077163	NYL3-1041/70-0061	BFV 3WA 4" 50PSI 120VAC 2 POS
BV3W04UE2LBXXHX	A7F30002670	NYL3-8041/70-0061H	BFV 3WB 4" 50PSI 120VAC 2 POS HTR
BV3W04UE2LBXXHX	A7F30077182	NYL3-8041/70-0061H	BFV 3WB 4" 50PSI 120VAC 2 POS HTR
BV3W04UE2LBXXXX	A7F30002660	NYL3-8041/70-0061	BFV 3WB 4" 50PSI 120VAC 2 POS
BV3W04UE2LBXXXX	A7F30077181	NYL3-8041/70-0061	BFV 3WB 4" 50PSI 120VAC 2 POS

Unrestricted

BV3W04UE2LCXXHX	A7F30002903	NYL3-2041/70-0061H	BFV 3WC 4" 50PSI 120VAC 2 POS HTR
BV3W04UE2LCXXHX	A7F30077200	NYL3-2041/70-0061H	BFV 3WC 4" 50PSI 120VAC 2 POS HTR
BV3W04UE2LCXXXX	A7F30002902	NYL3-2041/70-0061	BFV 3WC 4" 50PSI 120VAC 2 POS
BV3W04UE2LCXXXX	A7F30077199	NYL3-2041/70-0061	BFV 3WC 4" 50PSI 120VAC 2 POS
BV3W04UE2LDXXHX	A7F30003148	NYL3-7041/70-0061H	BFV 3WD 4" 50PSI 120VAC 2 POS HTR
BV3W04UE2LDXXHX	A7F30077218	NYL3-7041/70-0061H	BFV 3WD 4" 50PSI 120VAC 2 POS HTR
BV3W04UE2LDXXXX	A7F30003147	NYL3-7041/70-0061	BFV 3WD 4" 50PSI 120VAC 2 POS
BV3W04UE2LDXXXX	A7F30077217	NYL3-7041/70-0061	BFV 3WD 4" 50PSI 120VAC 2 POS
BV3W04UEMLAXXXH	A7F30077165	NYL3-1041/70-0061SVH	BFV 3WA 4" 50PSI 120VAC MOD HTR
BV3W04UEMLBXXHX	A7F30002696	NYL3-8041/70-0061SVH	BFV 3WB 4" 50PSI 120VAC MOD HTR
BV3W04UEMLCXXHX	A7F30077201	NYL3-2041/70-0061SVH	BFV 3WC 4" 50PSI 120VAC MOD HTR
BV3W04UEMLDXXHX	A7F30003149	NYL3-7041/70-0061SVH	BFV 3WD 4" 50PSI 120VAC MOD HTR
BV3W04UEPLBXXHX	A7F30077183	NYL3-8041/70-0061SVH	BFV 3WB 4" 50PSI 120VAC 4-20 MOD HTR
BV3W04UEPLCXXHX	A7F30002904	NYL3-2041/70-0061SVH	BFV 3WC 4" 50PSI 120VAC 4-20 MOD HTR
BV3W04UEPLDXXHX	A7F30077219	NYL3-7041/70-0061SVH	BFV 3WD 4" 50PSI 120VAC 4-20 MOD HTR
BV3W04UG2LAXXXX	A7F30005274	NYL3-1041/GCA121.1U-D	BFV 3WA 4" 50PSI SR 24VAC 2 POS
BV3W04UG2LBXXXX	A7F30005329	NYL3-8041/GCA121.1U-D	BFV 3WB 4" 50PSI SR 24VAC 2 POS
BV3W04UG2LCXXXX	A7F30005384	NYL3-2041/GCA121.1U-D	BFV 3WC 4" 50PSI SR 24VAC 2 POS
BV3W04UG2LDXAXX	A7F30005442	NYL3-7041/GCA226.1U-D	BFV 3WD 4" 50PSI SR 24VAC 2 POS SW
BV3W04UG2LDXXXX	A7F30005439	NYL3-7041/GCA121.1U-D	BFV 3WD 4" 50PSI SR 24VAC 2 POS
BV3W04UG4LAXXXX	A7F30005280	NYL3-1041/GCA161.1U-D	BFV 3WA 4" 50PSI SR 24VAC 0-10DC
BV3W04UG4LBXXXX	A7F30005335	NYL3-8041/GCA161.1U-D	BFV 3WB 4" 50PSI SR 24VAC 0-10DC
BV3W04UG4LCXXXX	A7F30005390	NYL3-2041/GCA161.1U-D	BFV 3WC 4" 50PSI SR 24VAC 0-10DC
BV3W04UG4LDXXXX	A7F30005445	NYL3-7041/GCA161.1U-D	BFV 3WD 4" 50PSI SR 24VAC 0-10DC
BV3W04UG5LAXXXX	A7F30005282	NYL3-1041/GCA151.1U-D	BFV 3WA 4" 50PSI SR 24VAC 4-20mA
BV3W04UG5LBXXXX	A7F30005337	NYL3-8041/GCA151.1U-D	BFV 3WB 4" 50PSI SR 24VAC 4-20mA
BV3W04UG5LCXXXX	A7F30005392	NYL3-2041/GCA151.1U-D	BFV 3WC 4" 50PSI SR 24VAC 4-20mA
BV3W04UG5LDXXXX	A7F30005447	NYL3-7041/GCA151.1U-D	BFV 3WD 4" 50PSI SR 24VAC 4-20mA
BV3W04UG6LAXXXX	A7F30005273	NYL3-1041/GIB131.1U	BFV 3WA 4" 50PSI 24VAC TRI
BV3W04UG6LBXXXX	A7F30005328	NYL3-8041/GIB131.1U	BFV 3WB 4" 50PSI 24VAC TRI
BV3W04UG6LCXXXX	A7F30005383	NYL3-2041/GIB131.1U	BFV 3WC 4" 50PSI 24VAC TRI
BV3W04UG6LDXXXX	A7F30005438	NYL3-7041/GIB131.1U	BFV 3WD 4" 50PSI 24VAC TRI
BV3W04UG7LAXXXX	A7F30005278	NYL3-1041/GIB161.1U	BFV 3WA 4" 50PSI 24VAC 0-10DC
BV3W04UG7LBXXXX	A7F30005333	NYL3-8041/GIB-161.1U	BFV 3WB 4" 50PSI 24VAC 0-10DC
BV3W04UG7LCXXXX	A7F30005388	NYL3-2041/GIB-161.1U	BFV 3WC 4" 50PSI 24VAC 0-10DC
BV3W04UG7LDXXXX	A7F30005443	NYL3-7041/GIB-161.1U	BFV 3WD 4" 50PSI 24VAC 0-10DC
BV3W04US6LAQXXX	A7F30004539	NYL3-1041/93-1182-P	BFV 3WA 4" 50PSI SR NC 60PSI POS
BV3W04US6LAVXXX	A7F30004535	NYL3-1041/93-1182-S	BFV 3WA 4" 50PSI SR NC 60PSI 120V
BV3W04US6LAWXXX	A7F30004536	NYL3-1041/93-1182-S4C	BFV 3WA 4" 50PSI SR NC 60PSI 24V
BV3W04US6LAXXXX	A7F30004693	NYL3-1041/93-1182	BFV 3WB 4" 50PSI SR NC 60PSI
BV3W04US6LBQXXX	A7F30004699	NYL3-8041/93-1182-P	BFV 3WB 4" 50PSI SR NC 60PSI POS
BV3W04US6LBVXXX	A7F30004695	NYL3-8041/93-1182-S	BFV 3WB 4" 50PSI SR NC 60PSI 120V
BV3W04US6LBWXXX	A7F30004696	NYL3-8041/93-1182-S4C	BFV 3WB 4" 50PSI SR NC 60PSI 24V
BV3W04US6LCQXXX	A7F30004859	NYL3-2041/93-1182-P	BFV 3WC 4" 50PSI SR NC 60PSI POS
BV3W04US6LCVXXX	A7F30004855	NYL3-2041/93-1182-S	BFV 3WC 4" 50PSI SR NC 60PSI 120V
BV3W04US6LCWXXX	A7F30004856	NYL3-2041/93-1182-S4C	BFV 3WC 4" 50PSI SR NC 60PSI 24V
BV3W04US6LCXXXX	A7F30004853	NYL3-2041/93-1182	BFV 3WC 4" 50PSI SR NC 60PSI
BV3W04US6LDQXXX	A7F30005019	NYL3-7041/93-1182-P	BFV 3WD 4" 50PSI SR NC 60PSI POS
BV3W04US6LDVXXX	A7F30005015	NYL3-7041/93-1182-S	BFV 3WD 4" 50PSI SR NC 60PSI 120V
BV3W04US6LDWXXX	A7F30005016	NYL3-7041/93-1182-S4C	BFV 3WD 4" 50PSI SR NC 60PSI 24V
BV3W04US6LDXXXX	A7F30005013	NYL3-7041/93-1182	BFV 3WD 4" 50PSI SR NC 60PSI
BV3W05FD6LARXXX	A7F30003491	NYL3-1050/92-118-P	BFV 3WA 5" 175PSI DA NC 60PSI POS

Unrestricted

BV3W05FD6LAXXXX	A7F30003485	NYL3-1050/92-118	BFV 3WA 5" 175PSI DA 60PSI
BV3W05FD6LAYXXX	A7F30003487	NYL3-1050/92-118-S	BFV 3WA 5" 175PSI DA 60PSI 120V
BV3W05FD6LAZXXX	A7F30003488	NYL3-1050/92-118-S4C	BFV 3WA 5" 175PSI DA 60PSI 24V
BV3W05FD6LBRXXX	A7F30003675	NYL3-8050/92-118-P	BFV 3WB 5" 175PSI DA NC 60PSI POS
BV3W05FD6LBXXXX	A7F30003669	NYL3-8050/92-118	BFV 3WB 5" 175PSI DA 60PSI
BV3W05FD6LBYXXX	A7F30003671	NYL3-8050/92-118-S	BFV 3WB 5" 175PSI DA 60PSI 120V
BV3W05FD6LBZXXX	A7F30003672	NYL3-8050/92-118-S4C	BFV 3WB 5" 175PSI DA 60PSI 24V
BV3W05FD6LCRXXX	A7F30003859	NYL3-2050/92-118-P	BFV 3WC 5" 175PSI DA NC 60PSI POS
BV3W05FD6LCXXXX	A7F30003853	NYL3-2050/92-118	BFV 3WC 5" 175PSI DA 60PSI
BV3W05FD6LCYXXX	A7F30003855	NYL3-2050/92-118-S	BFV 3WC 5" 175PSI DA 60PSI 120V
BV3W05FD6LCZXXX	A7F30003856	NYL3-2050/92-118-S4C	BFV 3WC 5" 175PSI DA 60PSI 24V
BV3W05FD6LDRXXX	A7F30004043	NYL3-7050/92-118-P	BFV 3WD 5" 175PSI DA NC 60PSI POS
BV3W05FD6LDXXXX	A7F30004037	NYL3-7050/92-118	BFV 3WD 5" 175PSI DA 60PSI
BV3W05FD6LDYXXX	A7F30004039	NYL3-7050/92-118-S	BFV 3WD 5" 175PSI DA 60PSI 120V
BV3W05FD6LDZXXX	A7F30004040	NYL3-7050/92-118-S4C	BFV 3WD 5" 175PSI DA 60PSI 24V
BV3W05FE2LAXHHX	A7F30002408	NYL3-1050/70-0121H	BFV 3WA 5" 175PSI 120VAC 2 POS HTR
BV3W05FE2LAXXXX	A7F30002403	NYL3-1050/70-0121	BFV 3WA 5" 175PSI 120VAC 2 POS
BV3W05FE2LBXHHX	A7F30002708	NYL3-8050/70-0121H	BFV 3WB 5" 175PSI 120VAC 2 POS HTR
BV3W05FE2LBXXXX	A7F30002707	NYL3-8050/70-0121	BFV 3WB 5" 175PSI 120VAC 2 POS
BV3W05FE2LCXHHX	A7F30002913	NYL3-2050/70-0121H	BFV 3WC 5" 175PSI 120VAC 2 POS HTR
BV3W05FE2LCXXXX	A7F30002912	NYL3-2050/70-0121	BFV 3WC 5" 175PSI 120VAC 2 POS
BV3W05FE2LDXHHX	A7F30003157	NYL3-7050/70-0121H	BFV 3WD 5" 175PSI 120VAC 2 POS HTR
BV3W05FE2LDXXXX	A7F30003156	NYL3-7050/70-0121	BFV 3WD 5" 175PSI 120VAC 2 POS
BV3W05FEMLAXHHX	A7F30002409	NYL3-1050/70-0121SVH	BFV 3WA 5" 175PSI 120VAC MOD HTR
BV3W05FEMLBXHHX	A7F30002709	NYL3-8050/70-0121SVH	BFV 3WB 5" 175PSI 120VAC MOD HTR
BV3W05FEMLCXHHX	A7F30002914	NYL3-2050/70-0121SVH	BFV 3WC 5" 175PSI 120VAC MOD HTR
BV3W05FEMLDXHHX	A7F30003158	NYL3-7050/70-0121SVH	BFV 3WD 5" 175PSI 120VAC MOD HTR
BV3W05FS6LAQXXX	A7F30004563	NYL3-1050/93-1602-P	BFV 3WA 5" 175PSI SR NC 60PSI POS
BV3W05FS6LAVXXX	A7F30004559	NYL3-1050/93-1602-S	BFV 3WA 5" 175PSI SR NC 60PSI 120V
BV3W05FS6LAWXXX	A7F30004560	NYL3-1050/93-1602-S4C	BFV 3WA 5" 175PSI SR NC 60PSI 24V
BV3W05FS6LAXXXX	A7F30004557	NYL3-1050/93-1602	BFV 3WA 5" 175PSI SR NC 60PSI
BV3W05FS6LBQXXX	A7F30004723	NYL3-8050/93-1602-P	BFV 3WB 5" 175PSI SR NC 60PSI POS
BV3W05FS6LBVXXX	A7F30004719	NYL3-8050/93-1602-S	BFV 3WB 5" 175PSI SR NC 60PSI 120V
BV3W05FS6LBWXXX	A7F30004720	NYL3-8050/93-1602-S4C	BFV 3WB 5" 175PSI SR NC 60PSI 24V
BV3W05FS6LBXXXX	A7F30004717	NYL3-8050/93-1602	BFV 3WB 5" 175PSI SR NC 60PSI
BV3W05FS6LCQXXX	A7F30004883	NYL3-2050/93-1602-P	BFV 3WC 5" 175PSI SR NC 60PSI POS
BV3W05FS6LCVXXX	A7F30004879	NYL3-2050/93-1602-S	BFV 3WC 5" 175PSI SR NC 60PSI 120V
BV3W05FS6LCWXXX	A7F30004880	NYL3-2050/93-1602-S4C	BFV 3WC 5" 175PSI SR NC 60PSI 24V
BV3W05FS6LCXXXX	A7F30004877	NYL3-2050/93-1602	BFV 3WC 5" 175PSI SR NC 60PSI
BV3W05FS6LDQXXX	A7F30005043	NYL3-7050/93-1602-P	BFV 3WD 5" 175PSI SR NC 60PSI POS
BV3W05FS6LDVXXX	A7F30005039	NYL3-7050/93-1602-S	BFV 3WD 5" 175PSI SR NC 60PSI 120V
BV3W05FS6LDWXXX	A7F30005040	NYL3-7050/93-1602-S4C	BFV 3WD 5" 175PSI SR NC 60PSI 24V
BV3W05FS6LDXXXX	A7F30005037	NYL3-7050/93-1602	BFV 3WD 5" 175PSI SR NC 60PSI
BV3W05UD6LARXXX	A7F30003483	NYL3-1051/92-092-P	BFV 3WA 5" 50PSI DA NC 60PSI POS
BV3W05UD6LAXXXX	A7F30003477	NYL3-1051/92-092	BFV 3WA 5" 50PSI DA 60PSI
BV3W05UD6LAZXXX	A7F30003480	NYL3-1051/92-092-S4C	BFV 3WA 5" 50PSI DA 60PSI 24V
BV3W05UD6LBRXXX	A7F30003667	NYL3-8051/92-092-P	BFV 3WB 5" 50PSI DA NC 60PSI POS
BV3W05UD6LBXXXX	A7F30003661	NYL3-8051/92-092	BFV 3WB 5" 50PSI DA 60PSI
BV3W05UD6LBYXXX	A7F30003663	NYL3-8051/92-092-S	BFV 3WB 5" 50PSI DA 60PSI 120V
BV3W05UD6LBZXXX	A7F30003664	NYL3-8051/92-092-S4C	BFV 3WB 5" 50PSI DA 60PSI 24V
BV3W05UD6LCRXXX	A7F30003851	NYL3-2051/92-092-P	BFV 3WC 5" 50PSI DA NC 60PSI POS
BV3W05UD6LCXXXX	A7F30003845	NYL3-2051/92-092	BFV 3WC 5" 50PSI DA 60PSI

Unrestricted

BV3W05UD6LCYXXX	A7F30003847	NYL3-2051/92-092-S	BFV 3WC 5" 50PSI DA 60PSI 120V
BV3W05UD6LCZXXX	A7F30003848	NYL3-2051/92-092-S4C	BFV 3WC 5" 50PSI DA 60PSI 24V
BV3W05UD6LDRXXX	A7F30004035	NYL3-7051/92-092-P	BFV 3WD 5" 50PSI DA NC 60PSI POS
BV3W05UD6LDXXXX	A7F30004029	NYL3-7051/92-092	BFV 3WD 5" 50PSI DA 60PSI
BV3W05UD6LDYXXX	A7F30004031	NYL3-7051/92-092-S	BFV 3WD 5" 50PSI DA 60PSI 120V
BV3W05UD6LDZXXX	A7F30004032	NYL3-7051/92-092-S4C	BFV 3WD 5" 50PSI DA 60PSI 24V
BV3W05UE2LAXXHX	A7F30002395	NYL3-1051/70-0061H	BFV 3WA 5" 50PSI 120VAC 2 POS HTR
BV3W05UE2LAXXHX	A7F30077170	NYL3-1051/70-0061H	BFV 3WA 5" 50PSI 120VAC 2 POS HTR
BV3W05UE2LAXXXX	A7F30002390	NYL3-1051/70-0061	BFV 3WA 5" 50PSI 120VAC 2 POS
BV3W05UE2LAXXXX	A7F30077169	NYL3-1051/70-0061	BFV 3WA 5" 50PSI 120VAC 2 POS
BV3W05UE2LBXXHX	A7F30002705	NYL3-8051/70-0061H	BFV 3WB 5" 50PSI 120VAC 2 POS HTR
BV3W05UE2LBXXHX	A7F30077188	NYL3-8051/70-0061H	BFV 3WB 5" 50PSI 120VAC 2 POS HTR
BV3W05UE2LBXXXX	A7F30002704	NYL3-8051/70-0061	BFV 3WB 5" 50PSI 120VAC 2 POS
BV3W05UE2LBXXXX	A7F30077187	NYL3-8051/70-0061	BFV 3WB 5" 50PSI 120VAC 2 POS
BV3W05UE2LCXXHX	A7F30002909	NYL3-2051/70-0061H	BFV 3WC 5" 50PSI 120VAC 2 POS HTR
BV3W05UE2LCXXHX	A7F30077206	NYL3-2051/70-0061H	BFV 3WC 5" 50PSI 120VAC 2 POS HTR
BV3W05UE2LCXXXX	A7F30002908	NYL3-2051/70-0061	BFV 3WC 5" 50PSI 120VAC 2 POS
BV3W05UE2LCXXXX	A7F30077205	NYL3-2051/70-0061	BFV 3WC 5" 50PSI 120VAC 2 POS
BV3W05UE2LDXXHX	A7F30077224	NYL3-7051/70-0061H	BFV 3WD 5" 50PSI 120VAC 2 POS HTR
BV3W05UE2LDXXXX	A7F30077223	NYL3-7051/70-0061	BFV 3WD 5" 50PSI 120VAC 2 POS
BV3W05UEMLAXXHX	A7F30002396	NYL3-1051/70-0061SVH	BFV 3WA 5" 50PSI 120VAC MOD HTR
BV3W05UEMLBXXHX	A7F30002706	NYL3-8051/70-0061SVH	BFV 3WB 5" 50PSI 120VAC MOD HTR
BV3W05UEMLCXXHX	A7F30002911	NYL3-2051/70-0061SVH	BFV 3WC 5" 50PSI 120VAC MOD HTR
BV3W05UEMLDXXHX	A7F30077225	NYL3-7051/70-0061SVH	BFV 3WD 5" 50PSI 120VAC MOD HTR
BV3W05UEPLAXXHX	A7F30077171	NYL3-1051/70-0061SVH	BFV 3WA 5" 50PSI 120VAC 4-20 MOD HTR
BV3W05UEPLBXXHX	A7F30077189	NYL3-8051/70-0061SVH	BFV 3WB 5" 50PSI 120VAC 4-20 MOD HTR
BV3W05UEPLCXXHX	A7F30077207	NYL3-2051/70-0061SVH	BFV 3WC 5" 50PSI 120VAC 4-20 MOD HTR
BV3W05UG6LAXXXX	A7F30005287	NYL3-1051/GIB131.1U-D	BFV 3WA 5" 50PSI 24VAC TRI
BV3W05UG6LBXXXX	A7F30005342	NYL3-8051/GIB131.1U-D	BFV 3WB 5" 50PSI 24VAC TRI
BV3W05UG6LCXXXX	A7F30005397	NYL3-2051/GIB131.1U-D	BFV 3WC 5" 50PSI 24VAC TRI
BV3W05UG6LDXXXX	A7F30005452	NYL3-7051/GIB131.1U-D	BFV 3WD 5" 50PSI 24VAC TRI
BV3W05UG7LAXXXX	A7F30005288	NYL3-1051/GIB161.1U-D	BFV 3WA 5" 50PSI 24VAC 0-10DC
BV3W05UG7LBXXXX	A7F30005343	NYL3-8051/GIB161.1U-D	BFV 3WB 5" 50PSI 24VAC 0-10DC
BV3W05UG7LCXXXX	A7F30005398	NYL3-2051/GIB161.1U-D	BFV 3WC 5" 50PSI 24VAC 0-10DC
BV3W05UG7LDXXXX	A7F30005453	NYL3-7051/GIB161.1U-D	BFV 3WD 5" 50PSI 24VAC 0-10DC
BV3W05US6LAQXXX	A7F30004555	NYL3-1051/93-1183-P	BFV 3WA 5" 50PSI SR NC 60PSI POS
BV3W05US6LAVXXX	A7F30004551	NYL3-1051/93-1183-S	BFV 3WA 5" 50PSI SR NC 60PSI 120V
BV3W05US6LAWXXX	A7F30004552	NYL3-1051/93-1183-S4C	BFV 3WA 5" 50PSI SR NC 60PSI 24V
BV3W05US6LAXXXX	A7F30004549	NYL3-1051/93-1183	BFV 3WA 5" 50PSI SR NC 60PSI
BV3W05US6LBQXXX	A7F30004715	NYL3-8051/93-1183-P	BFV 3WB 5" 50PSI SR NC 60PSI POS
BV3W05US6LBVXXX	A7F30004711	NYL3-8051/93-1183-S	BFV 3WB 5" 50PSI SR NC 60PSI 120V
BV3W05US6LBWXXX	A7F30004712	NYL3-8051/93-1183-S4C	BFV 3WB 5" 50PSI SR NC 60PSI 24V
BV3W05US6LBXXXX	A7F30004709	NYL3-8051/93-1183	BFV 3WB 5" 50PSI SR NC 60PSI
BV3W05US6LCQXXX	A7F30004875	NYL3-2051/93-1183-P	BFV 3WC 5" 50PSI SR NC 60PSI POS
BV3W05US6LCVXXX	A7F30004871	NYL3-2051/93-1183-S	BFV 3WC 5" 50PSI SR NC 60PSI 120V
BV3W05US6LCWXXX	A7F30004872	NYL3-2051/93-1183-S4C	BFV 3WC 5" 50PSI SR NC 60PSI 24V
BV3W05US6LCXXXX	A7F30004869	NYL3-2051/93-1183	BFV 3WC 5" 50PSI SR NC 60PSI
BV3W05US6LDQXXX	A7F30005035	NYL3-7051/93-1183-P	BFV 3WD 5" 50PSI SR NC 60PSI POS
BV3W05US6LDVXXX	A7F30005031	NYL3-7051/93-1183-S	BFV 3WD 5" 50PSI SR NC 60PSI 120V
BV3W05US6LDWXXX	A7F30005032	NYL3-7051/93-1183-S4C	BFV 3WD 5" 50PSI SR NC 60PSI 24V
BV3W05US6LDXXXX	A7F30005029	NYL3-7051/93-1183	BFV 3WD 5" 50PSI SR NC 60PSI
BV3W06FD6LARXXX	A7F30003507	NYL3-1060/92-118-P	BFV 3WA 6" 175PSI DA NC 60PSI POS

Unrestricted

BV3W06FD6LAXXXX	A7F30003501	NYL3-1060/92-118	BFV 3WA 6" 175PSI DA 60PSI
BV3W06FD6LAYXXX	A7F30003503	NYL3-1060/92-118-S	BFV 3WA 6" 175PSI DA 60PSI 120V
BV3W06FD6LAZXXX	A7F30003504	NYL3-1060/92-118-S4C	BFV 3WA 6" 175PSI DA 60PSI 24V
BV3W06FD6LBRXXX	A7F30003691	NYL3-8060/92-118-P	BFV 3WB 6" 175PSI DA NC 60PSI POS
BV3W06FD6LBXXXX	A7F30003685	NYL3-8060/92-118	BFV 3WB 6" 175PSI DA 60PSI
BV3W06FD6LBYXXX	A7F30003687	NYL3-8060/92-118-S	BFV 3WB 6" 175PSI DA 60PSI 120V
BV3W06FD6LBZXXX	A7F30003688	NYL3-8060/92-118-S4C	BFV 3WB 6" 175PSI DA 60PSI 24V
BV3W06FD6LCRXXX	A7F30003875	NYL3-2060/92-118-P	BFV 3WC 6" 175PSI DA NC 60PSI POS
BV3W06FD6LCXXXX	A7F30003869	NYL3-2060/92-118	BFV 3WC 6" 175PSI DA 60PSI
BV3W06FD6LCYXXX	A7F30003871	NYL3-2060/92-118-S	BFV 3WC 6" 175PSI DA 60PSI 120V
BV3W06FD6LCZXXX	A7F30003872	NYL3-2060/92-118-S4C	BFV 3WC 6" 175PSI DA 60PSI 24V
BV3W06FD6LDRXXX	A7F30004059	NYL3-7060/92-118-P	BFV 3WD 6" 175PSI DA NC 60PSI POS
BV3W06FD6LDXXXX	A7F30004053	NYL3-7060/92-118	BFV 3WD 6" 175PSI DA 60PSI
BV3W06FD6LDYXXX	A7F30004055	NYL3-7060/92-118-S	BFV 3WD 6" 175PSI DA 60PSI 120V
BV3W06FD6LDZXXX	A7F30004056	NYL3-7060/92-118-S4C	BFV 3WD 6" 175PSI DA 60PSI 24V
BV3W06FE2LAXXHX	A7F30002444	NYL3-1060/70-0121H	BFV 3WA 6" 175PSI 120VAC 2 POS HTR
BV3W06FE2LAXXXX	A7F30002442	NYL3-1060/70-0121	BFV 3WA 6" 175PSI 120VAC 2 POS
BV3W06FE2LBXXHX	A7F30002777	NYL3-8060/70-0121H	BFV 3WB 6" 175PSI 120VAC 2 POS HTR
BV3W06FE2LBXXXX	A7F30002776	NYL3-8060/70-0121	BFV 3WB 6" 175PSI 120VAC 2 POS
BV3W06FE2LCXXHX	A7F30002919	NYL3-2060/70-0121H	BFV 3WC 6" 175PSI 120VAC 2 POS HTR
BV3W06FE2LCXXXX	A7F30002918	NYL3-2060/70-0121	BFV 3WC 6" 175PSI 120VAC 2 POS
BV3W06FE2LDXXHX	A7F30003163	NYL3-7060/70-0121H	BFV 3WD 6" 175PSI 120VAC 2 POS HTR
BV3W06FE2LDXXXX	A7F30003162	NYL3-7060/70-0121	BFV 3WD 6" 175PSI 120VAC 2 POS
BV3W06FEMLAXXHX	A7F30002447	NYL3-1060/70-0121SVH	BFV 3WA 6" 175PSI 120VAC MOD HTR
BV3W06FEMLBXXHX	A7F30002778	NYL3-8060/70-0121SVH	BFV 3WB 6" 175PSI 120VAC MOD HTR
BV3W06FEMLCXXHX	A7F30002961	NYL3-2060/70-0121SVH	BFV 3WC 6" 175PSI 120VAC MOD HTR
BV3W06FEMLDXXHX	A7F30003164	NYL3-7060/70-0121SVH	BFV 3WD 6" 175PSI 120VAC MOD HTR
BV3W06FS6LAQXXX	A7F30004579	NYL3-1060/93-1603-P	BFV 3WA 6" 175PSI SR NC 60PSI POS
BV3W06FS6LAVXXX	A7F30004575	NYL3-1060/93-1603-S	BFV 3WA 6" 175PSI SR NC 60PSI 120V
BV3W06FS6LAWXXX	A7F30004576	NYL3-1060/93-1603-S4C	BFV 3WA 6" 175PSI SR NC 60PSI 24V
BV3W06FS6LAXXXX	A7F30004573	NYL3-1060/93-1603	BFV 3WA 6" 175PSI SR NC 60PSI
BV3W06FS6LBQXXX	A7F30004739	NYL3-8060/93-1603-P	BFV 3WB 6" 175PSI SR NC 60PSI POS
BV3W06FS6LBVXXX	A7F30004735	NYL3-8060/93-1603-S	BFV 3WB 6" 175PSI SR NC 60PSI 120V
BV3W06FS6LBWXXX	A7F30004736	NYL3-8060/93-1603-S4C	BFV 3WB 6" 175PSI SR NC 60PSI 24V
BV3W06FS6LBXXXX	A7F30004733	NYL3-8060/93-1603	BFV 3WB 6" 175PSI SR NC 60PSI
BV3W06FS6LCQXXX	A7F30004899	NYL3-2060/93-1603-P	BFV 3WC 6" 175PSI SR NC 60PSI POS
BV3W06FS6LCVXXX	A7F30004895	NYL3-2060/93-1603-S	BFV 3WC 6" 175PSI SR NC 60PSI 120V
BV3W06FS6LCWXXX	A7F30004896	NYL3-2060/93-1603-S4C	BFV 3WC 6" 175PSI SR NC 60PSI 24V
BV3W06FS6LCXXXX	A7F30004893	NYL3-2060/93-1603	BFV 3WC 6" 175PSI SR NC 60PSI
BV3W06FS6LDQXXX	A7F30005059	NYL3-7060/93-1603-P	BFV 3WD 6" 175PSI SR NC 60PSI POS
BV3W06FS6LDVXXX	A7F30005055	NYL3-7060/93-1603-S	BFV 3WD 6" 175PSI SR NC 60PSI 120V
BV3W06FS6LDWXXX	A7F30005056	NYL3-7060/93-1603-S4C	BFV 3WD 6" 175PSI SR NC 60PSI 24V
BV3W06FS6LDXXXX	A7F30005053	NYL3-7060/93-1603	BFV 3WD 6" 175PSI SR NC 60PSI
BV3W06UD6LARXXX	A7F30003499	NYL3-1061/92-092-P	BFV 3WA 6" 50PSI DA NC 60PSI POS
BV3W06UD6LAXXXX	A7F30003493	NYL3-1061/92-092	BFV 3WA 6" 50PSI DA 60PSI
BV3W06UD6LAYXXX	A7F30003495	NYL3-1061/92-092-S	BFV 3WA 6" 50PSI DA 60PSI 120V
BV3W06UD6LAZXXX	A7F30003496	NYL3-1061/92-092-S4C	BFV 3WA 6" 50PSI DA 60PSI 24V
BV3W06UD6LBRXXX	A7F30003683	NYL3-8061/92-092-P	BFV 3WB 6" 50PSI DA NC 60PSI POS
BV3W06UD6LBXXXX	A7F30003677	NYL3-8061/92-092	BFV 3WB 6" 50PSI DA 60PSI
BV3W06UD6LBYXXX	A7F30003679	NYL3-8061/92-092-S	BFV 3WB 6" 50PSI DA 60PSI 120V
BV3W06UD6LBZXXX	A7F30003680	NYL3-8061/92-092-S4C	BFV 3WB 6" 50PSI DA 60PSI 24V
BV3W06UD6LCRXXX	A7F30003867	NYL3-2061/92-092-P	BFV 3WC 6" 50PSI DA NC 60PSI POS

Unrestricted

BV3W06UD6LCXXXX	A7F30003861	NYL3-2061/92-092	BFV 3WC 6" 50PSI DA 60PSI
BV3W06UD6LCYXXX	A7F30003863	NYL3-2061/92-092-S	BFV 3WC 6" 50PSI DA 60PSI 120V
BV3W06UD6LCZXXX	A7F30003864	NYL3-2061/92-092-S4C	BFV 3WC 6" 50PSI DA 60PSI 24V
BV3W06UD6LDRXXX	A7F30004051	NYL3-7061/92-092-P	BFV 3WD 6" 50PSI DA NC 60PSI POS
BV3W06UD6LDXXXX	A7F30004045	NYL3-7061/92-092	BFV 3WD 6" 50PSI DA 60PSI
BV3W06UD6LDYXXX	A7F30004047	NYL3-7061/92-092-S	BFV 3WD 6" 50PSI DA 60PSI 120V
BV3W06UD6LDZXXX	A7F30004048	NYL3-7061/92-092-S4C	BFV 3WD 6" 50PSI DA 60PSI 24V
BV3W06UE2LAXHHX	A7F30002440	NYL3-1061/70-0121H	BFV 3WA 6" 50PSI 120VAC 2 POS HTR
BV3W06UE2LAXXXX	A7F30002439	NYL3-1061/70-0121	BFV 3WA 6" 50PSI 120VAC 2 POS
BV3W06UE2LBXHHX	A7F30002774	NYL3-8061/70-0121H	BFV 3WB 6" 50PSI 120VAC 2 POS HTR
BV3W06UE2LBXXXX	A7F30002773	NYL3-8061/70-0121	BFV 3WB 6" 50PSI 120VAC 2 POS
BV3W06UE2LCXHHX	A7F30002916	NYL3-2061/70-0121H	BFV 3WC 6" 50PSI 120VAC 2 POS HTR
BV3W06UE2LCXXXX	A7F30002915	NYL3-2061/70-0121	BFV 3WC 6" 50PSI 120VAC 2 POS
BV3W06UE2LDXHHX	A7F30003160	NYL3-7061/70-0121H	BFV 3WD 6" 50PSI 120VAC 2 POS HTR
BV3W06UE2LDXXXX	A7F30003159	NYL3-7061/70-0121	BFV 3WD 6" 50PSI 120VAC 2 POS
BV3W06UEMLAXHHX	A7F30002441	NYL3-1061/70-0121SVH	BFV 3WA 6" 50PSI 120VAC MOD HTR
BV3W06UEMLBXHHX	A7F30002775	NYL3-8061/70-0121SVH	BFV 3WB 6" 50PSI 120VAC MOD HTR
BV3W06UEMLCXXHHX	A7F30002917	NYL3-2061/70-0121SVH	BFV 3WC 6" 50PSI 120VAC MOD HTR
BV3W06UEMLDXXHHX	A7F30003161	NYL3-7061/70-0121SVH	BFV 3WD 6" 50PSI 120VAC MOD HTR
BV3W06UG6LAXXXX	A7F30005290	NYL3-1061/GIB131.1U-D	BFV 3WA 6" 50PSI 24VAC TRI
BV3W06UG6LBXXXX	A7F30005345	NYL3-8061/GIB131.1U-D	BFV 3WB 6" 50PSI 24VAC TRI
BV3W06UG6LCXXXX	A7F30005400	NYL3-2061/GIB131.1U-D	BFV 3WC 6" 50PSI 24VAC TRI
BV3W06UG6LDXXXX	A7F30005455	NYL3-7061/GIB131.1U-D	BFV 3WD 6" 50PSI 24VAC TRI
BV3W06UG7LAXXXX	A7F30005291	NYL3-1061/GIB161.1U-D	BFV 3WA 6" 50PSI 24VAC 0-10DC
BV3W06UG7LBXXXX	A7F30005346	NYL3-8061/GIB161.1U-D	BFV 3WB 6" 50PSI 24VAC 0-10DC
BV3W06UG7LCXXXX	A7F30005401	NYL3-2061/GIB161.1U-D	BFV 3WC 6" 50PSI 24VAC 0-10DC
BV3W06UG7LDXXXX	A7F30005456	NYL3-7061/GIB161.1U-D	BFV 3WD 6" 50PSI 24VAC 0-10DC
BV3W06US6LAQXXX	A7F30004571	NYL3-1061/93-1273-P	BFV 3WA 6" 50PSI SR NC 60PSI POS
BV3W06US6LAVXXX	A7F30004567	NYL3-1061/93-1273-S	BFV 3WA 6" 50PSI SR NC 60PSI 120V
BV3W06US6LAWXXX	A7F30004568	NYL3-1061/93-1273-S4C	BFV 3WA 6" 50PSI SR NC 60PSI 24V
BV3W06US6LAXXXX	A7F30004565	NYL3-1061/93-1273	BFV 3WA 6" 50PSI SR NC 60PSI
BV3W06US6LBQXXX	A7F30004731	NYL3-8061/93-1273-P	BFV 3WB 6" 50PSI SR NC 60PSI POS
BV3W06US6LBVXXX	A7F30004727	NYL3-8061/93-1273-S	BFV 3WB 6" 50PSI SR NC 60PSI 120V
BV3W06US6LBWXXX	A7F30004728	NYL3-8061/93-1273-S4C	BFV 3WB 6" 50PSI SR NC 60PSI 24V
BV3W06US6LBXXXX	A7F30004725	NYL3-8061/93-1273	BFV 3WB 6" 50PSI SR NC 60PSI
BV3W06US6LCQXXX	A7F30004891	NYL3-2061/93-1273-P	BFV 3WC 6" 50PSI SR NC 60PSI POS
BV3W06US6LCVXXX	A7F30004887	NYL3-2061/93-1273-S	BFV 3WC 6" 50PSI SR NC 60PSI 120V
BV3W06US6LCWXXX	A7F30004888	NYL3-2061/93-1273-S4C	BFV 3WC 6" 50PSI SR NC 60PSI 24V
BV3W06US6LCXXXX	A7F30004885	NYL3-2061/93-1273	BFV 3WC 6" 50PSI SR NC 60PSI
BV3W06US6LDQXXX	A7F30005051	NYL3-7061/93-1273-P	BFV 3WD 6" 50PSI SR NC 60PSI POS
BV3W06US6LDVXXX	A7F30005047	NYL3-7061/93-1273-S	BFV 3WD 6" 50PSI SR NC 60PSI 120V
BV3W06US6LDWXXX	A7F30005048	NYL3-7061/93-1273-S4C	BFV 3WD 6" 50PSI SR NC 60PSI 24V
BV3W06US6LDXXXX	A7F30005045	NYL3-7061/93-1273	BFV 3WD 6" 50PSI SR NC 60PSI
BV3W08FD6LARXXX	A7F30003523	NYL3-1080/92-160-P	BFV 3WA 8" 175PSI DA NC 60PSI POS
BV3W08FD6LAXXXX	A7F30003517	NYL3-1080/92-160	BFV 3WA 8" 175PSI DA 60PSI
BV3W08FD6LAYXXX	A7F30003519	NYL3-1080/92-160-S	BFV 3WA 8" 175PSI DA 60PSI 120V
BV3W08FD6LAZXXX	A7F30003520	NYL3-1080/92-160-S4C	BFV 3WA 8" 175PSI DA 60PSI 24V
BV3W08FD6LBRXXX	A7F30003707	NYL3-8080/92-160-P	BFV 3WB 8" 175PSI DA NC 60PSI POS
BV3W08FD6LBXXXX	A7F30003701	NYL3-8080/92-160	BFV 3WB 8" 175PSI DA 60PSI
BV3W08FD6LBYXXX	A7F30003703	NYL3-8080/92-160-S	BFV 3WB 8" 175PSI DA 60PSI 120V
BV3W08FD6LBZXXX	A7F30003704	NYL3-8080/92-160-S4C	BFV 3WB 8" 175PSI DA 60PSI 24V
BV3W08FD6LCRXXX	A7F30003891	NYL3-2080/92-160-P	BFV 3WC 8" 175PSI DA NC 60PSI POS

Unrestricted

BV3W08FD6LCXXX	A7F30003885	NYL3-2080/92-160	BFV 3WC 8" 175PSI DA 60PSI
BV3W08FD6LCYXXX	A7F30003887	NYL3-2080/92-160-S	BFV 3WC 8" 175PSI DA 60PSI 120V
BV3W08FD6LCZXXX	A7F30003888	NYL3-2080/92-160-S4C	BFV 3WC 8" 175PSI DA 60PSI 24V
BV3W08FD6LDRXXX	A7F30004075	NYL3-7080/92-160-P	BFV 3WD 8" 175PSI DA NC 60PSI POS
BV3W08FD6LDXXXX	A7F30004069	NYL3-7080/92-160	BFV 3WD 8" 175PSI DA 60PSI
BV3W08FD6LDYXXX	A7F30004071	NYL3-7080/92-160-S	BFV 3WD 8" 175PSI DA 60PSI 120V
BV3W08FD6LDZXXX	A7F30004072	NYL3-7080/92-160-S4C	BFV 3WD 8" 175PSI DA 60PSI 24V
BV3W08FE2LAXXXH	A7F30002479	NYL3-1080/70-0201H	BFV 3WA 8" 175PSI 120VAC 2 POS HTR
BV3W08FE2LAXXXX	A7F30002478	NYL3-1080/70-0201	BFV 3WA 8" 175PSI 120VAC 2 POS
BV3W08FE2LBXXHX	A7F30002793	NYL3-8080/70-0201H	BFV 3WB 8" 175PSI 120VAC 2 POS HTR
BV3W08FE2LBXXXX	A7F30002792	NYL3-8080/70-0201	BFV 3WB 8" 175PSI 120VAC 2 POS
BV3W08FE2LCXXHX	A7F30002966	NYL3-2080/70-0201H	BFV 3WC 8" 175PSI 120VAC 2 POS HTR
BV3W08FE2LCXXXX	A7F30002965	NYL3-2080/70-0201	BFV 3WC 8" 175PSI 120VAC 2 POS
BV3W08FE2LDXXHX	A7F30003169	NYL3-7080/70-0201H	BFV 3WD 8" 175PSI 120VAC 2 POS HTR
BV3W08FE2LDXXXX	A7F30003168	NYL3-7080/70-0201	BFV 3WD 8" 175PSI 120VAC 2 POS
BV3W08FEMLAXXXH	A7F30002485	NYL3-1080/70-0201SVH	BFV 3WA 8" 175PSI 120VAC MOD HTR
BV3W08FEMLBXXHX	A7F30002794	NYL3-8080/70-0201SVH	BFV 3WB 8" 175PSI 120VAC MOD HTR
BV3W08FEMLCXXHX	A7F30002967	NYL3-2080/70-0201SVH	BFV 3WC 8" 175PSI 120VAC MOD HTR
BV3W08FEMLDXXHX	A7F30003170	NYL3-7080/70-0201SVH	BFV 3WD 8" 175PSI 120VAC MOD HTR
BV3W08FS6LAQXXX	A7F30004595	NYL3-1080/93-2103-P	BFV 3WA 8" 175PSI SR NC 60PSI POS
BV3W08FS6LAVXXX	A7F30004591	NYL3-1080/93-2103-S	BFV 3WA 8" 175PSI SR NC 60PSI 120V
BV3W08FS6LAWXXX	A7F30004592	NYL3-1080/93-2103-S4C	BFV 3WA 8" 175PSI SR NC 60PSI 24V
BV3W08FS6LAXXXX	A7F30004589	NYL3-1080/93-2103	BFV 3WA 8" 175PSI SR NC 60PSI
BV3W08FS6LBQXXX	A7F30004755	NYL3-8080/93-2103-P	BFV 3WB 8" 175PSI SR NC 60PSI POS
BV3W08FS6LBVXXX	A7F30004751	NYL3-8080/93-2103-S	BFV 3WB 8" 175PSI SR NC 60PSI 120V
BV3W08FS6LBWXXX	A7F30004752	NYL3-8080/93-2103-S4C	BFV 3WB 8" 175PSI SR NC 60PSI 24V
BV3W08FS6LBXXXX	A7F30004749	NYL3-8080/93-2103	BFV 3WB 8" 175PSI SR NC 60PSI
BV3W08FS6LCQXXX	A7F30004915	NYL3-2080/93-2103-P	BFV 3WC 8" 175PSI SR NC 60PSI POS
BV3W08FS6LCVXXX	A7F30004911	NYL3-2080/93-2103-S	BFV 3WC 8" 175PSI SR NC 60PSI 120V
BV3W08FS6LCWXXX	A7F30004912	NYL3-2080/93-2103-S4C	BFV 3WC 8" 175PSI SR NC 60PSI 24V
BV3W08FS6LCXXXX	A7F30004909	NYL3-2080/93-2103	BFV 3WC 8" 175PSI SR NC 60PSI
BV3W08FS6LDQXXX	A7F30005075	NYL3-7080/93-2103-P	BFV 3WD 8" 175PSI SR NC 60PSI POS
BV3W08FS6LDVXXX	A7F30005071	NYL3-7080/93-2103-S	BFV 3WD 8" 175PSI SR NC 60PSI 120V
BV3W08FS6LDWXXX	A7F30005072	NYL3-7080/93-2103-S4C	BFV 3WD 8" 175PSI SR NC 60PSI 24V
BV3W08FS6LDXXXX	A7F30005069	NYL3-7080/93-2103	BFV 3WD 8" 175PSI SR NC 60PSI
BV3W08UD6LARXXX	A7F30003515	NYL3-1081/92-118-P	BFV 3WA 8" 50PSI DA NC 60PSI POS
BV3W08UD6LAXXXX	A7F30003509	NYL3-1081/92-118	BFV 3WA 8" 50PSI DA 60PSI
BV3W08UD6LAYXXX	A7F30003511	NYL3-1081/92-118-S	BFV 3WA 8" 50PSI DA 60PSI 120V
BV3W08UD6LAZXXX	A7F30003512	NYL3-1081/92-118-S4C	BFV 3WA 8" 50PSI DA 60PSI 24V
BV3W08UD6LBRXXX	A7F30003699	NYL3-8081/92-118-P	BFV 3WB 8" 50PSI DA NC 60PSI POS
BV3W08UD6LBXXXX	A7F30003693	NYL3-8081/92-118	BFV 3WB 8" 50PSI DA 60PSI
BV3W08UD6LBVXXX	A7F30003695	NYL3-8081/92-118-S	BFV 3WB 8" 50PSI DA 60PSI 120V
BV3W08UD6LBZXXX	A7F30003696	NYL3-8081/92-118-S4C	BFV 3WB 8" 50PSI DA 60PSI 24V
BV3W08UD6LCRXXX	A7F30003883	NYL3-2081/92-118-P	BFV 3WC 8" 50PSI DA NC 60PSI POS
BV3W08UD6LCXXXX	A7F30003877	NYL3-2081/92-118	BFV 3WC 8" 50PSI DA 60PSI
BV3W08UD6LCYXXX	A7F30003879	NYL3-2081/92-118-S	BFV 3WC 8" 50PSI DA 60PSI 120V
BV3W08UD6LCZXXX	A7F30003880	NYL3-2081/92-118-S4C	BFV 3WC 8" 50PSI DA 60PSI 24V
BV3W08UD6LDRXXX	A7F30004067	NYL3-7081/92-118-P	BFV 3WD 8" 50PSI DA NC 60PSI POS
BV3W08UD6LDXXXX	A7F30004061	NYL3-7081/92-118	BFV 3WD 8" 50PSI DA 60PSI
BV3W08UD6LDYXXX	A7F30004063	NYL3-7081/92-118-S	BFV 3WD 8" 50PSI DA 60PSI 120V
BV3W08UD6LDZXXX	A7F30004064	NYL3-7081/92-118-S4C	BFV 3WD 8" 50PSI DA 60PSI 24V
BV3W08UE2LAXXXH	A7F30002449	NYL3-1081/70-0121H	BFV 3WA 8" 50PSI 120VAC 2 POS HTR

Unrestricted

BV3W08UE2LAXXXX	A7F30002448	NYL3-1081/70-0121	BFV 3WA 8" 50PSI 120VAC 2 POS
BV3W08UE2LBXXHX	A7F30002789	NYL3-8081/70-0121H	BFV 3WB 8" 50PSI 120VAC 2 POS HTR
BV3W08UE2LBXXXX	A7F30002779	NYL3-8081/70-0121	BFV 3WB 8" 50PSI 120VAC 2 POS
BV3W08UE2LCXXHX	A7F30002963	NYL3-2081/70-0121H	BFV 3WC 8" 50PSI 120VAC 2 POS HTR
BV3W08UE2LCXXXX	A7F30002962	NYL3-2081/70-0121	BFV 3WC 8" 50PSI 120VAC 2 POS
BV3W08UE2LDXXHX	A7F30003166	NYL3-7081/70-0121H	BFV 3WD 8" 50PSI 120VAC 2 POS HTR
BV3W08UE2LDXXXX	A7F30003165	NYL3-7081/70-0121	BFV 3WD 8" 50PSI 120VAC 2 POS
BV3W08UEMLAXXXH	A7F30002468	NYL3-1081/70-0121SVH	BFV 3WA 8" 50PSI 120VAC MOD HTR
BV3W08UEMLBXXHX	A7F30002791	NYL3-8081/70-0121SVH	BFV 3WB 8" 50PSI 120VAC MOD HTR
BV3W08UEMLCXXHX	A7F30002964	NYL3-2081/70-0121SVH	BFV 3WC 8" 50PSI 120VAC MOD HTR
BV3W08UEMLDXXHX	A7F30003167	NYL3-7081/70-0121SVH	BFV 3WD 8" 50PSI 120VAC MOD HTR
BV3W08US6LAQXXX	A7F30004587	NYL3-1081/93-1603-P	BFV 3WA 8" 50PSI SR NC 60PSI POS
BV3W08US6LAVXXX	A7F30004583	NYL3-1081/93-1603-S	BFV 3WA 8" 50PSI SR NC 60PSI 120V
BV3W08US6LAWXXX	A7F30004584	NYL3-1081/93-1603-S4C	BFV 3WA 8" 50PSI SR NC 60PSI 24V
BV3W08US6LAXXXX	A7F30004581	NYL3-1081/93-1603	BFV 3WA 8" 50PSI SR NC 60PSI
BV3W08US6LBQXXX	A7F30004747	NYL3-8081/93-1603-P	BFV 3WB 8" 50PSI SR NC 60PSI POS
BV3W08US6LBVXXX	A7F30004743	NYL3-8081/93-1603-S	BFV 3WB 8" 50PSI SR NC 60PSI 120V
BV3W08US6LBWXXX	A7F30004744	NYL3-8081/93-1603-S4C	BFV 3WB 8" 50PSI SR NC 60PSI 24V
BV3W08US6LBXXXX	A7F30004741	NYL3-8081/93-1603	BFV 3WB 8" 50PSI SR NC 60PSI
BV3W08US6LCQXXX	A7F30004907	NYL3-2081/93-1603-P	BFV 3WC 8" 50PSI SR NC 60PSI POS
BV3W08US6LCVXXX	A7F30004903	NYL3-2081/93-1603-S	BFV 3WC 8" 50PSI SR NC 60PSI 120V
BV3W08US6LCWXXX	A7F30004904	NYL3-2081/93-1603-S4C	BFV 3WC 8" 50PSI SR NC 60PSI 24V
BV3W08US6LCXXXX	A7F30004901	NYL3-2081/93-1603	BFV 3WC 8" 50PSI SR NC 60PSI
BV3W08US6LDQXXX	A7F30005067	NYL3-7081/93-1603-P	BFV 3WD 8" 50PSI SR NC 60PSI POS
BV3W08US6LDVXXX	A7F30005063	NYL3-7081/93-1603-S	BFV 3WD 8" 50PSI SR NC 60PSI 120V
BV3W08US6LDWXXX	A7F30005064	NYL3-7081/93-1603-S4C	BFV 3WD 8" 50PSI SR NC 60PSI 24V
BV3W08US6LDXXXX	A7F30005061	NYL3-7081/93-1603	BFV 3WD 8" 50PSI SR NC 60PSI
BV3W10FD6LARXXX	A7F30003539	NYL3-1100/92-160-P	BFV 3WA 10" 175PSI DA NC 60PSI POS
BV3W10FD6LAXXXX	A7F30003533	NYL3-1100/92-160	BFV 3WA 10" 175PSI DA 60PSI
BV3W10FD6LAYXXX	A7F30003535	NYL3-1100/92-160-S	BFV 3WA 10" 175PSI DA 60PSI 120V
BV3W10FD6LAZXXX	A7F30003536	NYL3-1100/92-160-S4C	BFV 3WA 10" 175PSI DA 60PSI 24V
BV3W10FD6LBRXXX	A7F30003723	NYL3-8100/92-160-P	BFV 3WB 10" 175PSI DA NC 60PSI POS
BV3W10FD6LBXXXX	A7F30003717	NYL3-8100/92-160	BFV 3WB 10" 175PSI DA 60PSI
BV3W10FD6LBYXXX	A7F30003719	NYL3-8100/92-160-S	BFV 3WB 10" 175PSI DA 60PSI 120V
BV3W10FD6LBZXXX	A7F30003720	NYL3-8100/92-160-S4C	BFV 3WB 10" 175PSI DA 60PSI 24V
BV3W10FD6LCRXXX	A7F30003907	NYL3-2100/92-160-P	BFV 3WC 10" 175PSI DA NC 60PSI POS
BV3W10FD6LCXXXX	A7F30003901	NYL3-2100/92-160	BFV 3WC 10" 175PSI DA 60PSI
BV3W10FD6LCYXXX	A7F30003903	NYL3-2100/92-160-S	BFV 3WC 10" 175PSI DA 60PSI 120V
BV3W10FD6LCZXXX	A7F30003904	NYL3-2100/92-160-S4C	BFV 3WC 10" 175PSI DA 60PSI 24V
BV3W10FD6LDRXXX	A7F30004091	NYL3-7100/92-160-P	BFV 3WD 10" 175PSI DA NC 60PSI POS
BV3W10FD6LDXXXX	A7F30004085	NYL3-7100/92-160	BFV 3WD 10" 175PSI DA 60PSI
BV3W10FD6LDYXXX	A7F30004087	NYL3-7100/92-160-S	BFV 3WD 10" 175PSI DA 60PSI 120V
BV3W10FD6LDZXXX	A7F30004088	NYL3-7100/92-160-S4C	BFV 3WD 10" 175PSI DA 60PSI 24V
BV3W10FE2LAXXXH	A7F30002502	NYL3-1100/70-0501H	BFV 3WA 10" 175PSI 120VAC 2 POS HTR
BV3W10FE2LAXXXX	A7F30002489	NYL3-1100/70-0501	BFV 3WA 10" 175PSI 120VAC 2 POS
BV3W10FE2LBXXHX	A7F30002799	NYL3-8100/70-0501H	BFV 3WB 10" 175PSI 120VAC 2 POS HTR
BV3W10FE2LBXXXX	A7F30002798	NYL3-8100/70-0501	BFV 3WB 10" 175PSI 120VAC 2 POS
BV3W10FE2LCXXHX	A7F30002992	NYL3-2100/70-0501H	BFV 3WC 10" 175PSI 120VAC 2 POS HTR
BV3W10FE2LCXXXX	A7F30002991	NYL3-2100/70-0501	BFV 3WC 10" 175PSI 120VAC 2 POS
BV3W10FE2LDXXHX	A7F30003175	NYL3-7100/70-0501H	BFV 3WD 10" 175PSI 120VAC 2 POS HTR
BV3W10FE2LDXXXX	A7F30003174	NYL3-7100/70-0501	BFV 3WD 10" 175PSI 120VAC 2 POS
BV3W10FEMLAXXXH	A7F30002503	NYL3-1100/70-0501SVH	BFV 3WA 10" 175PSI 120VAC MOD HTR

Unrestricted

BV3W10FEMLBXXHX	A7F30002818	NYL3-8100/70-0501SVH	BFV 3WB 10" 175PSI 120VAC MOD HTR
BV3W10FEMLCXXHX	A7F30002993	NYL3-2100/70-0501SVH	BFV 3WC 10" 175PSI 120VAC MOD HTR
BV3W10FEMLDXXHX	A7F30003176	NYL3-7100/70-0501SVH	BFV 3WD 10" 175PSI 120VAC MOD HTR
BV3W10FS6LAQXXX	A7F30004611	NYL3-1100/93-2552-P	BFV 3WA 10" 175PSI SR NC 60PSI POS
BV3W10FS6LAVXXX	A7F30004607	NYL3-1100/93-2552-S	BFV 3WA 10" 175PSI SR NC 60PSI 120V
BV3W10FS6LAWXXX	A7F30004608	NYL3-1100/93-2552-S4C	BFV 3WA 10" 175PSI SR NC 60PSI 24V
BV3W10FS6LAXXXX	A7F30004605	NYL3-1100/93-2552	BFV 3WA 10" 175PSI SR NC 60PSI
BV3W10FS6LBQXXX	A7F30004771	NYL3-8100/93-2552-P	BFV 3WB 10" 175PSI SR NC 60PSI POS
BV3W10FS6LBVXXX	A7F30004767	NYL3-8100/93-2552-S	BFV 3WB 10" 175PSI SR NC 60PSI 120V
BV3W10FS6LBWXXX	A7F30004768	NYL3-8100/93-2552-S4C	BFV 3WB 10" 175PSI SR NC 60PSI 24V
BV3W10FS6LBXXXX	A7F30004765	NYL3-8100/93-2552	BFV 3WB 10" 175PSI SR NC 60PSI
BV3W10FS6LCQXXX	A7F30004931	NYL3-2100/93-2552-P	BFV 3WC 10" 175PSI SR NC 60PSI POS
BV3W10FS6LCVXXX	A7F30004927	NYL3-2100/93-2552-S	BFV 3WC 10" 175PSI SR NC 60PSI 120V
BV3W10FS6LCWXXX	A7F30004928	NYL3-2100/93-2552-S4C	BFV 3WC 10" 175PSI SR NC 60PSI 24V
BV3W10FS6LCXXXX	A7F30004925	NYL3-2100/93-2552	BFV 3WC 10" 175PSI SR NC 60PSI
BV3W10FS6LDQXXX	A7F30005091	NYL3-7100/93-2552-P	BFV 3WD 10" 175PSI SR NC 60PSI POS
BV3W10FS6LDVXXX	A7F30005087	NYL3-7100/93-2552-S	BFV 3WD 10" 175PSI SR NC 60PSI 120V
BV3W10FS6LDWXXX	A7F30005088	NYL3-7100/93-2552-S4C	BFV 3WD 10" 175PSI SR NC 60PSI 24V
BV3W10FS6LDXXXX	A7F30005085	NYL3-7100/93-2552	BFV 3WD 10" 175PSI SR NC 60PSI
BV3W10UD6LARXXX	A7F30003531	NYL3-1101/92-127-P	BFV 3WA 10" 50PSI DA NC 60PSI POS
BV3W10UD6LAXXXX	A7F30003525	NYL3-1101/92-127	BFV 3WA 10" 50PSI DA 60PSI
BV3W10UD6LAYXXX	A7F30003527	NYL3-1101/92-127-S	BFV 3WA 10" 50PSI DA 60PSI 120V
BV3W10UD6LAZXXX	A7F30003528	NYL3-1101/92-127-S4C	BFV 3WA 10" 50PSI DA 60PSI 24V
BV3W10UD6LBRXXX	A7F30003715	NYL3-8101/92-127-P	BFV 3WB 10" 50PSI DA NC 60PSI POS
BV3W10UD6LBXXXX	A7F30003709	NYL3-8101/92-127	BFV 3WB 10" 50PSI DA 60PSI
BV3W10UD6LBYXXX	A7F30003711	NYL3-8101/92-127-S	BFV 3WB 10" 50PSI DA 60PSI 120V
BV3W10UD6LBZXXX	A7F30003712	NYL3-8101/92-127-S4C	BFV 3WB 10" 50PSI DA 60PSI 24V
BV3W10UD6LCRXXX	A7F30003899	NYL3-2101/92-127-P	BFV 3WC 10" 50PSI DA NC 60PSI POS
BV3W10UD6LCXXXX	A7F30003893	NYL3-2101/92-127	BFV 3WC 10" 50PSI DA 60PSI
BV3W10UD6LCYXXX	A7F30003895	NYL3-2101/92-127-S	BFV 3WC 10" 50PSI DA 60PSI 120V
BV3W10UD6LCZXXX	A7F30003896	NYL3-2101/92-127-S4C	BFV 3WC 10" 50PSI DA 60PSI 24V
BV3W10UD6LDRXXX	A7F30004083	NYL3-7101/92-127-P	BFV 3WD 10" 50PSI DA NC 60PSI POS
BV3W10UD6LDXXXX	A7F30004077	NYL3-7101/92-127	BFV 3WD 10" 50PSI DA 60PSI
BV3W10UD6LDYXXX	A7F30004079	NYL3-7101/92-127-S	BFV 3WD 10" 50PSI DA 60PSI 120V
BV3W10UD6LDZXXX	A7F30004080	NYL3-7101/92-127-S4C	BFV 3WD 10" 50PSI DA 60PSI 24V
BV3W10UE2LAXXXH	A7F30002487	NYL3-1101/70-0201H	BFV 3WA 10" 50PSI 120VAC 2 POS HTR
BV3W10UE2LAXXXX	A7F30002486	NYL3-1101/70-0201	BFV 3WA 10" 50PSI 120VAC 2 POS
BV3W10UE2LBXXHX	A7F30002796	NYL3-8101/70-0201H	BFV 3WB 10" 50PSI 120VAC 2 POS HTR
BV3W10UE2LBXXXX	A7F30002795	NYL3-8101/70-0201	BFV 3WB 10" 50PSI 120VAC 2 POS
BV3W10UE2LCXXHX	A7F30002969	NYL3-2101/70-0201H	BFV 3WC 10" 50PSI 120VAC 2 POS HTR
BV3W10UE2LCXXXX	A7F30002968	NYL3-2101/70-0201	BFV 3WC 10" 50PSI 120VAC 2 POS
BV3W10UE2LDXXHX	A7F30003172	NYL3-7101/70-0201H	BFV 3WD 10" 50PSI 120VAC 2 POS HTR
BV3W10UE2LDXXXX	A7F30003171	NYL3-7101/70-0201	BFV 3WD 10" 50PSI 120VAC 2 POS
BV3W10UEMLAXXXH	A7F30002488	NYL3-1101/70-0201SVH	BFV 3WA 10" 50PSI 120VAC MOD HTR
BV3W10UEMLBXXHX	A7F30002797	NYL3-8101/70-0201SVH	BFV 3WB 10" 50PSI 120VAC MOD HTR
BV3W10UEMLCXXHX	A7F30002990	NYL3-2101/70-0201SVH	BFV 3WC 10" 50PSI 120VAC MOD HTR
BV3W10UEMLDXXHX	A7F30003173	NYL3-7101/70-0201SVH	BFV 3WD 10" 50PSI 120VAC MOD HTR
BV3W10US6LAQXXX	A7F30004603	NYL3-1101/93-2102-P	BFV 3WA 10" 50PSI SR NC 60PSI POS
BV3W10US6LAVXXX	A7F30004599	NYL3-1101/93-2102-S	BFV 3WA 10" 50PSI SR NC 60PSI 120V
BV3W10US6LAWXXX	A7F30004600	NYL3-1101/93-2102-S4C	BFV 3WA 10" 50PSI SR NC 60PSI 24V
BV3W10US6LAXXXX	A7F30004597	NYL3-1101/93-2102	BFV 3WA 10" 50PSI SR NC 60PSI
BV3W10US6LBQXXX	A7F30004763	NYL3-8101/93-2102-P	BFV 3WB 10" 50PSI SR NC 60PSI POS

Unrestricted

BV3W10US6LBVXXX	A7F30004759	NYL3-8101/93-2102-S	BFV 3WB 10" 50PSI SR NC 60PSI 120V
BV3W10US6LBWXXX	A7F30004760	NYL3-8101/93-2102-S4C	BFV 3WB 10" 50PSI SR NC 60PSI 24V
BV3W10US6LBXXX	A7F30004757	NYL3-8101/93-2102	BFV 3WB 10" 50PSI SR NC 60PSI
BV3W10US6LCQXXX	A7F30004923	NYL3-2101/93-2102-P	BFV 3WC 10" 50PSI SR NC 60PSI POS
BV3W10US6LCVXXX	A7F30004919	NYL3-2101/93-2102-S	BFV 3WC 10" 50PSI SR NC 60PSI 120V
BV3W10US6LCWXXX	A7F30004920	NYL3-2101/93-2102-S4C	BFV 3WC 10" 50PSI SR NC 60PSI 24V
BV3W10US6LCXXX	A7F30004917	NYL3-2101/93-2102	BFV 3WC 10" 50PSI SR NC 60PSI
BV3W10US6LDQXXX	A7F30005083	NYL3-7101/93-2102-P	BFV 3WD 10" 50PSI SR NC 60PSI POS
BV3W10US6LDVXXX	A7F30005079	NYL3-7101/93-2102-S	BFV 3WD 10" 50PSI SR NC 60PSI 120V
BV3W10US6LDWXXX	A7F30005080	NYL3-7101/93-2102-S4C	BFV 3WD 10" 50PSI SR NC 60PSI 24V
BV3W10US6LDXXX	A7F30005077	NYL3-7101/93-2102	BFV 3WD 10" 50PSI SR NC 60PSI
BV3W12FD6LARXXX	A7F30003555	NYL3-1120/92-210-P	BFV 3WA 12" 175PSI DA NC 60PSI POS
BV3W12FD6LAXXXX	A7F30003549	NYL3-1120/92-210	BFV 3WA 12" 175PSI DA 60PSI
BV3W12FD6LAYXXX	A7F30003551	NYL3-1120/92-210-S	BFV 3WA 12" 175PSI DA 60PSI 120V
BV3W12FD6LAZXXX	A7F30003552	NYL3-1120/92-210-S4C	BFV 3WA 12" 175PSI DA 60PSI 24V
BV3W12FD6LBRXXX	A7F30003739	NYL3-8120/92-210-P	BFV 3WB 12" 175PSI DA NC 60PSI POS
BV3W12FD6LBXXX	A7F30003733	NYL3-8120/92-210	BFV 3WB 12" 175PSI DA 60PSI
BV3W12FD6LBYXXX	A7F30003735	NYL3-8120/92-210-S	BFV 3WB 12" 175PSI DA 60PSI 120V
BV3W12FD6LBZXXX	A7F30003736	NYL3-8120/92-210-S4C	BFV 3WB 12" 175PSI DA 60PSI 24V
BV3W12FD6LCRXXX	A7F30003923	NYL3-2120/92-210-P	BFV 3WC 12" 175PSI DA NC 60PSI POS
BV3W12FD6LCXXX	A7F30003917	NYL3-2120/92-210	BFV 3WC 12" 175PSI DA 60PSI
BV3W12FD6LCYXXX	A7F30003919	NYL3-2120/92-210-S	BFV 3WC 12" 175PSI DA 60PSI 120V
BV3W12FD6LCZXXX	A7F30003920	NYL3-2120/92-210-S4C	BFV 3WC 12" 175PSI DA 60PSI 24V
BV3W12FD6LDRXXX	A7F30004107	NYL3-7120/92-210-P	BFV 3WD 12" 175PSI DA NC 60PSI POS
BV3W12FD6LDXXX	A7F30004101	NYL3-7120/92-210	BFV 3WD 12" 175PSI DA 60PSI
BV3W12FD6LDYXXX	A7F30004103	NYL3-7120/92-210-S	BFV 3WD 12" 175PSI DA 60PSI 120V
BV3W12FD6LDZXXX	A7F30004104	NYL3-7120/92-210-S4C	BFV 3WD 12" 175PSI DA 60PSI 24V
BV3W12FE2LAXXHX	A7F30002508	NYL3-1120/70-0651H	BFV 3WA 12" 175PSI 120VAC 2 POS HTR
BV3W12FE2LAXXXX	A7F30002507	NYL3-1120/70-0651	BFV 3WA 12" 175PSI 120VAC 2 POS
BV3W12FE2LBXXHX	A7F30002826	NYL3-8120/70-0651H	BFV 3WB 12" 175PSI 120VAC 2 POS HTR
BV3W12FE2LBXXX	A7F30002825	NYL3-8120/70-0651	BFV 3WB 12" 175PSI 120VAC 2 POS
BV3W12FE2LCXXHX	A7F30002998	NYL3-2120/70-0651H	BFV 3WC 12" 175PSI 120VAC 2 POS HTR
BV3W12FE2LCXXX	A7F30002997	NYL3-2120/70-0651	BFV 3WC 12" 175PSI 120VAC 2 POS
BV3W12FE2LDXXHX	A7F30003181	NYL3-7120/70-0651H	BFV 3WD 12" 175PSI 120VAC 2 POS HTR
BV3W12FE2LDXXX	A7F30003180	NYL3-7120/70-0651	BFV 3WD 12" 175PSI 120VAC 2 POS
BV3W12FEMLAXXHX	A7F30002509	NYL3-1120/70-0651SVH	BFV 3WA 12" 175PSI 120VAC MOD HTR
BV3W12FEMLBXXHX	A7F30002827	NYL3-8120/70-0651SVH	BFV 3WB 12" 175PSI 120VAC MOD HTR
BV3W12FEMLCXXHX	A7F30002999	NYL3-2120/70-0651SVH	BFV 3WC 12" 175PSI 120VAC MOD HTR
BV3W12FEMLDXXHX	A7F30003182	NYL3-7120/70-0651SVH	BFV 3WD 12" 175PSI 120VAC MOD HTR
BV3W12FS6LAQXXX	A7F30004627	NYL3-1120/93-2553-P	BFV 3WA 12" 175PSI SR NC 60PSI POS
BV3W12FS6LAVXXX	A7F30004623	NYL3-1120/93-2553-S	BFV 3WA 12" 175PSI SR NC 60PSI 120V
BV3W12FS6LAWXXX	A7F30004624	NYL3-1120/93-2553-S4C	BFV 3WA 12" 175PSI SR NC 60PSI 24V
BV3W12FS6LAXXXX	A7F30004621	NYL3-1120/93-2553	BFV 3WA 12" 175PSI SR NC 60PSI
BV3W12FS6LBQXXX	A7F30004787	NYL3-8120/93-2553-P	BFV 3WB 12" 175PSI SR NC 60PSI POS
BV3W12FS6LBVXXX	A7F30004783	NYL3-8120/93-2553-S	BFV 3WB 12" 175PSI SR NC 60PSI 120V
BV3W12FS6LBWXXX	A7F30004784	NYL3-8120/93-2553-S4C	BFV 3WB 12" 175PSI SR NC 60PSI 24V
BV3W12FS6LBXXX	A7F30004781	NYL3-8120/93-2553	BFV 3WB 12" 175PSI SR NC 60PSI
BV3W12FS6LCQXXX	A7F30004947	NYL3-2120/93-2553-P	BFV 3WC 12" 175PSI SR NC 60PSI POS
BV3W12FS6LCVXXX	A7F30004943	NYL3-2120/93-2553-S	BFV 3WC 12" 175PSI SR NC 60PSI 120V
BV3W12FS6LCWXXX	A7F30004944	NYL3-2120/93-2553-S4C	BFV 3WC 12" 175PSI SR NC 60PSI 24V
BV3W12FS6LCXXX	A7F30004941	NYL3-2120/93-2553	BFV 3WC 12" 175PSI SR NC 60PSI
BV3W12FS6LDQXXX	A7F30005107	NYL3-7120/93-2553-P	BFV 3WD 12" 175PSI SR NC 60PSI POS

Unrestricted

BV3W12FS6LDVXXX	A7F30005103	NYL3-7120/93-2553-S	BFV 3WD 12" 175PSI SR NC 60PSI 120V
BV3W12FS6LDWXXX	A7F30005104	NYL3-7120/93-2553-S4C	BFV 3WD 12" 175PSI SR NC 60PSI 24V
BV3W12FS6LDXXX	A7F30005101	NYL3-7120/93-2553	BFV 3WD 12" 175PSI SR NC 60PSI
BV3W12UD6LARXXX	A7F30003547	NYL3-1121/92-160-P	BFV 3WA 12" 50PSI DA NC 60PSI POS
BV3W12UD6LAXXXX	A7F30003541	NYL3-1121/92-160	BFV 3WA 12" 50PSI DA 60PSI
BV3W12UD6LAYXXX	A7F30003543	NYL3-1121/92-160-S	BFV 3WA 12" 50PSI DA 60PSI 120V
BV3W12UD6LAZXXX	A7F30003544	NYL3-1121/92-160-S4C	BFV 3WA 12" 50PSI DA 60PSI 24V
BV3W12UD6LBRXXX	A7F30003731	NYL3-8121/92-160-P	BFV 3WB 12" 50PSI DA NC 60PSI POS
BV3W12UD6LBXXXX	A7F30003725	NYL3-8121/92-160	BFV 3WB 12" 50PSI DA 60PSI
BV3W12UD6LBYXXX	A7F30003727	NYL3-8121/92-160-S	BFV 3WB 12" 50PSI DA 60PSI 120V
BV3W12UD6LBZXXX	A7F30003728	NYL3-8121/92-160-S4C	BFV 3WB 12" 50PSI DA 60PSI 24V
BV3W12UD6LCRXXX	A7F30003915	NYL3-2121/92-160-P	BFV 3WC 12" 50PSI DA NC 60PSI POS
BV3W12UD6LCXXXX	A7F30003909	NYL3-2121/92-160	BFV 3WC 12" 50PSI DA 60PSI
BV3W12UD6LCYXXX	A7F30003911	NYL3-2121/92-160-S	BFV 3WC 12" 50PSI DA 60PSI 120V
BV3W12UD6LCZXXX	A7F30003912	NYL3-2121/92-160-S4C	BFV 3WC 12" 50PSI DA 60PSI 24V
BV3W12UD6LDRXXX	A7F30004099	NYL3-7121/92-160-P	BFV 3WD 12" 50PSI DA NC 60PSI POS
BV3W12UD6LDXXXX	A7F30004093	NYL3-7121/92-160	BFV 3WD 12" 50PSI DA 60PSI
BV3W12UD6LDYXXX	A7F30004095	NYL3-7121/92-160-S	BFV 3WD 12" 50PSI DA 60PSI 120V
BV3W12UD6LDZXXX	A7F30004096	NYL3-7121/92-160-S4C	BFV 3WD 12" 50PSI DA 60PSI 24V
BV3W12UE2LAXXHX	A7F30002505	NYL3-1121/70-0501H	BFV 3WA 12" 50PSI 120VAC 2 POS HTR
BV3W12UE2LAXXXX	A7F30002504	NYL3-1121/70-0501	BFV 3WA 12" 50PSI 120VAC 2 POS
BV3W12UE2LBXXHX	A7F30002823	NYL3-8121/70-0501H	BFV 3WB 12" 50PSI 120VAC 2 POS HTR
BV3W12UE2LBXXXX	A7F30002821	NYL3-8121/70-0501	BFV 3WB 12" 50PSI 120VAC 2 POS
BV3W12UE2LCXXHX	A7F30002995	NYL3-2121/70-0501H	BFV 3WC 12" 50PSI 120VAC 2 POS HTR
BV3W12UE2LCXXXX	A7F30002994	NYL3-2121/70-0501	BFV 3WC 12" 50PSI 120VAC 2 POS
BV3W12UE2LDXXHX	A7F30003178	NYL3-7121/70-0501H	BFV 3WD 12" 50PSI 120VAC 2 POS HTR
BV3W12UE2LDXXXX	A7F30003177	NYL3-7121/70-0501	BFV 3WD 12" 50PSI 120VAC 2 POS
BV3W12UEMLAXXHX	A7F30002506	NYL3-1121/70-0501SVH	BFV 3WA 12" 50PSI 120VAC MOD HTR
BV3W12UEMLBXXHX	A7F30002824	NYL3-8121/70-0501SVH	BFV 3WB 12" 50PSI 120VAC MOD HTR
BV3W12UEMLCXXHX	A7F30002996	NYL3-2121/70-0501SVH	BFV 3WC 12" 50PSI 120VAC MOD HTR
BV3W12UEMLDXXHX	A7F30003179	NYL3-7121/70-0501SVH	BFV 3WD 12" 50PSI 120VAC MOD HTR
BV3W12US6LAQXXX	A7F30004619	NYL3-1121/93-2103-P	BFV 3WA 12" 50PSI SR NC 60PSI POS
BV3W12US6LAVXXX	A7F30004615	NYL3-1121/93-2103-S	BFV 3WA 12" 50PSI SR NC 60PSI 120V
BV3W12US6LAWXXX	A7F30004616	NYL3-1121/93-2103-S4C	BFV 3WA 12" 50PSI SR NC 60PSI 24V
BV3W12US6LAXXXX	A7F30004613	NYL3-1121/93-2103	BFV 3WA 12" 50PSI SR NC 60PSI
BV3W12US6LBQXXX	A7F30004779	NYL3-8121/93-2103-P	BFV 3WB 12" 50PSI SR NC 60PSI POS
BV3W12US6LBVXXX	A7F30004775	NYL3-8121/93-2103-S	BFV 3WB 12" 50PSI SR NC 60PSI 120V
BV3W12US6LBWXXX	A7F30004776	NYL3-8121/93-2103-S4C	BFV 3WB 12" 50PSI SR NC 60PSI 24V
BV3W12US6LBXXXX	A7F30004773	NYL3-8121/93-2103	BFV 3WB 12" 50PSI SR NC 60PSI
BV3W12US6LCQXXX	A7F30004939	NYL3-2121/93-2103-P	BFV 3WC 12" 50PSI SR NC 60PSI POS
BV3W12US6LCVXXX	A7F30004935	NYL3-2121/93-2103-S	BFV 3WC 12" 50PSI SR NC 60PSI 120V
BV3W12US6LCWXXX	A7F30004936	NYL3-2121/93-2103-S4C	BFV 3WC 12" 50PSI SR NC 60PSI 24V
BV3W12US6LCXXXX	A7F30004933	NYL3-2121/93-2103	BFV 3WC 12" 50PSI SR NC 60PSI
BV3W12US6LDQXXX	A7F30005099	NYL3-7121/93-2103-P	BFV 3WD 12" 50PSI SR NC 60PSI POS
BV3W12US6LDVXXX	A7F30005095	NYL3-7121/93-2103-S	BFV 3WD 12" 50PSI SR NC 60PSI 120V
BV3W12US6LDWXXX	A7F30005096	NYL3-7121/93-2103-S4C	BFV 3WD 12" 50PSI SR NC 60PSI 24V
BV3W12US6LDXXXX	A7F30005093	NYL3-7121/93-2103	BFV 3WD 12" 50PSI SR NC 60PSI
BV3W14FD6LARXXX	A7F30003571	NYL3-1140/92-210-P	BFV 3WA 14" 150PSI DA NC 60PSI POS
BV3W14FD6LAXXXX	A7F30003565	NYL3-1140/92-210	BFV 3WA 14" 150PSI DA 60PSI
BV3W14FD6LAYXXX	A7F30003567	NYL3-1140/92-210-S	BFV 3WA 14" 150PSI DA 60PSI 120V
BV3W14FD6LAZXXX	A7F30003568	NYL3-1140/92-210-S4C	BFV 3WA 14" 150PSI DA 60PSI 24V
BV3W14FD6LBRXXX	A7F30003755	NYL3-8140/92-210-P	BFV 3WB 14" 150PSI DA NC 60PSI POS

Unrestricted

BV3W14FD6LBXXXX	A7F30003749	NYL3-8140/92-210	BFV 3WB 14" 150PSI DA 60PSI
BV3W14FD6LBXXXX	A7F30003751	NYL3-8140/92-210-S	BFV 3WB 14" 150PSI DA 60PSI 120V
BV3W14FD6LBZXXX	A7F30003752	NYL3-8140/92-210-S4C	BFV 3WB 14" 150PSI DA 60PSI 24V
BV3W14FD6LCRXXX	A7F30003939	NYL3-2140/92-210-P	BFV 3WC 14" 150PSI DA NC 60PSI POS
BV3W14FD6LCXXXX	A7F30003933	NYL3-2140/92-210	BFV 3WC 14" 150PSI DA 60PSI
BV3W14FD6LCYXXX	A7F30003935	NYL3-2140/92-210-S	BFV 3WC 14" 150PSI DA 60PSI 120V
BV3W14FD6LCZXXX	A7F30003936	NYL3-2140/92-210-S4C	BFV 3WC 14" 150PSI DA 60PSI 24V
BV3W14FD6LDRXXX	A7F30004123	NYL3-7140/92-210-P	BFV 3WD 14" 150PSI DA NC 60PSI POS
BV3W14FD6LDXXXX	A7F30004119	NYL3-7140/92-210-S	BFV 3WD 14" 150PSI DA 60PSI 120V
BV3W14FD6LDZXXX	A7F30004120	NYL3-7140/92-210-S4C	BFV 3WD 14" 150PSI DA 60PSI 24V
BV3W14FE2LAXXHX	A7F30063469	NYL3-1140/70-1300H	BFV 3WA 14" 150PSI 120VAC 2 POS HTR
BV3W14FE2LBXXHX	A7F30063481	NYL3-8140/70-1300H	BFV 3WB 14" 150PSI 120VAC 2 POS HTR
BV3W14FE2LCXXHX	A7F30063493	NYL3-2140/70-1300H	BFV 3WC 14" 150PSI 120VAC 2 POS HTR
BV3W14FE2LDXXHX	A7F30063505	NYL3-7140/70-1300H	BFV 3WD 14" 150PSI 120VAC 2 POS HTR
BV3W14FEMLAXXHX	A7F30065931	NYL3-1140/70-1300SVH	BFV 3WA 14" 150PSI 120VAC MOD HTR
BV3W14FEMLBXXHX	A7F30077286	NYL3-8140/70-1300SVH	BFV 3WB 14" 150PSI 120VAC MOD HTR
BV3W14FEMLCXXHX	A7F30077291	NYL3-2140/70-1300SVH	BFV 3WC 14" 150PSI 120VAC MOD HTR
BV3W14FEMLDXXHX	A7F30065930	NYL3-7140/70-1300SVH	BFV 3WD 14" 150PSI 120VAC MOD HTR
BV3W14FS6LAQXXX	A7F30004643	NYL3-1140/93-2554-P	BFV 3WA 14" 150PSI SR NC 60PSI POS
BV3W14FS6LAVXXX	A7F30004639	NYL3-1140/93-2554-S	BFV 3WA 14" 150PSI SR NC 60PSI 120V
BV3W14FS6LAWXXX	A7F30004640	NYL3-1140/93-2554-S4C	BFV 3WA 14" 150PSI SR NC 60PSI 24V
BV3W14FS6LAXXXX	A7F30004637	NYL3-1140/93-2554	BFV 3WA 14" 150PSI SR NC 60PSI
BV3W14FS6LBQXXX	A7F30004803	NYL3-8140/93-2554-P	BFV 3WB 14" 150PSI SR NC 60PSI POS
BV3W14FS6LBVXXX	A7F30004799	NYL3-8140/93-2554-S	BFV 3WB 14" 150PSI SR NC 60PSI 120V
BV3W14FS6LBWXXX	A7F30004800	NYL3-8140/93-2554-S4C	BFV 3WB 14" 150PSI SR NC 60PSI 24V
BV3W14FS6LBXXXX	A7F30004797	NYL3-8140/93-2554	BFV 3WB 14" 150PSI SR NC 60PSI
BV3W14FS6LCQXXX	A7F30004963	NYL3-2140/93-2554-P	BFV 3WC 14" 150PSI SR NC 60PSI POS
BV3W14FS6LCVXXX	A7F30004959	NYL3-2140/93-2554-S	BFV 3WC 14" 150PSI SR NC 60PSI 120V
BV3W14FS6LCWXXX	A7F30004960	NYL3-2140/93-2554-S4C	BFV 3WC 14" 150PSI SR NC 60PSI 24V
BV3W14FS6LCXXXX	A7F30004957	NYL3-2140/93-2554	BFV 3WC 14" 150PSI SR NC 60PSI
BV3W14FS6LDQXXX	A7F30005123	NYL3-7140/93-2554-P	BFV 3WD 14" 150PSI SR NC 60PSI POS
BV3W14FS6LDVXXX	A7F30005119	NYL3-7140/93-2554-S	BFV 3WD 14" 150PSI SR NC 60PSI 120V
BV3W14FS6LDWXXX	A7F30005120	NYL3-7140/93-2554-S4C	BFV 3WD 14" 150PSI SR NC 60PSI 24V
BV3W14FS6LDXXXX	A7F30005117	NYL3-7140/93-2554	BFV 3WD 14" 150PSI SR NC 60PSI
BV3W14UD6LARXXX	A7F30003563	NYL3-1141/92-160-P	BFV 3WA 14" 50PSI DA NC 60PSI POS
BV3W14UD6LAXXXX	A7F30003557	NYL3-1141/92-160	BFV 3WA 14" 50PSI DA 60PSI
BV3W14UD6LAYXXX	A7F30003559	NYL3-1141/92-160-S	BFV 3WA 14" 50PSI DA 60PSI 120V
BV3W14UD6LAZXXX	A7F30003560	NYL3-1141/92-160-S4C	BFV 3WA 14" 50PSI DA 60PSI 24V
BV3W14UD6LBRXXX	A7F30003747	NYL3-8141/92-160-P	BFV 3WB 14" 50PSI DA NC 60PSI POS
BV3W14UD6LBXXXX	A7F30003741	NYL3-8141/92-160	BFV 3WB 14" 50PSI DA 60PSI
BV3W14UD6LBXXXX	A7F30003743	NYL3-8141/92-160-S	BFV 3WB 14" 50PSI DA 60PSI 120V
BV3W14UD6LBZXXX	A7F30003744	NYL3-8141/92-160-S4C	BFV 3WB 14" 50PSI DA 60PSI 24V
BV3W14UD6LCRXXX	A7F30003931	NYL3-2141/92-160-P	BFV 3WC 14" 50PSI DA NC 60PSI POS
BV3W14UD6LCXXXX	A7F30003925	NYL3-2141/92-160	BFV 3WC 14" 50PSI DA 60PSI
BV3W14UD6LCYXXX	A7F30003927	NYL3-2141/92-160-S	BFV 3WC 14" 50PSI DA 60PSI 120V
BV3W14UD6LCZXXX	A7F30003928	NYL3-2141/92-160-S4C	BFV 3WC 14" 50PSI DA 60PSI 24V
BV3W14UD6LDRXXX	A7F30004115	NYL3-7141/92-160-P	BFV 3WD 14" 50PSI DA NC 60PSI POS
BV3W14UD6LDXXXX	A7F30004109	NYL3-7141/92-160	BFV 3WD 14" 50PSI DA 60PSI
BV3W14UD6LDYXXX	A7F30004111	NYL3-7141/92-160-S	BFV 3WD 14" 50PSI DA 60PSI 120V
BV3W14UD6LDZXXX	A7F30004112	NYL3-7141/92-160-S4C	BFV 3WD 14" 50PSI DA 60PSI 24V
BV3W14UE2LAXXHX	A7F30002522	NYL3-1141/70-0501H	BFV 3WA 14" 50PSI 120VAC 2 POS HTR
BV3W14UE2LAXXXX	A7F30002521	NYL3-1141/70-0501	BFV 3WA 14" 50PSI 120VAC 2 POS

Unrestricted

BV3W14UE2LBXXHX	A7F30002829	NYL3-8141/70-0501H	BFV 3WB 14" 50PSI 120VAC 2 POS HTR
BV3W14UE2LBXXXX	A7F30002828	NYL3-8141/70-0501	BFV 3WB 14" 50PSI 120VAC 2 POS
BV3W14UE2LCXXHX	A7F30003021	NYL3-2141/70-0501H	BFV 3WC 14" 50PSI 120VAC 2 POS HTR
BV3W14UE2LCXXXX	A7F30003001	NYL3-2141/70-0501	BFV 3WC 14" 50PSI 120VAC 2 POS
BV3W14UE2LDXXHX	A7F30003184	NYL3-7141/70-0501H	BFV 3WD 14" 50PSI 120VAC 2 POS HTR
BV3W14UE2LDXXXX	A7F30003183	NYL3-7141/70-0501	BFV 3WD 14" 50PSI 120VAC 2 POS
BV3W14UEMLAXXHX	A7F30002523	NYL3-1141/70-0501SVH	BFV 3WA 14" 50PSI 120VAC MOD HTR
BV3W14UEMLBXXHX	A7F30002831	NYL3-8141/70-0501SVH	BFV 3WB 14" 50PSI 120VAC MOD HTR
BV3W14UEMLCXXHX	A7F30003022	NYL3-2141/70-0501SVH	BFV 3WC 14" 50PSI 120VAC MOD HTR
BV3W14UEMLDXXHX	A7F30003185	NYL3-7141/70-0501SVH	BFV 3WD 14" 50PSI 120VAC MOD HTR
BV3W14US6LAQXXX	A7F30004635	NYL3-1141/93-2552-P	BFV 3WA 14" 50PSI SR NC 60PSI POS
BV3W14US6LAVXXX	A7F30004631	NYL3-1141/93-2552-S	BFV 3WA 14" 50PSI SR NC 60PSI 120V
BV3W14US6LAWXXX	A7F30004632	NYL3-1141/93-2552-S4C	BFV 3WA 14" 50PSI SR NC 60PSI 24V
BV3W14US6LAXXXX	A7F30004629	NYL3-1141/93-2552	BFV 3WA 14" 50PSI SR NC 60PSI
BV3W14US6LBQXXX	A7F30004795	NYL3-8141/93-2552-P	BFV 3WB 14" 50PSI SR NC 60PSI POS
BV3W14US6LBVXXX	A7F30004791	NYL3-8141/93-2552-S	BFV 3WB 14" 50PSI SR NC 60PSI 120V
BV3W14US6LBWXXX	A7F30004792	NYL3-8141/93-2552-S4C	BFV 3WB 14" 50PSI SR NC 60PSI 24V
BV3W14US6LBXXXX	A7F30004789	NYL3-8141/93-2552	BFV 3WB 14" 50PSI SR NC 60PSI
BV3W14US6LCQXXX	A7F30004955	NYL3-2141/93-2552-P	BFV 3WC 14" 50PSI SR NC 60PSI POS
BV3W14US6LCVXXX	A7F30004951	NYL3-2141/93-2552-S	BFV 3WC 14" 50PSI SR NC 60PSI 120V
BV3W14US6LCWXXX	A7F30004952	NYL3-2141/93-2552-S4C	BFV 3WC 14" 50PSI SR NC 60PSI 24V
BV3W14US6LCXXXX	A7F30004949	NYL3-2141/93-2552	BFV 3WC 14" 50PSI SR NC 60PSI
BV3W14US6LDQXXX	A7F30005115	NYL3-7141/93-2552-P	BFV 3WD 14" 50PSI SR NC 60PSI POS
BV3W14US6LDVXXX	A7F30005111	NYL3-7141/93-2552-S	BFV 3WD 14" 50PSI SR NC 60PSI 120V
BV3W14US6LDWXXX	A7F30005112	NYL3-7141/93-2552-S4C	BFV 3WD 14" 50PSI SR NC 60PSI 24V
BV3W14US6LDXXXX	A7F30005109	NYL3-7141/93-2552	BFV 3WD 14" 50PSI SR NC 60PSI
BV3W16FD6LARXXX	A7F30003587	NYL3-1160/92-255-P	BFV 3WA 16" 150PSI DA NC 60PSI POS
BV3W16FD6LAXXXX	A7F30003581	NYL3-1160/92-255	BFV 3WA 16" 150PSI DA 60PSI
BV3W16FD6LAYXXX	A7F30003583	NYL3-1160/92-255-S	BFV 3WA 16" 150PSI DA 60PSI 120V
BV3W16FD6LAZXXX	A7F30003584	NYL3-1160/92-255-S4C	BFV 3WA 16" 150PSI DA 60PSI 24V
BV3W16FD6LBRXXX	A7F30003771	NYL3-8160/92-255-P	BFV 3WB 16" 150PSI DA NC 60PSI POS
BV3W16FD6LBXXXX	A7F30003765	NYL3-8160/92-255	BFV 3WB 16" 150PSI DA 60PSI
BV3W16FD6LBYXXX	A7F30003767	NYL3-8160/92-255-S	BFV 3WB 16" 150PSI DA 60PSI 120V
BV3W16FD6LBZXXX	A7F30003768	NYL3-8160/92-255-S4C	BFV 3WB 16" 150PSI DA 60PSI 24V
BV3W16FD6LCRXXX	A7F30003955	NYL3-2160/92-255-P	BFV 3WC 16" 150PSI DA NC 60PSI POS
BV3W16FD6LCXXXX	A7F30003949	NYL3-2160/92-255	BFV 3WC 16" 150PSI DA 60PSI
BV3W16FD6LCYXXX	A7F30003951	NYL3-2160/92-255-S	BFV 3WC 16" 150PSI DA 60PSI 120V
BV3W16FD6LCZXXX	A7F30003952	NYL3-2160/92-255-S4C	BFV 3WC 16" 150PSI DA 60PSI 24V
BV3W16FD6LDRXXX	A7F30004139	NYL3-7160/92-255-P	BFV 3WD 16" 150PSI DA NC 60PSI POS
BV3W16FD6LDXXXX	A7F30004133	NYL3-7160/92-255	BFV 3WD 16" 150PSI DA 60PSI
BV3W16FD6LDYXXX	A7F30004135	NYL3-7160/92-255-S	BFV 3WD 16" 150PSI DA 60PSI 120V
BV3W16FD6LDZXXX	A7F30004136	NYL3-7160/92-255-S4C	BFV 3WD 16" 150PSI DA 60PSI 24V
BV3W16FE2LAXXHX	A7F30063471	NYL3-1160/70-1300H	BFV 3WA 16" 150PSI 120VAC 2 POS HTR
BV3W16FE2LBXXHX	A7F30063483	NYL3-8160/70-1300H	BFV 3WB 16" 150PSI 120VAC 2 POS HTR
BV3W16FE2LCXXHX	A7F30063495	NYL3-2160/70-1300H	BFV 3WC 16" 150PSI 120VAC 2 POS HTR
BV3W16FE2LDXXHX	A7F30063507	NYL3-7160/70-1300H	BFV 3WD 16" 150PSI 120VAC 2 POS HTR
BV3W16FEMLAXXHX	A7F30077282	NYL3-1160/70-1300SVH	BFV 3WA 16" 150PSI 120VAC MOD HTR
BV3W16FEMLBXXHX	A7F30077287	NYL3-8160/70-1300SVH	BFV 3WB 16" 150PSI 120VAC MOD HTR
BV3W16FEMLCXXHX	A7F30077292	NYL3-2160/70-1300SVH	BFV 3WC 16" 150PSI 120VAC MOD HTR
BV3W16FEMLDXXHX	A7F30077296	NYL3-7160/70-1300SVH	BFV 3WD 16" 150PSI 120VAC MOD HTR
BV3W16UD6LARXXX	A7F30003579	NYL3-1161/92-210-P	BFV 3WA 16" 50PSI DA NC 60PSI POS
BV3W16UD6LAXXXX	A7F30003573	NYL3-1161/92-210	BFV 3WA 16" 50PSI DA 60PSI

Unrestricted

BV3W16UD6LAYXXX	A7F30003575	NYL3-1161/92-210-S	BFV 3WA 16" 50PSI DA 60PSI 120V
BV3W16UD6LAZXXX	A7F30003576	NYL3-1161/92-210-S4C	BFV 3WA 16" 50PSI DA 60PSI 24V
BV3W16UD6LBRXXX	A7F30003763	NYL3-8161/92-210-P	BFV 3WB 16" 50PSI DA NC 60PSI POS
BV3W16UD6LBXXXX	A7F30003757	NYL3-8161/92-210	BFV 3WB 16" 50PSI DA 60PSI
BV3W16UD6LBYXXX	A7F30003759	NYL3-8161/92-210-S	BFV 3WB 16" 50PSI DA 60PSI 120V
BV3W16UD6LBZXXX	A7F30003760	NYL3-8161/92-210-S4C	BFV 3WB 16" 50PSI DA 60PSI 24V
BV3W16UD6LCRXXX	A7F30003947	NYL3-2161/92-210-P	BFV 3WC 16" 50PSI DA NC 60PSI POS
BV3W16UD6LCXXXX	A7F30003941	NYL3-2161/92-210	BFV 3WC 16" 50PSI DA 60PSI
BV3W16UD6LCYXXX	A7F30003943	NYL3-2161/92-210-S	BFV 3WC 16" 50PSI DA 60PSI 120V
BV3W16UD6LCZXXX	A7F30003944	NYL3-2161/92-210-S4C	BFV 3WC 16" 50PSI DA 60PSI 24V
BV3W16UD6LDRXXX	A7F30004131	NYL3-7161/92-210-P	BFV 3WD 16" 50PSI DA NC 60PSI POS
BV3W16UD6LDXXXX	A7F30004125	NYL3-7161/92-210	BFV 3WD 16" 50PSI DA 60PSI
BV3W16UD6LDYXXX	A7F30004127	NYL3-7161/92-210-S	BFV 3WD 16" 50PSI DA 60PSI 120V
BV3W16UD6LDZXXX	A7F30004128	NYL3-7161/92-210-S4C	BFV 3WD 16" 50PSI DA 60PSI 24V
BV3W16UE2LAXHXX	A7F30002528	NYL3-1161/70-0651H	BFV 3WA 16" 50PSI 120VAC 2 POS HTR
BV3W16UE2LAXXXX	A7F30002527	NYL3-1161/70-0651	BFV 3WA 16" 50PSI 120VAC 2 POS
BV3W16UE2LBXHXX	A7F30002836	NYL3-8161/70-0651H	BFV 3WB 16" 50PSI 120VAC 2 POS HTR
BV3W16UE2LBXXXX	A7F30002835	NYL3-8161/70-0651	BFV 3WB 16" 50PSI 120VAC 2 POS
BV3W16UE2LCXHXX	A7F30003027	NYL3-2161/70-0651H	BFV 3WC 16" 50PSI 120VAC 2 POS HTR
BV3W16UE2LCXXXX	A7F30003026	NYL3-2161/70-0651	BFV 3WC 16" 50PSI 120VAC 2 POS
BV3W16UE2LDXHXX	A7F30003190	NYL3-7161/70-0651H	BFV 3WD 16" 50PSI 120VAC 2 POS HTR
BV3W16UE2LDXXXX	A7F30003189	NYL3-7161/70-0651	BFV 3WD 16" 50PSI 120VAC 2 POS
BV3W16UEMLAXHXX	A7F30002529	NYL3-1161/70-0651SVH	BFV 3WA 16" 50PSI 120VAC MOD HTR
BV3W16UEMLBXHXX	A7F30002837	NYL3-8161/70-0651SVH	BFV 3WB 16" 50PSI 120VAC MOD HTR
BV3W16UEMLCXHXX	A7F30003028	NYL3-2161/70-0651SVH	BFV 3WC 16" 50PSI 120VAC MOD HTR
BV3W16UEMLDXHXX	A7F30003191	NYL3-7161/70-0651SVH	BFV 3WD 16" 50PSI 120VAC MOD HTR
BV3W16US6LAQXXX	A7F30004651	NYL3-1161/93-2553-P	BFV 3WA 16" 50PSI SR NC 60PSI POS
BV3W16US6LAVXXX	A7F30004647	NYL3-1161/93-2553-S	BFV 3WA 16" 50PSI SR NC 60PSI 120V
BV3W16US6LAWXXX	A7F30004648	NYL3-1161/93-2553-S4C	BFV 3WA 16" 50PSI SR NC 60PSI 24V
BV3W16US6LAXXXX	A7F30004645	NYL3-1161/93-2553	BFV 3WA 16" 50PSI SR NC 60PSI
BV3W16US6LBQXXX	A7F30004811	NYL3-8161/93-2553-P	BFV 3WB 16" 50PSI SR NC 60PSI POS
BV3W16US6LBVXXX	A7F30004807	NYL3-8161/93-2553-S	BFV 3WB 16" 50PSI SR NC 60PSI 120V
BV3W16US6LBWXXX	A7F30004808	NYL3-8161/93-2553-S4C	BFV 3WB 16" 50PSI SR NC 60PSI 24V
BV3W16US6LCQXXX	A7F30004971	NYL3-2161/93-2553-P	BFV 3WC 16" 50PSI SR NC 60PSI POS
BV3W16US6LCVXXX	A7F30004967	NYL3-2161/93-2553-S	BFV 3WC 16" 50PSI SR NC 60PSI 120V
BV3W16US6LCWXXX	A7F30004968	NYL3-2161/93-2553-S4C	BFV 3WC 16" 50PSI SR NC 60PSI 24V
BV3W16US6LDQXXX	A7F30005131	NYL3-7161/93-2553-P	BFV 3WD 16" 50PSI SR NC 60PSI POS
BV3W16US6LDVXXX	A7F30005127	NYL3-7161/93-2553-S	BFV 3WD 16" 50PSI SR NC 60PSI 120V
BV3W16US6LDWXXX	A7F30005128	NYL3-7161/93-2553-S4C	BFV 3WD 16" 50PSI SR NC 60PSI 24V
BV3W25FD6LARXXX	A7F30003451	NYL3-1025/92-083-P	BFV 3WA 2.5" 175PSI DA NC 60PSI POS
BV3W25FD6LAXXXX	A7F30003445	NYL3-1025/92-083	BFV 3WA 2.5" 175PSI DA 60PSI
BV3W25FD6LAYXXX	A7F30003447	NYL3-1025/92-083-SC	BFV 3WA 2.5" 175PSI DA 60PSI 120V
BV3W25FD6LAZXXX	A7F30003448	NYL3-1025/92-083-S4C	BFV 3WA 2.5" 175PSI DA 60PSI 24V
BV3W25FD6LBRXXX	A7F30003635	NYL3-8025/92-083-P	BFV 3WB 2.5" 175PSI DA NC 60PSI POS
BV3W25FD6LBXXXX	A7F30003629	NYL3-8025/92-083	BFV 3WB 2.5" 175PSI DA 60PSI
BV3W25FD6LBYXXX	A7F30003631	NYL3-8025/92-083-S	BFV 3WB 2.5" 175PSI DA 60PSI 120V
BV3W25FD6LBZXXX	A7F30003632	NYL3-8025/92-083-S4C	BFV 3WB 2.5" 175PSI DA 60PSI 24V
BV3W25FD6LCRXXX	A7F30003819	NYL3-2025/92-083-P	BFV 3WC 2.5" 175PSI DA NC 60PSI POS
BV3W25FD6LCXXXX	A7F30003813	NYL3-2025/92-083	BFV 3WC 2.5" 175PSI DA 60PSI
BV3W25FD6LCYXXX	A7F30003815	NYL3-2025/92-083-S	BFV 3WC 2.5" 175PSI DA 60PSI 120V
BV3W25FD6LCZXXX	A7F30003816	NYL3-2025/92-083-S4C	BFV 3WC 2.5" 175PSI DA 60PSI 24V
BV3W25FD6LDRXXX	A7F30004003	NYL3-7025/92-083-P	BFV 3WD 2.5" 175PSI DA NC 60PSI POS

Unrestricted

BV3W25FD6LDXXXX	A7F30003997	NYL3-7025/92-083	BFV 3WD 2.5" 175PSI DA 60PSI
BV3W25FD6LDYXXX	A7F30003999	NYL3-7025/92-083-S	BFV 3WD 2.5" 175PSI DA 60PSI 120V
BV3W25FD6LDZXXX	A7F30004000	NYL3-7025/92-083-S4C	BFV 3WD 2.5" 175PSI DA 60PSI 24V
BV3W25FE2LAXXHX	A7F30002347	NYL3-1025/70-0061H	BFV 3WA 2.5" 175PSI 120VAC 2 POS HTR
BV3W25FE2LAXXHX	A7F300077158	NYL3-1025/70-0061H	BFV 3WA 2.5" 175PSI 120VAC 2 POS HTR
BV3W25FE2LAXXXX	A7F30002346	NYL3-1025/70-0061	BFV 3WA 2.5" 175PSI 120VAC 2 POS
BV3W25FE2LAXXXX	A7F300077157	NYL3-1025/70-0061	BFV 3WA 2.5" 175PSI 120VAC 2 POS
BV3W25FE2LBXXHX	A7F30002645	NYL3-8025/70-0061H	BFV 3WB 2.5" 175PSI 120VAC 2 POS HTR
BV3W25FE2LBXXHX	A7F300077176	NYL3-8025/70-0061H	BFV 3WB 2.5" 175PSI 120VAC 2 POS HTR
BV3W25FE2LBXXXX	A7F30002644	NYL3-8025/70-0061	BFV 3WB 2.5" 175PSI 120VAC 2 POS
BV3W25FE2LBXXXX	A7F300077175	NYL3-8025/70-0061	BFV 3WB 2.5" 175PSI 120VAC 2 POS
BV3W25FE2LCXXHX	A7F30002895	NYL3-2025/70-0061H	BFV 3WC 2.5" 175PSI 120VAC 2 POS HTR
BV3W25FE2LCXXHX	A7F300077194	NYL3-2025/70-0061H	BFV 3WC 2.5" 175PSI 120VAC 2 POS HTR
BV3W25FE2LCXXXX	A7F30002889	NYL3-2025/70-0061	BFV 3WC 2.5" 175PSI 120VAC 2 POS
BV3W25FE2LCXXXX	A7F300077193	NYL3-2025/70-0061	BFV 3WC 2.5" 175PSI 120VAC 2 POS
BV3W25FE2LDXXHX	A7F30003142	NYL3-7025/70-0061H	BFV 3WD 2.5" 175PSI 120VAC 2 POS HTR
BV3W25FE2LDXXHX	A7F300077212	NYL3-7025/70-0061H	BFV 3WD 2.5" 175PSI 120VAC 2 POS HTR
BV3W25FE2LDXXXX	A7F30003141	NYL3-7025/70-0061	BFV 3WD 2.5" 175PSI 120VAC 2 POS
BV3W25FE2LDXXXX	A7F300077211	NYL3-7025/70-0061	BFV 3WD 2.5" 175PSI 120VAC 2 POS
BV3W25FEMLAXXHX	A7F30002348	NYL3-1025/70-0061SVH	BFV 3WA 2.5" 175PSI 120VAC MOD HTR
BV3W25FEMLBXXHX	A7F30002646	NYL3-8025/70-0061SVH	BFV 3WB 2.5" 175PSI 120VAC MOD HTR
BV3W25FEMLCXXHX	A7F300077195	NYL3-2025/70-0061SVH	BFV 3WC 2.5" 175PSI 120VAC MOD HTR
BV3W25FEMLDXXHX	A7F30003143	NYL3-7025/70-0061SVH	BFV 3WD 2.5" 175PSI 120VAC MOD HTR
BV3W25FEPLAXXHX	A7F300077159	NYL3-1025/70-0061SVH	BFV 3WA 2.5" 175PSI 120VAC 4-20 MOD HTR
BV3W25FEPLBXXHX	A7F300077177	NYL3-8025/70-0061SVH	BFV 3WB 2.5" 175PSI 120VAC 4-20 MOD HTR
BV3W25FEPLCXXHX	A7F30002896	NYL3-2025/70-0061SVH	BFV 3WC 2.5" 175PSI 120VAC 4-20 MOD HTR
BV3W25FEPLDXXHX	A7F300077213	NYL3-7025/70-0061SVH	BFV 3WD 2.5" 175PSI 120VAC 4-20 MOD HTR
BV3W25FS6LAQXXX	A7F30004523	NYL3-1025/93-923-P	BFV 3WA 2.5" 175PSI SR NC 60PSI POS
BV3W25FS6LAVXXX	A7F30004519	NYL3-1025/93-923-S	BFV 3WA 2.5" 175PSI SR NC 60PSI 120V
BV3W25FS6LAWXXX	A7F30004520	NYL3-1025/93-923-S4C	BFV 3WA 2.5" 175PSI SR NC 60PSI 24V
BV3W25FS6LAXXXX	A7F30004517	NYL3-1025/93-923	BFV 3WA 2.5" 175PSI SR NC 60PSI
BV3W25FS6LBQXXX	A7F30004683	NYL3-8025/93-923-P	BFV 3WB 2.5" 175PSI SR NC 60PSI POS
BV3W25FS6LBVXXX	A7F30004679	NYL3-8025/93-923-S	BFV 3WB 2.5" 175PSI SR NC 60PSI 120V
BV3W25FS6LBWXXX	A7F30004680	NYL3-8025/93-923-S4C	BFV 3WB 2.5" 175PSI SR NC 60PSI 24V
BV3W25FS6LBXXXX	A7F30004677	NYL3-8025/93-923	BFV 3WB 2.5" 175PSI SR NC 60PSI
BV3W25FS6LCQXXX	A7F30004843	NYL3-2025/93-923-P	BFV 3WC 2.5" 175PSI SR NC 60PSI POS
BV3W25FS6LCVXXX	A7F30004839	NYL3-2025/93-923-S	BFV 3WC 2.5" 175PSI SR NC 60PSI 120V
BV3W25FS6LCWXXX	A7F30004840	NYL3-2025/93-923-S4C	BFV 3WC 2.5" 175PSI SR NC 60PSI 24V
BV3W25FS6LCXXXX	A7F30004837	NYL3-2025/93-923	BFV 3WC 2.5" 175PSI SR NC 60PSI
BV3W25FS6LDQXXX	A7F30005003	NYL3-7025/93-923-P	BFV 3WD 2.5" 175PSI SR NC 60PSI POS
BV3W25FS6LDVXXX	A7F30004999	NYL3-7025/93-923-S	BFV 3WD 2.5" 175PSI SR NC 60PSI 120V
BV3W25FS6LDWXXX	A7F30005000	NYL3-7025/93-923-S4C	BFV 3WD 2.5" 175PSI SR NC 60PSI 24V
BV3W25FS6LDXXXX	A7F30004997	NYL3-7025/93-923	BFV 3WD 2.5" 175PSI SR NC 60PSI
BV3W25UG4LAXXXX	A7F30005258	NYL3-1025/GCA161.1U-D	BFV 3WA 2.5" 175PSI SR 24VAC 0-10DC
BV3W25UG4LBXXXX	A7F30005313	NYL3-8025/GCA161.1U-D	BFV 3WB 2.5" 175PSI SR 24VAC 0-10DC
BV3W25UG4LCXXXX	A7F30005368	NYL3-2025/GCA161.1U-D	BFV 3WC 2.5" 175PSI SR 24VAC 0-10DC
BV3W25UG4LDXXXX	A7F30005423	NYL3-7025/GCA161.1U-D	BFV 3WD 2.5" 175PSI SR 24VAC 0-10DC
BV3W25UG5LAXXXX	A7F30005260	NYL3-1025/GCA151.1U-D	BFV 3WA 2.5" 175PSI SR 24VAC 4-20mA
BV3W25UG5LBXXXX	A7F30005315	NYL3-8025/GCA151.1U-D	BFV 3WB 2.5" 175PSI SR 24VAC 4-20mA
BV3W25UG5LCXXXX	A7F30005370	NYL3-2025/GCA151.1U-D	BFV 3WC 2.5" 175PSI SR 24VAC 4-20mA
BV3W25UG5LDXXXX	A7F30005425	NYL3-7025/GCA151.1U-D	BFV 3WD 2.5" 175PSI SR 24VAC 4-20mA
BV3W25UG6LAXXXX	A7F30005251	NYL3-1025/GIB131.1U	BFV 3WA 2.5" 175PSI 24VAC TRI

Unrestricted

BV3W25UG6LBXXXX	A7F30005306	NYL3-8025/GIB131.1U	BFV 3WB 2.5" 175PSI 24VAC TRI
BV3W25UG6LCXXXX	A7F30005361	NYL3-2025/GIB131.1U	BFV 3WC 2.5" 175PSI 24VAC TRI
BV3W25UG6LDXXXX	A7F30005416	NYL3-7025/GIB131.1U	BFV 3WD 2.5" 175PSI 24VAC TRI
BV3W25UG7LAXXXX	A7F30005256	NYL3-1025/GIB161.1U	BFV 3WA 2.5" 175PSI 24VAC 0-10DC
BV3W25UG7LBXXXX	A7F30005311	NYL3-8025/GIB161.1U	BFV 3WB 2.5" 175PSI 24VAC 0-10DC
BV3W25UG7LCXXXX	A7F30005366	NYL3-2025/GIB161.1U	BFV 3WC 2.5" 175PSI 24VAC 0-10DC
BV3W25UG7LDXXXX	A7F30005421	NYL3-7025/GIB-161.1U	BFV 3WD 2.5" 175PSI 24VAC 0-10DC
BV2W02UE2LNXXHX	A7F30089281	NYL2-C020/70-0061H	BFV 2W 2" 120V 2POS 50PSI W/HT
BV2W03UE2LNXXHX	A7F30089282	NYL2-C030/70-0061H	BFV 2W 3" 120V 2POS 50PSI W/HT
BV2W25UE2LNXXHX	A7F30089283	NYL2-C025/70-0061H	BFV 2W 2.5" 120V 2POS 50PSI W/HT
BV3W02UE2LAXXHX	A7F30089284	NYL3-1020/70-0061H	BFV 3WA 2" 120V 2POS 50PSI W/HT
BV3W02UE2LBXXHX	A7F30089285	NYL3-8020/70-0061H	BFV 3WB 2" 120V 2POS 50PSI W/HT
BV3W02UE2LCXXHX	A7F30089286	NYL3-2020/70-0061H	BFV 3WC 2" 120V 2POS 50PSI W/HT
BV3W02UE2LDXXHX	A7F30089287	NYL3-7020/70-0061H	BFV 3WD 2" 120V 2POS 50PSI W/HT
BV3W02UE2LEXXHX	A7F30089288	NYL3-5020/70-0061H	BFV 3WE 2" 120V 2POS 50PSI W/HT
BV3W02UE2LFXXHX	A7F30089289	NYL3-6020/70-0061H	BFV 3WF 2" 120V 2POS 50PSI W/HT
BV3W03UE2LAXXHX	A7F30089370	NYL3-1020/70-0061H	BFV 3WA 3" 120V 2POS 50PSI W/HT
BV3W03UE2LBXXHX	A7F30089371	NYL3-8020/70-0061H	BFV 3WB 3" 120V 2POS 50PSI W/HT
BV3W03UE2LCXXHX	A7F30089372	NYL3-2020/70-0061H	BFV 3WC 3" 120V 2POS 50PSI W/HT
BV3W03UE2LDXXHX	A7F30089373	NYL3-7020/70-0061H	BFV 3WD 3" 120V 2POS 50PSI W/HT
BV3W03UE2LEXXHX	A7F30089374	NYL3-5020/70-0061H	BFV 3WE 3" 120V 2POS 50PSI W/HT
BV3W03UE2LFXXHX	A7F30089375	NYL3-6020/70-0061H	BFV 3WF 3" 120V 2POS 50PSI W/HT
BV3W25UE2LAXXHX	A7F30089376	NYL3-1025/70-0061H	BFV 3WA 2.5" 120V 2POS 50PSI W/HT
BV3W25UE2LBXXHX	A7F30089377	NYL3-8025/70-0061H	BFV 3WB 2.5" 120V 2POS 50PSI W/HT
BV3W25UE2LCXXHX	A7F30089378	NYL3-2025/70-0061H	BFV 3WC 2.5" 120V 2POS 50PSI W/HT
BV3W25UE2LDXXHX	A7F30089379	NYL3-7025/70-0061H	BFV 3WD 2.5" 120V 2POS 50PSI W/HT
BV3W25UE2LEXXHX	A7F30089380	NYL3-5025/70-0061H	BFV 3WE 2.5" 120V 2POS 50PSI W/HT
BV3W25UE2LFXXHX	A7F30089381	NYL3-6025/70-0061H	BFV 3WF 2.5" 120V 2POS 50PSI W/HT
BV2W02FEPLNXXHX	A7F30077122	NYL2-C020/70-0061SVH	BFV 2W 2" 100-240V MOD 4-20 W/HT
BV2W03FEPLNXXHX	A7F30077031	NYL2-C030/70-0061SVH	BFV 2W 3" 100-240V MOD 4-20 W/HT
BV2W04FEPLNXXHX	A7F30077030	NYL2-C040/70-0061SVH	BFV 2W 4" 100-240V MOD 4-20 W/HT
BV2W04UG3LCPXX	A7F30005194	NYL2-C041/GCA166.1U-D	BFV2W 4"24V FLOAT SR,NC,100W/SW
BV2W04UG3LOPXX	A7F30005235	NYL2-N041/GCA166.1U-D	BFV2W 4"24V FLOAT SR,NO,100W/SW
BV2W05FEPLNXXHX	A7F30077138	NYL2-C050/70-0061SVH	BFV 2W 5"100-240V MOD 4-20 W/HT
BV2W05UEPLNXXHX	A7F30077135	NYL2-C051/70-0061SVH	BFV 2W 5"100-240V MOD 4-20 100W/HT
BV2W06FEPLNXXHX	A7F30077144	NYL2-C060/70-0061SVH	BFV 2W 6"100-240V MOD 4-20 W/HT
BV2W06FS6LOXXX	A7F30004405	NYL2-N060/93-1274	BFV 2W 6" 60PSI SR NO
BV2W06UEPLNXXHX	A7F30077141	NYL2-C061/70-0061SVH	BFV 2W 6"100-240V MOD 4-20 100W/HT
BV2W08FEPLNXXHX	A7F30001797	NYL2-C080/70-0201SVH	BFV 2W 8"100-240V MOD 4-20 W/HT
BV2W08FS6LOXXX	A7F30004421	NYL2-N080/93-1603	BFV 2W 8" 60PSI SR NO
BV2W08UEPLNXXHX	A7F30001779	NYL2-C081/70-0121SVH	BFV 2W 8"100-240V MOD 4-20 50W/HT
BV2W10FEPLNXXHX	A7F30001829	NYL2-C100/70-0301SVH	BFV 2W 10"100-240V MOD 4-20 W/HT
BV2W10UEPLNXXHX	A7F30001815	NYL2-C101/70-0201SVH	BFV 2W 10"100-240V MOD 4-20 50W/HT
BV2W12FEPLNXXHX	A7F30001859	NYL2-C120/70-0501SVH	BFV 2W 12"100-240V MOD 4-20 W/HT
BV2W12UEPLNXXHX	A7F30001856	NYL2-C121/70-0301SVH	BFV 2W 12"100-240V MOD 4-20 50W/HT
BV2W14FEPLNXXHX	A7F30001908	NYL2-C140/70-0651SVH	BFV 2W 14"100-240V MOD 4-20 W/HT
BV2W14UEPLNXXHX	A7F30001905	NYL2-C141/70-0501SVH	BFV 2W 14"100-240V MOD 4-20 50W/HT
BV2W16FEPLNXXHX	A7F30073614	NYL2-C160/70-1300SVH	BFV 2W 16"100-240V MOD 4-20 W/HT
BV2W16UEPLNXXHX	A7F30001996	NYL2-C161/70-0651SVH	BFV 2W 16"100-240V MOD 4-20 50W/HT
BV2W25FEPLNXXHX	A7F30077125	NYL2-C025/70-0061SVH	BFV 2W 2.5"100-240V MOD 4-20 W/HT
BV3W02UG1LAXXXX	A7F30005241	NYL3-1020/GCA221.1U	BFV 3WA 2" 120V ON/OFF SR 50PSI
BV3W02UG1LBXXXX	A7F30005296	NYL3-8020/GCA221.1U	BFV 3WB 2"120V ON/OFF SR 50PSI

Unrestricted

BV3W02UG1LCXXX	A7F30005351	NYL3-2020/GCA221.1U	BFV 3WC 2" 120V ON/OFF SR 50PSI
BV3W02UG1LDXXX	A7F30005406	NYL3-7020/GCA221.1U	BFV 3WD 2"120V ON/OFF SR 50PSI
BV3W02UG2LBXAXX	A7F30005297	NYL3-8020/GCA226.1U	BFV 3WB 2"24V ON/OF SR 50PSI W/SW
BV3W03UG1LAXXXX	A7F30005265	NYL3-1030/GCA221.1U-D	BFV 3WA 3" 120V ON/OFF SR 50PSI
BV3W03UG1LBXXXX	A7F30005320	NYL3-8030/GCA221.1U-D	BFV 3WB 3" 120V ON/OFF SR 50PSI
BV3W03UG1LDXXX	A7F30005430	NYL3-7030/GCA221.1U-D	BFV 3WD 3"120V ON/OFF SR 50PSI
BV3W03UG2LAXXXX	A7F30005263	NYL3-1030/GCA121.1U-D	BFV 3WA 3"24V ON/OFF SR 50PSI
BV3W03UG2LBXXXX	A7F30005318	NYL3-8030/GCA121.1U-D	BFV 3WB 3"24V ON/OFF SR 50PSI
BV3W03UG2LCXAXX	A7F30005376	NYL3-2030/GCA226.1U-D	BFV 3WC 3"24V ON/OF SR 50PSI W/SW
BV3W03UG2LCXXX	A7F30005373	NYL3-2030/GCA121.1U-D	BFV 3WC 3" 24V ON/OFF SR 50PSI
BV3W03UG2LDXXX	A7F30005428	NYL3-7030/GCA121.1U-D	BFV 3WD 3" 24V ON/OFF SR 50PSI
BV3W04UEPLAXXHX	A7F300077165	NYL3-1041/70-0061SVH	BFV 3WA 4" 100-240V MOD 4-20 50PSI W/HT
BV3W04UG1LAXXXX	A7F30005276	NYL3-1041/GCA221.1U-D	BFV 3WA 4"120V ON/OFF SR 50PSI
BV3W04UG1LBXXXX	A7F30005331	NYL3-8041/GCA221.1U-D	BFV 3WB 4"120V ON/OFF SR 50PSI
BV3W04UG1LCXXX	A7F30005386	NYL3-2041/GCA221.1U-D	BFV 3WC 4"120V ON/OFF SR 50PSI
BV3W04UG1LDXXX	A7F30005441	NYL3-7041/GCA221.1U-D	BFV 3WD 4"120V ON/OFF SR 50PSI
BV3W04US6LBXXXX	A7F30004693	NYL3-8041/93-1182	BFV 3WB 4" 60PSI SR 50PSI UNDERCUT
BV3W05FEPLAXXHX	A7F30002409	NYL3-1050/70-0121SVH	BFV 3WA 5"100-240V MOD 4-20 W/HT
BV3W05FEPLBXXHX	A7F30002709	NYL3-8050/70-0121SVH	BFV 3WB 5"100-240V MOD 4-20 W/HT
BV3W05FEPLCXXHX	A7F30002914	NYL3-2050/70-0121SVH	BFV 3WC 5"100-240V MOD 4-20 W/HT
BV3W05FEPLDXXHX	A7F30003158	NYL3-7050/70-0121SVH	BFV 3WD 5"100-240V MOD 4-20 W/HT
BV3W05UD6LAYXXX	A7F30003479	NYL3-1051/92-092-S	BFV 3WA 5" 60PSI PNEUMATIC 50PSI/120V EP
BV3W05UEPLDXXHX	A7F300077225	NYL3-7051/70-0061SVH	BFV 3WD 5"100-240V MOD 4-20 100HT
BV3W06FEPLAXXHX	A7F30002447	NYL3-1060/70-0121SVH	BFV 3WA 6"100-240V MOD 4-20 W/HT
BV3W06FEPLBXXHX	A7F30002778	NYL3-8060/70-0121SVH	BFV 3WB 6"100-240V MOD 4-20 W/HT
BV3W06FEPLCXXHX	A7F30002961	NYL3-2060/70-0121SVH	BFV 3WC 6"100-240V MOD 4-20 W/HT
BV3W06FEPLDXXHX	A7F30003164	NYL3-7060/70-0121SVH	BFV 3WD 6"100-240V MOD 4-20 W/HT
BV3W06UEPLAXXHX	A7F30002441	NYL3-1061/70-0121SVH	BFV 3WA 6"100-240V MOD 4-20100HT
BV3W06UEPLBXXHX	A7F30002775	NYL3-8061/70-0121SVH	BFV 3WB 6"100-240V MOD 4-20 100HT
BV3W06UEPLCXXHX	A7F30002917	NYL3-2061/70-0121SVH	BFV 3WC 6"100-240V MOD 4-20 100HT
BV3W06UEPLDXXHX	A7F30003161	NYL3-7061/70-0121SVH	BFV 3WD 6"100-240V MOD 4-20 100HT
BV3W08FEPLAXXHX	A7F30002485	NYL3-1080/70-0201SVH	BFV 3WA 8"100-240V MOD 4-20 W/HT
BV3W08FEPLBXXHX	A7F30002794	NYL3-8080/70-0201SVH	BFV 3WB 8"100-240V MOD 4-20 W/HT
BV3W08FEPLCXXHX	A7F30002967	NYL3-2080/70-0201SVH	BFV 3WC 8"100-240V MOD 4-20 W/HT
BV3W08FEPLDXXHX	A7F30003170	NYL3-7080/70-0201SVH	BFV 3WD 8"100-240V MOD 4-20 W/HT
BV3W08UEPLAXXHX	A7F30002468	NYL3-1081/70-0121SVH	BFV 3WA 8"100-240V MOD 4-20 50PSI W/HT
BV3W08UEPLBXXHX	A7F30002791	NYL3-8081/70-0121SVH	BFV 3WB 8"100-240V MOD 4-20 50PSI W/HT
BV3W08UEPLCXXHX	A7F30002964	NYL3-2081/70-0121SVH	BFV 3WC 8"100-240V MOD 4-20 50PSI W/HT
BV3W08UEPLDXXHX	A7F30003167	NYL3-7081/70-0121SVH	BFV 3WD 8"100-240V MOD 4-20 50PSI W/HT
BV3W10FEPLAXXHX	A7F30002503	NYL3-1100/70-0501SVH	BFV 3WA 10"100-240V MOD 4-20 W/HT
BV3W10FEPLBXXHX	A7F30002818	NYL3-8100/70-0501SVH	BFV 3WB 10"100-240V MOD 4-20 W/HT
BV3W10FEPLCXXHX	A7F30002993	NYL3-2100/70-0501SVH	BFV 3WC 10"100-240V MOD 4-20 W/HT
BV3W10FEPLDXXHX	A7F30003176	NYL3-7100/70-0501SVH	BFV 3WD 10"100-240V MOD 4-20 W/HT
BV3W10UEPLAXXHX	A7F30002488	NYL3-1101/70-0201SVH	BFV 3WA 10"100-240V MOD 4-20 50 W/HT
BV3W10UEPLBXXHX	A7F30002797	NYL3-8101/70-0201SVH	BFV 3WB 10"100-240V MOD 4-20 50 W/HT
BV3W10UEPLCXXHX	A7F30002990	NYL3-2101/70-0201SVH	BFV 3WC 10"100-240V MOD 4-20 50 W/HT
BV3W10UEPLDXXHX	A7F30003173	NYL3-7101/70-0201SVH	BFV 3WD 10"100-240V MOD 4-20 D 50 W/HT
BV3W12FEPLAXXHX	A7F30002509	NYL3-1120/70-0651SVH	BFV 3WA 12"100-240V MOD 4-20 W/HT
BV3W12FEPLBXXHX	A7F30002827	NYL3-8120/70-0651SVH	BFV 3WB 12"100-240V MOD 4-20 W/HT
BV3W12FEPLCXXHX	A7F30002999	NYL3-2120/70-0651SVH	BFV 3WC 12"100-240V MOD 4-20 W/HT
BV3W12FEPLDXXHX	A7F30003182	NYL3-7120/70-0651SVH	BFV 3WD 12"100-240V MOD 4-20 W/HT
BV3W12UEPLAXXHX	A7F30002506	NYL3-1121/70-0501SVH	BFV 3WA 12"100-240V MOD 4-20 50 W/HT

Unrestricted

BV3W12UEPLBXXHX	A7F30002824	NYL3-8121/70-0501SVH	BFV 3WB 12"100-240V MOD 4-20 50 W/HT
BV3W12UEPLCXXHX	A7F30002996	NYL3-2121/70-0501SVH	BFV 3WC 12"100-240V MOD 4-20 50 W/HT
BV3W12UEPLDXXHX	A7F30003179	NYL3-7121/70-0501SVH	BFV 3WD 12"100-240V MOD 4-20 50 W/HT
BV3W14FD6LDYXXX	A7F30004119	NYL3-7140/92-210-S	BFV3WD 14" 60PSI DA W/120V EP
BV3W14FEPLAXXHX	A7F300065931	NYL3-1140/70-1300SVH	BFV 3WA 14"100-240V MOD 4-20 W/HT
BV3W14FEPLBXXHX	A7F30077286	NYL3-8140/70-1300SVH	BFV 3WB 14"100-240V MOD 4-20 W/HT
BV3W14FEPLCXXHX	A7F30077291	NYL3-2140/70-1300SVH	BFV 3WC 14"100-240V MOD 4-20 W/HT
BV3W14FEPLDXXHX	A7F300065930	NYL3-7140/70-1300SVH	BFV 3WD 14"100-240V MOD 4-20 W/HT
BV3W14UEPLAXXHX	A7F30002523	NYL3-1141/70-0501SVH	BFV 3WA 14"100-240V MOD 4-20 50 W/HT
BV3W14UEPLBXXHX	A7F30002831	NYL3-8141/70-0501SVH	BFV 3WB 14"100-240V MOD 4-20 50 W/HT
BV3W14UEPLCXXHX	A7F30003022	NYL3-2141/70-0501SVH	BFV 3WC 14"100-240V MOD 4-20 50 W/HT
BV3W14UEPLDXXHX	A7F30003185	NYL3-7141/70-0501SVH	BFV 3WD 14"100-240V MOD 4-20 50 W/HT
BV3W16FEPLAXXHX	A7F30077282	NYL3-1160/70-1300SVH	BFV 3WA 16"100-240V MOD 4-20 W/HT
BV3W16FEPLBXXHX	A7F30077287	NYL3-8160/70-1300SVH	BFV 3WB 16"100-240V MOD 4-20 W/HT
BV3W16FEPLCXXHX	A7F30077292	NYL3-2160/70-1300SVH	BFV 3WC 16"100-240V MOD 4-20 W/HT
BV3W16FEPLDXXHX	A7F30077296	NYL3-7160/70-1300SVH	BFV 3WD 16"100-240V MOD 4-20 W/HT
BV3W16UEPLAXXHX	A7F30002529	NYL3-1161/70-0651SVH	BFV 3WA 16"100-240V MOD 4-20 50 W/HT
BV3W16UEPLBXXHX	A7F30002837	NYL3-8161/70-0651SVH	BFV 3WB 16"100-240V MOD 4-20 B 50 W/HT
BV3W16UEPLCXXHX	A7F30003028	NYL3-2161/70-0651SVH	BFV 3WC 16"100-240V MOD 4-20 C 50 W/HT
BV3W16UEPLDXXHX	A7F30003191	NYL3-7161/70-0651SVH	BFV 3WD 16"100-240V MOD 4-20 D 50 W/HT
BV3W16US6LBXXXX	A7F30004805	NYL3-8161/93-2553	BFV 3WB 16" 60PSI SR 50
BV3W16US6LCXXXX	A7F30004965	NYL3-2161/93-2553	BFV 3WC 16" 60PSI SR 50
BV3W16US6LDXXXX	A7F30005125	NYL3-7161/93-2553	BFV 3WD 16" 60PSI SR 50
BV3W25UG2LAXXXX	A7F30005252	NYL3-1025/GCA121.1U-D	BFV 3WA 2.5"24V ON/OFF SR 50
BV3W25UG2LBXAXX	A7F30005308	NYL3-8025/GCA126.1U-D	BFV 3WB 2.5"24V ON/OFF SR 50 W/SW
BV3W25UG2LBXXXX	A7F30005307	NYL3-8025/GCA121.1U-D	BFV 3WB 2.5"24V ON/OFF SR 50
BV3W25UG2LCXXXX	A7F30005362	NYL3-2025/GCA121.1U-D	BFV 3WC 2.5"24V ON/OFF SR 50
BV3W25UG2LDXXXX	A7F30005417	NYL3-7025/GCA121.1U-D	BFV 3WD 2.5"24V ON/OFF SR 50